





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	9427	RELEASED	3/06/09	
A	-	REDRAWN	7/11/11	



Recommended PCB Layout



Poles	Tolerance
2-6P	±.006 [0.15]
7-12P	±.008 [0.20]
13-18P	±.010 [0.25]
19-24P	±.012 [0.30]

SPECIFICATIONS:

Material: Insulator: Thermoplastic, rated UL 94V-0
Insulator color: Green
Contact: Copper Alloy, Tin plated.
Electrical:
Operation voltage: 300 VAC
Current rating: 10 Amps
Mechanical:
Withstanding Voltage: 1.6KV
Environmental:
Operating temperature: -40°C to +115°C
Lead free, RoHS compliant.



Poles: 2 thru 24
A = .150 [3.81] X No. of Spaces + .197 [5.00]
B = .150 [3.81] X No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
.X	± .10	ØX	± .10	TITLE .150 [3.81] PITCH, TERMINAL BLOCK, VERTICAL			
.XX	± .020	ØXX	± .015				
.XXX	± .015	ØXXX	± .010				
.XXX	± .010	ØXXX	± .010				
APPROVALS				DATE			
DRAWN				3/06/09			
CHECKED							
APPROVED							
SIZE				PART NO.			
X				EB3-XX-B-180			
REF:				SHEET 1 OF 1			
SCALE				N/A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EB3-02-B-180](#) [EB3-03-B-180](#) [EB3-05-B-180](#) [EB3-04-B-180](#) [EB3-06-B-180](#) [EB3-14-B-180](#)