




APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	6/27/13	
A		UPDATE SHAPE	10/27/14	AY/NP



RECOMMENDED PCB LAYOUT



SECTION A-A



SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Contact: Brass, Tin plated

Screw: Steel, M2/Zinc plated

Cage: Brass, Nickel plated

Electrical:

Voltage rated: 300 V

Current rated: 10 A

Contact resistance: 20 mΩ

Insulation resistance: 500 MΩ/ 500VDC

Withstanding voltage: 2000 VAC for 1 minute

Mechanical:

Torque: 0.2Nm (1.8 lb.in)

Wire Range: 28-16Awg 1.0mm²

Environmental:

Temperature range: -40°C to +105°C

Lead free, RoHS compliant.



Positions: 02 thru 24

A = .138 [3.50] x No. of Positions

B = .138 [3.50] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	AY	6/27/13
CHECKED	NP	6/27/13
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE		REV.	
TERMINAL BLOCK, PCB, VERTICAL, .138" [3.50] PITCH		A	
SIZE	PART NO.		
X	EBWA-XX-A		
REF:	S00067C	SCALE:	NTS
		SHEET	1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EBWA-02-A](#) [EBWA-06-A](#) [EBWA-05-A](#) [EBWA-03-A](#) [EBWA-04-A](#)