

FEATURES:

- 7 pin SIP package
- No-load input current as low as 5mA
- Continuous short-circuit protection
- High Efficiency up to 89%
- Unregulated Output Types
- 1.5KVDC ~ 6KVDC Isolation
- Industry Standard Pinout
- Designed to IEC62368, UL62368, EN62368
- UL Recognized
- RoHS Compliant

Specifications typical at TA=25°C nominal input voltage and rated output current unless otherwise specified

Part Number	Input	Output	Output	Efficiency	Capacitive
	Voltage	Voltage	Current		Load μ F
	Range				
	Vdc	Vdc	mA	%TYP	μ F
EC2-05S052P3	4.5~5.5	5	400	84	2400
EC2-24S152P6	19.2~28.8	15	133	88	220
EC2-05D052P3	4.5~5.5	$\pm$ 5	$\pm$ 200	82	$\pm$ 1200

Note:

1: No suffix is standard isolation (1.5KVDC) e.g., EC2-05S052P

*add suffix "3" for 3KVDC isolation, *add suffix "4" for 4KVDC isolation,

*add suffix "5" for 5.2KVDC isolation, *add suffix "6" for 6KVDC isolation

2: Character after "-" is Input Voltage: 12=12Vdc, 15=15Vdc, 24=24Vdc


e.g., EC2-12S052P, EC2-15S122P3, EC2-24S152P6.

ADAM TECH


DC-DC Converter EC2-2W Series

2 Watt

1.5KV ~ 6KV Isolated
Single & Dual Output
SIP7



Temperature Derating Graph



Input Specifications

Parameters	Conditions	Min	Typ	Max	Units
Voltage Range	Vo,Io Nom		±10		%
Filter	Capacitor				

Output Specifications

Parameters	Conditions	Min	Typ	Max	Units
Voltage Tolerance	100% full load			±5	%
Short Circuit Protection	Continuous				
Line Regulation	For 1.0% OF Vin		1.2		%
Load Regulation	5V (10% To 100% F.L)		8	15	%
	9V (10% To 100% F.L)		6	10	%
	12V (10% To 100% F.L)		5	10	%
	15V (10% To 100% F.L)		4	10	%
	24V (10% To 100% F.L)		3	10	%
Ripple & Noise	BW=DC To 20MHz		75	150	mVp-p

General Specifications


Parameters	Conditions	Min	Typ	Max	Units
Isolation Resistance	500Vdc	1000			MΩ
Isolation Capacitance	Input-output, 100KHz/0.1V		20		pF
Switching Frequency	Full load, nominal input @5V Vin		215		KHz
	Full load, nominal input @other Vin		250		KHz
Operating Temperature		-40		+105	°C
Storage Temperature		-55		+125	°C
Humidity	Non Condensing			95	%
Cooling	Free air Convection				
Case Material	DAP				
MTBF	MIL-HDBK-217F@25°C	3,500,000			Hours
Weight			2.1		g
Dimensions			19.5x6.0x10.0		mm

Part Number

EC2 - XX X XX X X X
A B C D E F G

A: Series
B: Input Voltage
C: Single (S) / Dual Output (D)
D: Output Voltage
E: Output Power
F: Protection (P)
G: Isolation Voltage


Tolerance Envelope Graph



Electromagnetic Compatibility (EMC)


EMI	CE	CISPR32/EN55032 CLASS B (see Fig. 1 for recommended circuit)
	RE	CISPR32/EN55032 CLASS B (see Fig. 1 for recommended circuit)
EMS	ESD	IEC/EN61000-4-2 Air ±8kV , Contact ±4kV perf. Criteria B

Packaging



Size (mm)			
A	B	C	D
9.5	16.5	522	5.0

Recommended Test Circuit



Vin	Cin	Single Vout	Cout	Dual Vout	Cout
5Vdc	4.7 μ F/25V	5Vdc	10 μ F/16V	$\pm$ 5Vdc	$\pm$ 4.7 μ F/16V
12Vdc	2.2 μ F/25V	9Vdc	2.2 μ F/16V	$\pm$ 9Vdc	$\pm$ 1 μ F/16V
15Vdc	2.2 μ F/25V	12Vdc	2.2 μ F/25V	$\pm$ 12Vdc	$\pm$ 1 μ F/25V
24Vdc	1 μ F/50V	15Vdc	1 μ F/25V	$\pm$ 15Vdc	$\pm$ 1 μ F/25V
--	--	24Vdc	1 μ F/50V	$\pm$ 24Vdc	$\pm$ 1 μ F/50V

EMC (CLASS B) Compliance Circuit





Fig.1

EMC Recommended Circuit Value Table

EMI	C1	4.7 μ F /50V
	C2	4.7 μ F /50V
	CY	1nF/4kV
	C3	Recommended Test Circuit
	L	6.8 μ H

Markings and Dimensions



UNIT: mm unless otherwise specified, all tolerances are ± 0.25

PIN Connection

PIN	1	2	5	6	7
Single	+Vin	-Vin	-Vout	No Pin	+Vout
Dual	+Vin	-Vin	-Vout	Com	+Vout

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EC2-05D052P3](#)