

## SmartPro UPS, Lithium Battery Backup - 120V 3kVA Line Interactive, 2U, Sine Wave, LCD

MODEL NUMBER: **SMART3000RM2UL**



3kVA UPS system with LiFePO4 battery protects equipment against damage and data loss due to brownouts, spikes and surges.

### Features

**Reliable LiFePO4 Battery Backup Offers Longer Life and Less Weight than Lead Acid Battery** This Tripp Lite SmartPro® UPS system features a state-of-the-art lithium iron phosphate (LiFePO4) internal battery with longer life, more cycles and faster recharge. It more than doubles the service life of an equivalent lead acid battery, and offers up to three times more charge/discharge cycles. It recharges to 100-percent capacity in less than two hours, making the lithium UPS system an ideal backup in case of power outage. The LiFePO4 battery weighs 60-percent less than an equivalent lead acid battery, which reduces the overall UPS weight.

**120-Volt Battery Backup Keeps Equipment Operating Through Short Power Failures** The SMART3000RM2UL provides up to 9.5 minutes (half load) and 3.5 minutes (full load) of battery backup, as well as AC power protection, for critical server, network and telecom equipment. In case of a prolonged blackout, the single-phase UPS system gives you enough time to save important data and perform an orderly system shutdown. With a 2250W capacity (3000VA), the line-interactive UPS system with automatic voltage regulation (AVR) maintains regulated 120V nominal output over an input range of 83V-145V without using battery power.

**Protect Your Mission-Critical Rack Equipment** Plug your equipment into the eight NEMA 5-15/20R and one NEMA L5-30R outlets. Two 5-15/20R outlets are switchable, allowing you to power connected equipment on and off remotely to reset or reboot connected equipment or to shed less significant loads to extend battery runtime for more critical equipment. All nine outlets are protected by 570-joule network-grade surge protection to fight off damaging power surges and spikes.

**High Efficiency Operation Helps the Environment and Your Cash Flow** Operating with a high 98% line-mode efficiency, this 3kVA UPS system can save BTU heat output and energy costs.

**Advanced Communications Ports Connect to Any Workstation or Server** USB and DB9 ports (cables are included) enable data-saving unattended shutdown when used with Tripp Lite's free downloadable PowerAlert® software. Capabilities include monitoring of equipment load level, self-test data and utility power conditions. The Emergency Power Off (EPO) interface offers options for instantaneous power-off of the UPS system and connected equipment in case of fire or other facility emergency. The SMART3000RM2UL is compatible with Tripp Lite network management cards, such as WEBCARDLX, for detailed monitoring of UPS and site power conditions.

**Multi-Function LCD and Audible Alarms Keep You Informed** The front-panel LCD information and configuration screen displays detailed UPS and site power status and operating data, as well as input and output voltage, operating mode, alarm function and additional options. An alarm sounds to warn you of power failure, low battery, overload, UPS fault and remote shutdown conditions.

**Versatile Installation Options** Hardware is included for mounting the Tripp Lite SmartPro UPS system in 2U of space in an EIA-standard 19-inch 4-post rack. Use the optional 2POSTRMKITWM for 2-post rack mounting or wall mounting. Use the optional 2-9USTAND for mounting in an upright tower position. A 10-

### Highlights

- Provides 3kVA/2.25kW capacity power protection for critical network components
- LiFePO4 battery backup lasts longer and weighs less than equivalent lead acid battery
- One NEMA L5-30R and 8 NEMA 5-15/20R outlets deliver power to rack equipment
- 570-joule surge protection shields connected devices from damaging surges and spikes
- High 98% line mode efficiency saves BTU heat output and reduces operating costs
- To enable the Auto Probe feature, this product requires LX firmware update 15.5.2 or later to be installed

### Applications

- Deliver regulated sine wave output to connected equipment in a network closet or small-business network
- Protect point-of-sale and VoIP networks against power surges and spikes
- Keep your server room operational during short power failures and allow time for safe shutdowns during longer blackouts

### Package Includes

- SMART3000RM2UL SmartPro UPS, Lithium Battery Backup
- USB cable



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

ft. (3.05 m) power cord with NEMA L5-30P plug connects the SMART3000RM2UL to a compatible AC power source.

**5-Year Warranty and \$250K Ultimate Lifetime Insurance** The SMART3000RM2UL comes with a 5-year warranty and \$250,000 of Ultimate Lifetime Insurance for any connected components damaged by a power surge (U.S., Canada and Puerto Rico only).

- DB9 cable
- EPO cable
- Rack-mounting hardware
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332207159
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	24A (120V)
Nominal Input Voltage(s) Supported	110V AC; 115V AC; 120V AC
UPS Input Connection Type	L5-30P
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	30A 120V
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	3000
Output kVA Capacity (kVA)	3.0
Output Watt Capacity (Watts)	2250
Output kW Capacity (kW)	2.25
Power Factor	0.75
Nominal Voltage Details	120v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-14%, +6%
Output Voltage Regulation (Battery Mode)	+/- 5%
Load Management Receptacles	Two switchable single-outlet load banks
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(8) 5-15/20R; (1) L5-30R
Individually Controllable Load Banks	Yes
<b>BATTERY</b>	
Battery Type	Lithium Ion
Full Load Runtime (min.)	3.5 min. (2250w)
Half Load Runtime (min.)	9.5 min. (1125w)
Expandable Runtime	No
DC System Voltage (VDC)	48
Battery Recharge Rate (Included Batteries)	1.7 hours from 10% to 90% (typical, full load discharge)
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 145
Overvoltage Correction	Input voltages between 127 and 145 are reduced by 12%
Undervoltage Correction	Input voltages between 108 and 96 are boosted by 12%
Severe Undervoltage Correction	Input voltages between 83 and 95 are boosted by 24%
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Switches	3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	570
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Cooling Method	Fan
Included Mounting Accessory Description	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="#">2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM</a> ); 2-4 post front rail rackmount ( <a href="#">Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT</a> ); 4 post rackmount short-depth ( <a href="#">4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM</a> ); Tower ( <a href="#">2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND</a> ); Wallmount ( <a href="#">2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM</a> );
Minimum Required Rack Depth (cm)	62.23
Minimum Required Rack Depth (inches)	24.5
Optional Mounting Accessory Notes	Optional ( <a href="#">2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND</a> ); enables upright tower UPS placement; ( <a href="#">2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM</a> ); enables wall-mount and 2-post rackmount installation; ( <a href="#">4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM</a> ); enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); ( <a href="#">Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT</a> ); enables installation in 2 or 4-post racks using front vertical rails only, without rear support
Primary Form Factor	Rackmount
Primary UPS Depth (mm)	494
Primary UPS Height (mm)	87
Primary UPS Width (mm)	440
Rack Height	2U
Shipping Dimensions (hwd / cm)	21.34 x 60.45 x 55.12
Shipping Dimensions (hwd / in.)	8.40 x 23.80 x 21.70
Shipping Weight (kg)	28.98
Shipping Weight (lbs.)	63.90
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	8.71 x 43.99 x 49.43
UPS Power Module Dimensions (hwd, in.)	3.43 x 17.32 x 19.46
UPS Power Module Weight (kg)	22.72
UPS Power Module Weight (lbs.)	50.1
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	189
AC Mode Efficiency Rating (100% Load)	98%
Audible Noise	50.3 dBA maximum, front side 1m



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

COMMUNICATIONS	
Network Management Cards	<a href="http://www.tripplite.com/SNMP-Web-Management-Accessory-Card-SmartPro-SmartOnline-UPS-Systems~SNMPWEBCARD">SNMPWEBCARD</a> <a href="http://www.tripplite.com/Web-Management-Accessory-Card-SmartPro-SmartOnline-UPS-Systems~TLNETCARD">TLNETCARD</a> <a href="http://www.tripplite.com/Web-Management-Accessory-Card~WEBCARDLX">WEBCARDLX</a> <a href="http://www.tripplite.com/Programmable-Relay-I-O-Card~RELAYIOCARD">RELAYIOCARD</a>
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	Available via free download from <a href="http://tripplite.com/poweralert">tripplite.com/poweralert</a>
Communications Cable	USB, DB9 and EPO cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at <a href="http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp+Lite">http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite</a>
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled)
LINE / BATTERY TRANSFER	
Transfer Time	5 milliseconds (AC to battery mode), 1 millisecond (Battery to AC mode)
Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	145
SPECIAL FEATURES	
Grounding Lug	Back panel grounding lug
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (requires WEBCARDLX); Automatic Voltage Regulation (AVR); Remote management; Sine wave output; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
STANDARDS & COMPLIANCE	
UPS Certifications	Meets FCC Part 15 Category A (EMI); ROHS (Restriction of Hazardous Substances); Tested to CSA (Canada); Tested to NOM (Mexico); Tested to UL1778 (USA)
Certification Details	SAFETY STANDARD (U.S.) - UL1778:2014 (5th Ed) R10.17; SAFETY STANDARD (CANADA) - CAN/CSA-C22.2 No. 107.3-14 (3rd Ed) + G11 / FCC/ICES COMPLIANT - CLASS A
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <a href="http://www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SMART3000RM2UL](#)