

SmartPro 230V 5kVA 3.75kW Line-Interactive Sine Wave UPS, 3U, Extended Run, Network Card Options, USB, DB9

MODEL NUMBER: **SMX5000XLRT3U**



Description

5000VA line interactive UPS system for server, network and telecommunications equipment. 5kVA UPS with internal batteries installs in only 3 rack spaces with a depth of only 635mm / 25 inches. High 98% line-power efficiency rating reduces energy consumption and BTU heat output. Expandable battery runtime with optional BP48V24-2U (limit 1), BP48V60RT-3U (multi-pack compatible) and BP48V27-2US (multi-pack compatible) external battery packs. Uninterruptible Power Supply (UPS) switches to battery-derived AC output during power failures and extreme voltage variations. Line interactive Automatic Voltage Regulation (AVR) offers voltage boost during brownouts and voltage reduction during overvoltage conditions to maintain regulated 230v output over an input range of 170-282V. Supports hardwire input. Includes C19 and C13 output receptacles. Network-grade AC surge and noise suppression. Network management interfaces support communications via USB, DB9 serial and slot for network management card options. Supports simultaneous detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces at once. PowerAlert UPS monitoring software is available via free download. Emergency Power Off (EPO) interface. 3-stage metered current monitoring and battery charge status LEDs. Utility power and voltage regulation LEDs. Audible alarm. Self-test. 4-post rackmount installation accessories included; 2-9USTAND tower kit and 2POSTRMKITHD two post rack mounting accessories available. Field-replaceable, hot-swappable internal batteries and external battery packs.

Features

- 5000VA/3750 watt max. output power capacity compatible with International 230V input voltage
- 3U rack/tower UPS installs in standard 19 inch rack enclosures with an installed depth of only 635mm / 25in
- Protects sensitive networking equipment from blackouts, voltage fluctuations and transient surges
- Line Interactive Automatic Voltage Regulation (AVR) corrects 230V nominal input from 170 to 282VAC

Highlights

- 5kVA / 5000VA line interactive 3U rack/tower UPS; Sine wave output
- 230V nominal output during brownouts to 170V and overvoltages to 282V
- Add optional WEBCARDLX with latest version of PADM20 for enhanced remote management
- 3U all-in-one chassis; 98% efficiency
- Hardwire input; 8 C13 & 3 C19 outlets

Package Includes

- SMX5000XLRT3U UPS system
- USB, DB9 and EPO Cabling
- Mounting hardware for 4 post rackmount installation
- Warranty information
- Instruction manual



to usable 230V levels without consuming battery power

- AVR circuits boost undervoltages from 170 to 199V by 12% and reduce overvoltages from 245 to 282V by 12%
- Network interfaces support simultaneous communications via USB, DB9 serial or contact closure and slot for network management card options
- Compatible with Tripp Lite UPS management card options TLNETCARD, WEBCARDLX and SNMPWEBCARD
- Optional WEBCARDLX (sold separately) with the latest version of PowerAlert Device Manager firmware (PADM20) provides enhanced remote management capabilities
- PADM20 and PowerAlert Element Manager (PAEM) form a powerful tool for expanding maintenance functions in large installations, including firmware update checks and backup and restoration of device configurations
- USB & Serial ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- Built-in Emergency Power Off (EPO) interface with cable
- Sine wave output in AC and battery mode
- Expandable runtime with optional BP48V24-2U (limit 1), BP48V60RT-3U (multi-pack compatible) and BP48V27-2US (multi-pack compatible) external battery packs
- Half/full load runtime of 20/8.5 minutes with internal batteries
- Intelligent battery management system extends battery life
- Includes 11 output receptacles (3 C19/8 C13)
- Hardwire input AC connection
- 3 stage metered LEDs offer current monitoring and battery charge level
- Mains power and voltage regulation LEDs offer at-a-glance power status information
- Front panel switches support self-test and alarm cancel functions
- Included adjustable mounting rails support installation in 4 post 19 inch racks
- Supports upright tower placement with optional 2-9USTAND accessory
- CE, GOST, SASO listed

Specifications

OVERVIEW	
UPC Code	037332121455
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	27A
Nominal Input Voltage(s) Supported	230V AC



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPS Input Connection Type	Hardwire
UPS Input Connection Description	Hardwire input supports International 230V input (L, N, PE)
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	5000
Output kVA Capacity (kVA)	5
Output Watt Capacity (Watts)	3750
Output kW Capacity (kW)	3.75
Power Factor	0.75
Nominal Voltage Details	230v nominal inverter output voltage
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Automatic frequency selection
Output Voltage Regulation (Line Mode)	-17%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
Included Output Power Cables	Includes 3 C13 to C14 output power cables
Output Circuit Breakers	15A (x3) breaker supports 1 C19 outlet each, 10A (x2) breaker supports 4 C13 outlets each
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	220V; 230V; 240V
Output Receptacles	(8) C13; (3) C19
Individually Controllable Load Banks	No
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Full Load Runtime (min.)	8.5 min. (3750w)
Half Load Runtime (min.)	20 min. (1875w)
Expandable Battery Runtime	Extended runtime supported via optional external battery packs
Expandable Runtime	Yes
External Battery Pack Compatibility	BP48V24-2U (limit 1); BP48V60RT-3U (multi-pack compatible); BP48V27-2US (multi-pack compatible)
DC System Voltage (VDC)	48

4 / 6



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Primary UPS Height (mm)	132
Primary UPS Width (mm)	445
Rack Height	3U
Shipping Dimensions (hwd / cm)	28.58 x 57.20 x 80.01
Shipping Dimensions (hwd / in.)	11.25 x 22.52 x 31.50
Shipping Weight (kg)	82.55
Shipping Weight (lbs.)	182.00
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	13.21 x 44.45 x 63.50
UPS Power Module Dimensions (hwd, in.)	5.2 x 17.5 x 25
UPS Power Module Weight (kg)	64.86
UPS Power Module Weight (lbs.)	143
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	271
Battery Mode BTU / Hr. (Full Load)	1267
AC Mode Efficiency Rating (100% Load)	98%
Audible Noise	45 dBA maximum, front side 1m
COMMUNICATIONS	
Network Management Cards	 SNMPWEBCARD TLNETCARD WEBCARDLX
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at https://www.tripplite.com/poweralert
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB
LINE / BATTERY TRANSFER	
Transfer Time	7 ms (AC to Battery); 1 ms (Battery to AC) typical



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Low Voltage Transfer to Battery Power (Setpoint)	170
High Voltage Transfer to Battery Power (Setpoint)	282
SPECIAL FEATURES	
Grounding Lug	Back panel grounding lug
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring (requires WEBCARDLX); Automatic Voltage Regulation (AVR); Expandable battery backup; Hot swappable batteries; Remote management; Sine wave output; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
STANDARDS & COMPLIANCE	
UPS Certifications	CE
Certification Details	Class A (EMI)
WARRANTY	
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SMX5000XLRT3U](#)