





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/12/05	
A		UPDATED DIM.	11/15/16	HR/MY



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:
Insulator: Nylon 66, rated UL 94V-2
Insulator color: Natural
Contacts: Brass

Plating:
Tin over Copper underplate overall

Electrical:
Voltage rating: 250 V AC, DC
Current rating: 5 A AC, DC
Insulation resistance: 1000Mohms min.
Dielectric withstanding voltage: 1500 VAC for 1 minute
Temperature Rating:

Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant.



Positions: 2 thru 20

A = .156 [3.96] x No. of Positions

B = .156 [3.96] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	4/12/05
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.156 [3.96] POWER HEADER
STRAIGHT, WITH LOCK POLARIZER

SIZE X	PART NO. LHB-XX-SA1	REV. A
REF: S00016T	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[LHB-02-SA1](#) [LHB-03-SA1](#) [LHB-04-SA1](#) [LHB-05-SA1](#) [LHB-08-SA1](#) [LHB-10-SA1](#) [LHB-09-SA1](#) [LHB-07-SA1](#) [LHB-06-SA1](#)