

SmartOnline 208/240V 10kVA On-Line UPS – Double Conversion, 9kW, 6U, Network Card Option, TAA Compliant

MODEL NUMBER: **SU10000RT3UTAA**



10kVA UPS protects connected equipment against damage and downtime due to blackouts, brownouts, surges and line noise.

Features

Protects Mission-Critical Rack-Mounted Equipment against Damage, Downtime and Data Loss This TAA-compliant UPS system protects connected equipment against damage, downtime and data loss due to power outages, voltage fluctuations and transient surges. Featuring a 9000W capacity, high 0.9 power factor, true on-line operation with pure sine wave output and zero transfer time to battery, the SmartOnline® SU10000RT3UTAA provides the highest level of battery backup and AC power protection for critical server, network and telecom equipment.

Reliable, Expandable Battery Backup UPS battery backup keeps connected equipment operational through short power failures, and provides time to save data and perform an orderly system shutdown in case of a prolonged blackout. The 3U external battery provides 12.5 minutes of support at half load and 4.3 minutes at full load. During normal operation, incoming utility power keeps the battery fully charged so backup power will be available when needed. For mission-critical applications demanding continuous uptime, the 10kVA UPS can provide expandable runtime with optional external battery packs, such as Tripp Lite's field-replaceable, hot-swappable BP240V10RT3UTAA (sold separately). A battery-independent restart ensures automatic UPS power-up after lengthy power outages, even with expired batteries.

Easily Hot-Swappable with No Expensive Service Calls or Downtime Needed With its detachable PDU, the SU10000RT3UTAA is easily hot-swappable by a user of any skill set. In bypass mode, the PDU passes power to equipment without the use of the power and battery modules, allowing them to be removed while keeping your application in operation. When making repairs or replacing a battery, no lengthy service calls or downtime are necessary.

Economy Mode Helps the Environment and Your Cash Flow Operating with a high 96% efficiency in optional economy mode, this TAA-compliant UPS system significantly reduces BTU heat output and operating energy costs.

Intuitive Front-Panel Interface for Convenient UPS Operation and Monitoring Front-panel LEDs indicate line power, online mode, economy/bypass mode, on-battery, charger and AC output status at a glance. The LCD readout with scroll controls supports visual monitoring of a variety of control options to support advanced UPS settings and configurations. The panel rotates for comfortable viewing in rack-mount or tower configuration.

Optional WEBCARDLX Network Interface Offers 24/7 Access An accessory slot accommodates the optional Java-free HTML5-based WEBCARDLX interface (sold separately), which enables full remote access for site power and UPS status monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network. Automated alerts help prevent accidental overloads, power loss and downtime.

Highlights

- Zero transfer time between AC power and battery for uninterrupted operation
- PDU keeps essential equipment powered during hot-swap battery replacement or repair
- Interactive LED/LCD interface delivers detailed UPS operation and monitoring options
- Optional external batteries provide additional runtime for essential applications
- Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Delivering perfectly regulated sine wave output to mission-critical equipment
- Protecting connected components from dangerous surges, spikes and line noise
- Keeping equipment operational through short power failures
- Allowing time to save data and safely shut down components in case of a prolonged blackout

Package Includes

- SU10KRT3UPMTAA hot-swappable UPS power module
- SUPDMB710TAA detachable PDU w/maintenance bypass switch
- BP240V10RT3UTAA external battery pack
- USB cable



Advanced Communications Ports USB and DB9 ports (cables are included) enable data-saving unattended shutdown of connected systems when used with Tripp Lite's free downloadable PowerAlert® software. Capabilities include detailed monitoring of load levels, self-test data and utility power conditions.

Versatile Installation Options Hardware is included for mounting the 10kVA UPS system in 6U of space in an EIA-standard 19-inch 4-post rack. Use the optional 2POSTRMKITHD (sold separately) for 2-post rack mounting or the included 2-9USTAND for mounting in an upright tower position.

TAA-Compliant UPS for GSA Schedule Purchases The SU10000RT3UTAA is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

2-Year Warranty, \$250K Ultimate Lifetime Insurance and Environmentally Responsible Design The SU10000RT3UTAA comes with a 2-year warranty and \$250,000 of Ultimate Lifetime Insurance for any connected components damaged by a power surge (U.S., Canada and Puerto Rico only). It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

- DB9 cable
- EPO cable
- Rack-mounting hardware
- 2-9USTAND tower stand kit
- Owner's manual

Specifications

| OVERVIEW | |
|---------------------------------------|--|
| UPC Code | 037332223753 |
| UPS Type | On-Line |
| INPUT | |
| Rated input current (Maximum Load) | 56.1A (200V), 54A (208V), 51A (220V), 48.8A (230V), 46.8A (240V) |
| Nominal Input Voltage(s) Supported | 200V AC; 208V AC; 240V AC |
| UPS Input Connection Type | Hardwire |
| UPS Input Connection Description | 3 wire single phase input (L1, L2, G) |
| Recommended Electrical Service | 60A |
| Input Phase | Single-Phase |
| OUTPUT | |
| Output Volt Amp Capacity (VA) | 10000 |
| Output kVA Capacity (kVA) | 10 |
| Output Watt Capacity (Watts) | 9000 |
| Output kW Capacity (kW) | 9 |
| Output Capacity Details | Supports up to 105% load continuously in double conversion mode, 106 to 125% for 1 minute, 126% to 150% for 30 seconds; Loads over 150% trigger immediate bypass mode operation to support loads directly from mains power; Double conversion mode is automatically restored as load levels are reduced to 95% or less |
| Power Factor | 0.9 |
| Crest Factor | 3:1 |
| Nominal Voltage Details | Voltage selection via front panel LCD interface |
| Frequency Compatibility | 50 / 60 Hz; Supports 50 to 60 Hz and 60 to 50 Hz conversion |
| Frequency Compatibility Details | Output frequency matches input nominal on startup; Frequency conversion mode enables conversion of 60Hz to 50Hz or 50Hz to 60Hz (No de-rating); Output frequency regulation +/- 0.05Hz (free running) |
| Output Voltage Regulation (Line Mode) | +/- 2% |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|---|--|
| Output Voltage Regulation (Economy Line Mode) | +/- 10% |
| Output Voltage Regulation (Battery Mode) | +/- 2% |
| Output Circuit Breakers | 20A double-pole (x2) protects 2 L6-20R outlets each, 30A double-pole (x2) protects 1 L6-30R outlet each |
| Output AC Waveform (AC Mode) | Pure Sine wave |
| Output AC Waveform (Battery Mode) | Pure Sine wave |
| Nominal Output Voltage(s) Supported | 200V; 208V; 240V |
| Output Receptacles | (4) L6-20R; (2) L6-30R |
| Individually Controllable Load Banks | No |
| BATTERY | |
| Battery Type | Valve Regulated Lead Acid (VRLA) |
| Full Load Runtime (min.) | 4.3 min. (9000w) |
| Half Load Runtime (min.) | 12.5 min. (4500w) |
| Expandable Battery Runtime | Supports extended runtime with optional external battery packs |
| Expandable Runtime | Yes |
| External Battery Pack Compatibility | BP240V10RT3UTAA ; BP240V787C-1PH |
| DC System Voltage (VDC) | 240 |
| Battery Recharge Rate (Included Batteries) | Less than 6 hours from 10% to 90% (typical, full load discharge) |
| Battery Replacement Description | Hot-swappable, user replaceable external battery packs |
| VOLTAGE REGULATION | |
| Voltage Regulation Description | 2% output voltage regulation in standard online, double-conversion mode |
| Overvoltage Correction | Corrects overvoltages up to 300V |
| Undervoltage Correction | Corrects undervoltages as low as 100V |
| USER INTERFACE, ALERTS & CONTROLS | |
| Front Panel LCD Display | Selectable LCD display with scroll and selection buttons enables UPS control and detailed monitoring options; LED/LCD panel rotates for viewing in rack/tower formats; LCD Display supports ENGLISH, FRENCH, GERMAN, ITALIAN, SPANISH and PORTUGUESE (see manual) |
| Switches | 2 Switches control off/on power status and alarm-cancel/self-test operation; 2 additional switches support set and execute scrolling LCD functions; bundled PDU includes bypass switch to enable hot-swap UPS power module replacement |
| Alarm Cancel Operation | Alarm cancel switch |
| Audible Alarm | Unique audible alarms for all major UPS, environmental and power conditions (see manual) |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|---|---|
| LED Indicators | 6 LEDs indicate line power, online mode, economy/bypass mode, on-battery, charger and AC output status; LCD screen offers additional information and control options |
| SURGE / NOISE SUPPRESSION | |
| UPS AC Suppression Joule Rating | 2565 |
| UPS AC Suppression Response Time | Instantaneous |
| EMI / RFI AC Noise Suppression | Yes |
| PHYSICAL | |
| Cooling Method | Fan |
| Included Battery Pack Dimensions (hwd / in.) | 5.25 x 17.5 x 25 |
| Included Battery Pack Weight (lbs.) | 159 |
| Included Battery Pack Weight (kg) | 72.12 |
| Included Mounting Accessory Description | 2 sets of adjustable 4 post rack rails included; 2-9USTAND tower kit included |
| Installation Form Factors Supported with Included Accessories | 4 post 19 inch rackmount |
| Installation Form Factors Supported with Optional Accessories | 2 post rackmount (2POSTRMKITHD) |
| Maximum Device Depth (cm) | 83.82 |
| Maximum Device Depth (in.) | 33 |
| Maximum Device Depth (mm) | 838 |
| Minimum Required Rack Depth (cm) | 96.52 |
| Minimum Required Rack Depth (inches) | 38 |
| Optional Mounting Accessory Notes | 2 sets of 2POSTRMKITHD required for 2 post rackmount installation of separate power module and battery pack |
| Primary Form Factor | Rackmount |
| Primary UPS Depth (mm) | 656 |
| Primary UPS Height (mm) | 131 |
| Primary UPS Width (mm) | 445 |
| Rack Height | 6U |
| Shipping Dimensions (hwd / cm) | 78.74 x 66.04 x 104.14 |
| Shipping Dimensions (hwd / in.) | 31.00 x 26.00 x 41.00 |
| Shipping Weight (kg) | 136.08 |
| Shipping Weight (lbs.) | 300.00 |
| Unit Dimension Details | Includes 3U UPS/power module, 3U external battery pack plus SUPDMB710TAA PDU with bypass; MAXIMUM DEVICE DEPTH specification refers to the whole UPS installed depth with bypass PDU installed |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|---|--|
| UPS Housing Material | Steel |
| UPS Power Module Dimensions (hwd, cm) | 13.06 x 44.45 x 65.58 |
| UPS Power Module Dimensions (hwd, in.) | 5.14 x 17.5 x 25.82 |
| UPS Power Module Weight (kg) | 19.50 |
| UPS Power Module Weight (lbs.) | 43 |
| ENVIRONMENTAL | |
| Operating Temperature Range | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius |
| Storage Temperature Range | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius |
| Relative Humidity | 0 to 95%, non-condensing |
| AC Mode BTU / Hr. (Full Load) | 3415 |
| AC Economy Mode BTU / Hr. (Full Load) | 1280 |
| Battery Mode BTU / Hr. (Full Load) | 4593 |
| AC Mode Efficiency Rating (100% Load) | 91% |
| AC Economy Mode Efficiency Rating (100% Load) | 96% |
| Operating Elevation (ft.) | 0-3000m (0 to 10,000 ft.) |
| Audible Noise | 60 dBA at front side 1 meter |
| Operating Elevation (m) | 0-3000 m |
| COMMUNICATIONS | |
| Network Management Cards | SNMPWEBCARD and TLNETCARD and WEBCARDLX and MODBUSCARD and RELAYIOCARD |
| Network Monitoring Port Description | Additional contact closure support with optional RELAYIOCARD and RELAYIOMINI interface cards. RELAYIOMINI installation requires removal of panel containing USB ports |
| PowerAlert Software | For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at https://www.tripplite.com/poweralert |
| Communications Cable | USB, DB9 serial and EPO cables included |
| WatchDog Compatibility | Supports Watchdog application, OS and hard-reboot restart options for remote applications |
| Communications Interface | DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled) |
| LINE / BATTERY TRANSFER | |
| Transfer Time | No transfer time (0 ms.) in online, double-conversion mode |
| Transfer Time (Economy Mode) | 8 ms. typical power failure response in optional economy mode |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|---|---|
| Low Voltage Transfer to Battery Power (Setpoint) | 100V |
| High Voltage Transfer to Battery Power (Setpoint) | 300V |
| SPECIAL FEATURES | |
| Cold Start (Startup in Battery Mode During a Power Failure) | Cold-start operation supported |
| Economy Mode Operation | Optional economy mode enables high efficiency bypass operation with a maximum output voltage variation of +/- 10%. Double conversion mode is automatically restored as mains voltage varies beyond +/-10% with less than 1 millisecond transfer time between modes. |
| High Availability UPS Features | Auto Probe Monitoring (requires WEBCARDLX); Automatic inverter bypass; Expandable battery backup; Hot swappable UPS power module; Hot swappable batteries; Manual bypass switch; On-Line/Double-Conversion; Remote management; Sine wave output; Surge/noise protection; Zero transfer time |
| Green Energy-Saving Features | High efficiency economy mode operation; Schedulable daily hours of economy mode operation |
| STANDARDS & COMPLIANCE | |
| UPS Certifications | Meets FCC Part 15 Category A (EMI); TAA Compliant; Tested to CSA (Canada); Tested to NOM (Mexico); Tested to UL1778 (USA) |
| Certification Details | IEC 61000-4-5 1995 B Surge Immunity |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$250,000 Ultimate Lifetime Insurance |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SU10000RT3UTAA](#)