





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/12/05	
A		REDRAWN	03/14/12	
B		UPDATE SPEC.	6/12/20	AY/RC



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 250 VAC/DC

Current rating: 5A AC/DC

Insulation resistance: 1,000 Mohms min

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20

A = .156 [3.96] x No. of Positions

B = .156 [3.96] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS			TITLE		.156 [3.96] POWER HEADER STRAIGHT, WITHOUT LOCK POLARIZER	
DRAWN		SS	DATE			
CHECKED			4/12/05			
APPROVED						
			SIZE	PART NO.	REV.	
			X	LHB-XX-SA2	B	
			REF:	S00016T	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[LHB-06-SA2](#) [LHB-09-SA2](#) [LHB-10-SA2](#) [LHB-04-SA2](#) [LHB-07-SA2](#) [LHB-03-SA2](#) [LHB-08-SA2](#) [LHB-05-SA2](#) [LHB-02-SA2](#)