





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/12/05	
A		UPDATED DIM.	3/20/15	HR/L



SPECIFICATIONS:

Material: Insulator: Nylon, rated UL 94V-2
Insulator color: White
Contacts: Brass
Plating: Tin over Copper underplate overall
Electrical: Operating voltage: 250 VAC/DC max
Current rating: AC/DC 5 Amps max
Contact resistance: 20 mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,500 VAC for 1 minute
Temperature Rating: Operating temperature: -25°C to +85°C
Environmental: Lead free, RoHS compliant

Positions: 2 thru 12
A = .156 [3.96] x No. of Positions + .008 [0.20]
B = .156 [3.96] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES				Holes			
.X	± .10	ØX	± .10	TITLE			
.XX	± .020	ØXX	± .015	.156 [3.96] POWER HEADER			
.XXX	± .015	ØXXX	± .010	RIGHT ANGLE, WITH REAR LOCK			
APPROVALS				DATE			
DRAWN				SS			
CHECKED				4/12/05			
APPROVED				X			
SIZE				PART NO.			
REF: S00016T				LHC-XX-TRA			
SCALE: NTS				REV. A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[LHC-02-TRA](#) [LHC-03-TRA](#) [LHC-20-TRA](#)