

## SmartOnline SUT Series 3-Phase 208/120V 220/127V 20kVA 20kW On-Line Double-Conversion UPS, Tower, Extended Run, SNMP Option

MODEL NUMBER: **SUT20K**



3-phase UPS system protects mission-critical network equipment against downtime and data loss in data center, telecom, medical, manufacturing and financial environments.

### Description

The SUT20K SmartOnline® SUT Series 3-Phase 208/120V 220/127V 20kVA 20kW On-Line Double-Conversion UPS provides complete protection against power interruptions and fluctuations that can contribute to equipment failures and data loss. It's recommended for critical data center, telecommunications, computer network, manufacturing and financial applications.

The Voltage and Frequency Independent (VFI) design allows continuous operation at either 50 or 60 Hz. Zero transfer time from online to battery mode ensures no disruption to attached equipment loads.

Offering an efficiency of 94% during normal operation and 98% in economy mode, the SUT20K reduces energy losses for cost-saving operation. Automatic bypass keeps connected equipment powered, even during overloads and many potential UPS fault conditions.

IGBT inverter technology produces output power with less than 2% total harmonic distortion (THDi) to keep connected equipment functioning at its peak. A 3:1 crest factor safely supports a variety of loads, even those with wildly fluctuating power demands.

Managing the SUT20K is simplified through the multi-language LCD interface, which displays critical operating conditions and diagnostic data, such as battery and load status. Four LEDs indicate AC, bypass, battery and fault modes. A built-in card slot supports optional remote management cards, such as WEBCARDLX, for comprehensive monitoring and control over a network.

### Features

**VFI True On-Line Double-Conversion 3-Phase UPS System** Provides fully regulated sine wave AC output for critical data center, telecom, computer network, light industrial and financial applications +/-1% output voltage regulation in online and battery modes High 1.0 unity power factor with 20kVA/20kW output capacity offers higher capacity than competing 0.8 and 0.9 PF designs Supports 208/120V or 220/127V at 50/60 Hz Wide input voltage window (125–253V) minimizes battery use and prolongs battery life

**Reliable Battery Backup with Expandable Runtime** Supports half load for 15.4 min. and full load for 5.2 min. with standard internal batteries Optional BP288VEBP external battery packs provide additional runtime Sine wave output with zero transfer time compatible with all equipment types

**IGBT Inverter Technology** Produces output power with <2% THD to keep connected equipment functioning at its peak Low <4% full load THDi input rating and advanced IGBT rectifier enables 1:1 generator sizing, eliminating costly oversizing requirements for generators, breakers and cables

**Paralleling Capability** Connect up to 4 units in parallel configuration for N+N fault tolerant redundancy or increased power capacity up to 80kVA

### Highlights

- On-line double-conversion topology, VFI operation
- 1.0 unity power factor supports 20kVA/20kW capacity
- Up to 98% economy-mode efficiency option saves energy
- Internal batteries included with external battery pack options
- Parallel up to 4 units for increased capacity or for N+N redundancy

### Package Includes

- SUT20K SmartOnline SUT Series 3-Phase 20kVA 20kW On-Line Double-Conversion UPS
- RS-232 (DB9) cable
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

**Automatic Bypass**Maintains output power to connected equipment during a variety of potential UPS fault conditions

**Economy Model**Increases operating efficiency levels as high as 98% when input line conditions are favorable

**Remote Management Card Options**Compatible with Tripp Lite UPS card accessories, such as WEBCARDLX, that enable comprehensive monitoring and control over a network

**Communications Ports**DB9 (RS-232) port enables data-saving unattended shutdown when used with PowerAlert® software (free download at [www.tripplite.com/poweralert](http://www.tripplite.com/poweralert))EPO port supports Emergency Power Off shutdown

**Standard Compliance**Tested to UL 1778 5th Edition, CSA C22.2 No. 107.3, NOM, FCC Part 15 Class A (EMC), GB17626-2/IEC 61000-4-2 (Electrostatic Discharge) Level 4, GB17626-3 (Radio-Frequency Electromagnetic Fields) Level 3, GB17626-4 (Fast Transient/Burst) Level 4, GB17626-5/IEC 61000-4-5 (Surge) Level 4 and RoHS

## Specifications

OVERVIEW	
UPC Code	037332186690
UPS Type	On-Line
INPUT	
Rated input current (Maximum Load)	67.5A (120/208V); 63.5A (120/208V)
Nominal Input Voltage(s) Supported	120/208V 3-PH Wye; 127/220V 3-PH Wye
Nominal Input Voltage Description	3-Phase Wye, 4 wire (L1, L2, L3, N, G)
UPS Input Connection Type	Hardwire
Input Circuit Breakers	75A 3 pole 240V breaker
Input Phase	3-Phase
Power Factor (Input)	>0.99 (maximum resistive load)
THDi	<4% (maximum resistive load)
OUTPUT	
Output Volt Amp Capacity (VA)	20000
Output kVA Capacity (kVA)	20
Output Watt Capacity (Watts)	20000
Output kW Capacity (kW)	20
Output Capacity Details	Supports parallel connection of up to 4 SUT20K systems for 80kVA max capacity or N+N fault tolerance redundancy; Supports up to 100% load continuously, 125% load for up to 10 minutes, 149% load for up to 1 minute and over 150% load for up to 0.5 seconds before transferring to bypass mode; Automatic inverter restart is available when the load level recovers to 95% or less after overload-related transfer to bypass
Power Factor	1.0
Crest Factor	3:1
Nominal Voltage Details	Factory default output voltage is 120/208V; Less than 2% THD (full resistive load); Less than 0.1V Max DC Offset; Less than 2° Max Phase Angle Deviation; Less than 1% Max Voltage Unbalance Deviation
Frequency Compatibility	50 / 60 Hz



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Frequency Compatibility Details	Auto-selectable frequency configuration
Output Voltage Regulation (Line Mode)	±1%
Output Voltage Regulation (Economy Line Mode)	±10%
Output Voltage Regulation (Battery Mode)	±1%
Output Circuit Breakers	Electronic AC output protection; Short-circuit protection
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120/208V 3-PH Wye; 127/220V 3-PH Wye
Output Receptacles	Hardwire
Individually Controllable Load Banks	No
<b>BATTERY</b>	
Full Load Runtime (min.)	5.2 minutes (20kW)
Half Load Runtime (min.)	15.4 minutes (10kW)
Expandable Battery Runtime	Supports extended runtime with optional external battery packs
Expandable Runtime	Yes
Expandable Runtime Description	External battery pack wiring is contractor supplied
External Battery Pack Compatibility	&nbsp;<a class="productLink" href="//www.tripplite.com/external-battery-pack-tripp-lite-sut-3-phase-ups-systems-internal-batteries-included~BP288VEBP">BP288VEBP</a>&nbsp;</td></tr><tr><td>DC System Voltage (VDC)</td><td>±144VDC</td></tr><tr><td>Battery Recharge Rate (Included Batteries)</td><td>3.2 hours from 10 to 90%; Battery charge current adjustable from 1 to 20A (5A factory default)</td></tr><tr><td data-cs=2 data-kind=parent><b>VOLTAGE REGULATION</b></td><td data-kind=ghost></td></tr><tr><td>Voltage Regulation Description</td><td>Online, double-conversion power conditioning maintains ±1% output voltage regulation</td></tr><tr><td>Overvoltage Correction</td><td>Maintains continuous operation without using battery power during overvoltages to 253V</td></tr><tr><td>Undervoltage Correction</td><td>Maintains continuous operation without using battery power during brownout/undervoltage conditions to 125V (63% load or less); 166V (100% load)</td></tr><tr><td data-cs=2 data-kind=parent><b>USER INTERFACE, ALERTS & CONTROLS</b></td><td data-kind=ghost></td></tr><tr><td>Front Panel LCD Display</td><td>Front panel LCD with scroll and enter buttons offers display of UPS operating mode, site power and UPS condition monitoring and operating configuration options; LCD also reports alarm conditions, including Short circuit, Inverter fail and Over temperature; Supports English, French, German, Russian, Portuguese, Spanish, Turkish and Polish language options</td></tr><tr><td>Switches</td><td>ON button turns UPS system on; OFF button turns UPS system off; SELECT/ENTER UP and SELECT/ENTER DOWN buttons enable on-screen selection and navigation options; EPO (Emergency Power Off) button turns UPS output off and disables Bypass output</td></tr><tr><td>Alarm Cancel Operation</td><td>Power-fail alarm can be silenced using alarm-cancel switch</td></tr></table></div><div data-bbox=



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Audible Alarm	Alarms signal a variety of operational conditions: low-battery, overload, shutdown, bypass and more
LED Indicators	Four LEDs indicate AC mode (Green), Bypass (Yellow), Battery (Yellow) and Fault (Red) modes
<b>SURGE / NOISE SUPPRESSION</b>	
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	9220
AC Suppression Response Time	Instantaneous
<b>PHYSICAL</b>	
Cooling Method	Fans
Installation Form Factors Supported with Included Accessories	Tower
Primary Form Factor	Tower
Primary UPS Depth (mm)	800
Primary UPS Height (mm)	1,351
Primary UPS Width (mm)	521
Shipping Dimensions (hwd / cm)	156.97 x 71.12 x 99.06
Shipping Dimensions (hwd / in.)	61.80 x 28.00 x 39.00
Shipping Weight (kg)	392.36
Shipping Weight (lbs.)	865.00
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	135.13 x 52.07 x 80.01
UPS Power Module Dimensions (hwd, in.)	53.2 x 20.5 x 31.5
UPS Power Module Weight (kg)	354.26
UPS Power Module Weight (lbs.)	781
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+4 to +104 degrees Fahrenheit / -20 to +40 degrees Celsius
Relative Humidity	Up to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	5250
AC Economy Mode BTU / Hr. (Full Load)	1210
Battery Mode BTU / Hr. (Full Load)	2112.4
AC Mode Efficiency Rating (100% Load)	93%



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

AC Economy Mode Efficiency Rating (100% Load)	98%
Operating Elevation (ft.)	0 to 10,000 feet, but derates 1% per 328 ft above 3280 ft
Audible Noise	Less than 65dBA at 1m front side
Operating Elevation (m)	0 to 3000m, but derates 1% per 100 m above 1000 m
<b>COMMUNICATIONS</b>	
Network Management Cards	&nbsp;<a class="productLink" href="//www.tripplite.com/SNMP-Web-Management-Accessory-Card-SmartPro-SmartOnline-UPS-Systems~SNMPWEBCARD">SNMPWEBCARD</a>&nbsp;; &nbsp;<a class="productLink" href="//www.tripplite.com/Web-Management-Accessory-Card-WEBCARDLX">WEBCARDLX</a>&nbsp;; &nbsp;<a class="productLink" href="//www.tripplite.com/MODBUS-Management-Accessory-Card-UPS-Remote-Monitoring-Control~MODBUSCARD">MODBUSCARD</a>&nbsp;; &nbsp;<a class="productLink" href="//www.tripplite.com/Programmable-Relay-I-O-Card~RELAYIOCARD">RELAYIOCARD</a>&nbsp;;
Network Monitoring Port Description	Additional built-in set of INPUT and OUTPUT contacts support remote notification of Online Mode operation, Battery Mode operation, Bypass Mode operation, Abnormal Bypass Mode Source, Battery Test Failure and Low Battery conditions
PowerAlert Software	Available via free download from <a href="http://www.tripplite.com/poweralert">www.tripplite.com/poweralert</a>
Communications Cable	DB9 cabling included
Communications Interface	DB9 Serial; Slot for SNMP/Web interface
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	Online mode: No transfer time (0 ms.); Economy mode: 6 ms. (AC to battery), 1 ms. (Battery to AC)
Low Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation without using battery power during brownout/undervoltage conditions to 125VAC (under 63% load) / 160VAC (100% load). Below this point, output is maintained utilizing reserve battery power
High Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation without using battery power during overvoltages to 253VAC, reducing output within 1% of nominal. Above this point, output is maintained utilizing reserve battery power
<b>SPECIAL FEATURES</b>	
Grounding Lug	Yes
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Hot swappable batteries; Auto Probe Monitoring (requires WEBCARDLX); Zero transfer time; On-Line/Double-Conversion
Green Energy-Saving Features	High efficiency economy mode operation; Schedulable daily hours of economy mode operation
<b>STANDARDS &amp; COMPLIANCE</b>	
UPS Certifications	Meets FCC Part 15 Category A (EMI); Tested to CSA (Canada); Tested to NOM (Mexico); Tested to UL1778 (USA)
Certification Details	IEC 61000-4-2 (Electrostatic Discharge) Contact: 8KV, Air: 15K; IEC 61000-4-3 (Radio-Frequency Electromagnetic Fields) Field strength 10V/m; IEC 61000-4-4 (Fast Transient/Burst) Power Supply Port: 4KV 2.5KHz; IEC 61000-4-5 (Surges) Input Port: 4KV 1.2/50s Combination Wave
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	1-year limited warranty
Product Warranty Period (International)	2-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty
3-Phase Warranty Statement	<u><a href="#">Tripp Lite 3-Phase UPS Factory Warranty</a></u>

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SUT20K](#)