

6

5

4

3



2

1



Rev	AWO #	Description	Date	Appr
-		RELEASED	8/4/06	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED P.C.B LAYOUT



X	PLATING
0	15 min Gold
1	30 min Gold
2	50 min Gold

SPECIFICATIONS:
Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating:
Gold flash over Nickel underplate on contact area,
Tin over copper underplate on solder tails.
See chart for thickness

Electrical:
Operating voltage: 150 VAC max
Current rating: 1.5 Amps max
Contact resistance: 20mohms max. initial
Insulation resistance: 500 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Temperature Rating:
Operating temperature: -40°C to +125°C
Environmental:
Lead free, RoHS compliant.
Recommended soldering temp: 235°C for 5 sec.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: MODULAR TELEPHONE JACK, R/A
LEDS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLESDIA ± .10 X ± .10 XX ± .020 XXX ± .015				DATE		TITLE	
APPROVALS				DATE		MODULAR TELEPHONE JACK, R/A	
DRAWN				SLS		8/4/06	
CHECKED							
APPROVED							
SIZE				PART NO.		REV.	
X				MTJ-88ARX1-FSM-LD		-	
REF:				SCALE: NTS		SHEET 1 OF 1	

A

B

C

D

A

B

C

D

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MTJ-88ARX1-FSM-LD](#)