

# SmartOnline SV Series 40kVA Small-Frame Modular Scalable 3-Phase On-Line Double-Conversion 208/120V 50/60 Hz UPS System, No SVBM Battery Modules

MODEL NUMBER: **SV40KS2P0B**



3-phase 40kVA UPS system offers network-grade power protection in a highly configurable, modular and scalable small-chassis rack-width frame. External batteries required to operate.

## Description

The SV40KS2P0B SmartOnline® SV Series 40kVA Small-Frame 3-Phase On-Line Double-Conversion UPS System delivers true scalability and offers the highest level of secure, uninterrupted power protection. Featuring a modular, scalable design with high-efficiency voltage and frequency independent (VFI) operation, this on-line UPS system with a high 0.9 power factor is ideal for protecting a variety of critical IT systems.

The SV40KS2P0B includes pre-installed input, bypass and output breakers, as well as a static transfer switch (STS) and two 20kVA SV20PM power modules. Space is included for one additional user-installable SV20PM power module. External  $\pm 120\text{VDC}$  battery options, such as BP240V370 or EBP240VXXX series battery cabinets, are available from Tripp Lite for extended runtime.

The Java-free HTML5-based WEBCARDLX interface enables full remote access for site power and UPS status monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network.

With up to 92% efficiency in standard mode and up to 98% efficiency in optional economy mode, this 40kVA UPS system helps you reduce operating and cooling costs. Automatic and manual bypass options keep connected equipment operational during routine maintenance or critical power module failure. Front-panel display offers full UPS condition and status reporting.

## Features

**40kVA 36kW 3-Phase Small-Chassis UPS System** Supports 208/120V or 220/127V AC 50/60Hz Wye 4-wire plus Earth hardwire input and output wiring  
 Dual hardwire input design enables operation from up to 2 power sources  
 Network-grade sine-wave AC output with 1% output voltage regulation and less than 2% output total harmonic distortion  
 Tested to UL 1778 (U.S.), CSA (Canada) and NOM (Mexico) standards  
 High 0.9 power factor offers higher kW output than lower-rated competing legacy designs  
**Pre-Installed WEBCARDLX Network Interface** Allows full remote access for power monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH  
 Supports 10/100 Mbps auto-sensing for communication with an Ethernet network  
 Optional EnviroSense2 sensors

## Highlights

- Scalable capacity up to 60kVA (or 40kVA with N+1 fault tolerance)
- Economy mode option helps reduce operating and cooling costs
- Pre-installed WEBCARDLX network interface for 24/7 remote access
- DSP/IGBT technology and 1% output voltage regulation
- No internal batteries and requires external batteries to operate.

## Package Includes

- SV40KS2P0B SmartOnline SV Series 40kVA Small-Frame 3-Phase On-Line Double-Conversion UPS System
- Pre-installed WEBCARDLX network interface
- (2) SV20PM 20kVA power modules (shipped separately)
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

(sold separately) enable site monitoring of temperature, humidity and contact-closure status No Java required

**Modular, Scalable Design for Maximum Flexibility** Modular configuration with hot-swappable power and battery modules enables easy, fast maintenance with zero downtime Open slot for 1 additional 20kVA SV20PM power module accommodates increased capacity up to 60kVA (or 40kVA with N+1 fault tolerance) Supports external  $\pm 120$ VDC battery options for extended runtimes

**Optional Economy Mode** Up to 98% efficiency in optional economy mode to lower operating and cooling costs

**Wide Input/Narrow Output Voltage Operating Range** Enables full continuous online operation during brownouts as low as 121V and overvoltages up to 253V Regulates output voltage within 1% of the selected nominal output voltage in on-line double-conversion mode

**Advanced IGBT Inverter with Digital Signal Processor (DSP) Technology** Provides for less than 3% input total harmonic distortion (THDi) to support 1:1 generator sizing and prevent the need to oversize generator systems relative to UPS capacity

**Automatic and Manual Bypass Options** Keep connected equipment operational during routine maintenance or critical power module failure

## Specifications

OVERVIEW	
UPC Code	037332237439
UPS Type	On-Line
INPUT	
Rated input current (Maximum Load)	SV40KS2P0B 40kVA Configuration: 120A; Maximum 60kVA Configuration: 180A; 313.7A maximum inrush current
Nominal Input Voltage(s) Supported	120/208V 3-PH Wye; 127/220V 3-PH Wye
Nominal Input Voltage Description	Set of two hardwire input connections enables 3-Phase Wye, 4 wire (3P, N, E) inputs from two separate power sources
UPS Input Connection Type	Hardwire
Input Circuit Breakers	MAIN and ALTERNATE AC inputs are each protected by 250A 3 pole magnetic breakers
Input Phase	3-Phase
Input Frequency	40 to 70Hz (online mode); 50/60Hz Auto-selectable
Power Factor (Input)	Greater than 0.99 (full load)
THDi	Less than 3% (full linear load)
OUTPUT	
Output Volt Amp Capacity (VA)	40000
Output kVA Capacity (kVA)	40
Output Watt Capacity (Watts)	36000
Output kW Capacity (kW)	36
Output Capacity Details	OVERLOAD CAPABILITY: Supports 105-110% load for 1 hour, 111-125% load for 10 minutes, 126-150% for 1 minute and Over 150% for 200ms before switching to Bypass; Online operation resumes when load is reduced to 100% or less
Power Factor	0.9



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Crest Factor	3:1
Nominal Voltage Details	Output THD full resistive load: <1.5%; Output THD non-linear load: <4%; Max DC offset: $\pm 50\text{mV}$ ; Max Phase angle deviation: $2^\circ$ ; Max Voltage unbalance deviation: 1%; Output short-circuit protection included
Frequency Compatibility	50 / 60 Hz; Supports 50 to 60 Hz and 60 to 50 Hz conversion
Frequency Compatibility Details	Auto-selectable, user adjustable
Output Receptacle Details	Output wiring (3P, N, E)
Output Circuit Breakers	250A 3 pole magnetic breaker
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120/208V 3-PH Wye; 127/220V 3-PH Wye
Output Receptacles	Hardwire
Output Voltage Regulation	ONLINE, FREQUENCY CONVERSION, BATTERY MODE: 208/120, 220/127 $\pm 1\%$ typical (balanced load); $\pm 2\%$ typical (unbalanced load); ECONOMY MODE: 208/120, 220/127 $\pm 15\text{V}$ ; BYPASS MODE: $+15\%$ (default, adjustable to $+10\%$ , $+15\%$ or $+20\%$ ), $-20\%$ (default, adjustable to $-10\%$ , $-20\%$ , $-30\%$ )
Output Frequency Regulation	ONLINE MODE: Output frequency is $\pm 0.05\text{Hz}$ of input frequency when input is within $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting; Output frequency is $\pm 0.05\text{Hz}$ the configured 50/60Hz output setting when input is outside $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting; BATTERY MODE: Output frequency is $\pm 0.1\text{Hz}$ of the configured 50/60Hz output setting; FREQUENCY CONVERTER MODE: Output frequency is $\pm 0.1\text{Hz}$ of the configured 50/60Hz output setting; ECONOMY MODE: Output frequency equals input frequency up to $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting (UPS switches to Online mode if frequency goes outside of this range); BYPASS MODE: Output frequency equals input frequency up to $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting (switches to STANDBY mode if frequency goes outside of this range). *The TRACKING RANGE is factory set to $\pm 4\text{Hz}$ and is user adjustable to $\pm 1\text{Hz}$ , $\pm 2\text{Hz}$ or $\pm 4\text{Hz}$ ; The selected TRACKING RANGE setting controls frequency output tolerances as described above in Online, Economy and Bypass modes
Output Amp Capacity	Output Amp Capacity 111A (208/120V); 105A (220/127V)
Individually Controllable Load Banks	No
Modular Upgrade Options	Includes 2 SV20PM 20kVA power modules; Up to 1 additional SV20PM 20kVA power module can be added for increased capacity or enhanced N+1 redundancy; Add 1 SV20PM for 60kVA capacity (or 40kVA with N+1)
<b>BATTERY</b>	
Full Load Runtime (min.)	No internal batteries and external batteries are required to operate
Half Load Runtime (min.)	No internal batteries and external batteries are required to operate
Expandable Battery Runtime	Extended runtime is available with the addition of $\pm 120\text{VDC}$ external battery packs (sold separately); Recommended 3 pole, 400A, 250VDC breaker rating for external battery system
Expandable Runtime	Yes
Expandable Runtime Description	External battery pack wiring is contractor supplied

4 / 6



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

AC Suppression Response Time	Instantaneous
<b>PHYSICAL</b>	
Cooling Method	Fans
Installation Form Factors Supported with Included Accessories	Tower
Primary Form Factor	Tower
Primary UPS Depth (mm)	1,100
Primary UPS Height (mm)	1,475
Primary UPS Width (mm)	600
Shipping Dimensions (hwd / cm)	164.49 x 74.98 x 122.00
Shipping Dimensions (hwd / in.)	64.76 x 29.52 x 48.03
Shipping Weight (kg)	388.73
Shipping Weight (lbs.)	857.00
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, in.)	58.07 x 23.62 x 43.3
UPS Power Module Weight (kg)	328.40
UPS Power Module Weight (lbs.)	724
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	0° to +40°C (+32° to +104°F); De-rates to 90% capacity at 35°C / 95°F and 80% capacity at 40°C / 104°F
Storage Temperature Range	-15° to +60°C (+5° to +140°F)
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	12249
AC Economy Mode BTU / Hr. (Full Load)	545
AC Economy Mode Efficiency Rating (100% Load)	98%
Audible Noise	Less than 70 DBA front-side, 1m
Operating Elevation (m)	Up to 1000m (At elevations over 1000m, output de-rates by 1% per 100m)
<b>COMMUNICATIONS</b>	
Network Management Cards	<a href="#">WEBCARDLX</a> & <a href="#">Modbus Cards</a>
Network Monitoring Port Description	Includes pre-installed Tripp Lite WEBCARDLX network interface
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at <a href="https://www.tripplite.com/poweralert">https://www.tripplite.com/poweralert</a>





**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Communications Cable	DB9 cabling included
SNMP Compatibility	Includes pre-installed <a href="http://www.tripplite.com/Web-Management-Accessory-Card~WEBCARDLX">WEBCARDLX</a> ; network interface card
Communications Interface	DB9 Serial; EPO (emergency power off); Pre-installed network card; Slot for SNMP/Web interface
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode; Less than 20 ms. transfer time in economy mode
Low Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation without using battery power during brownout/undervoltage conditions to to 156V (Ph-Ph) Full load or 121V (Ph-Ph) 70% load or less; Below the low transfer voltage point, output is maintained utilizing reserve battery power
High Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation without using battery power during overvoltages to 253V (Ph-Ph), reducing output within 1% of nominal; Above this point, output is maintained utilizing reserve battery power
<b>SPECIAL FEATURES</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Auto Probe Monitoring (included); Zero transfer time; On-Line/Double-Conversion
Green Energy-Saving Features	High efficiency economy mode operation; Schedulable daily hours of economy mode operation
<b>STANDARDS &amp; COMPLIANCE</b>	
UPS Certifications	ROHS (Restriction of Hazardous Substances); Tested to CSA (Canada); Tested to NOM (Mexico); Tested to UL1778 (USA)
Certification Details	UL1778: 2014 5th Edition; CSA C22.2 No. 107.3.14; FCC Part 15 Class A
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	1-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty
3-Phase Warranty Statement	<a href="#">Tripp Lite 3-Phase UPS Factory Warranty</a>

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SV40KS2P0B](#)