

6

5

4

3





2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/23/05	
A		REDRAWN	5/15/08	



SPECIFICATIONS:

Material:

Insulator: PBT, Glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC RMS max

Current rating: 1 Amp max

Contact resistance: 25 mohms max initial

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute


Temperature Rating:

Operating temperature: -55°C to +85°C

Environmental:

Lead free, RoHS compliant

Positions: 3 thru 30
A = .049 [1.25] x No. of Positions -1
B = A + .100 [2.55]
C = A + .183 [4.65]



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

LIF FLEX CIRCUIT CONNECTOR
SIDE ENTRY, 2.50 MM PCB ROW SPACING

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØXX	± .10	.X	± .10	ØXX	± .10
.XX	± .020	ØXXX	± .015	.XX	± .015	ØXXX	± .010
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	SS	3/23/05		CHECKED	AY	7/28/10	
APPROVED							
TITLE				SIZE			
LIF FLEX CIRCUIT CONNECTOR				PART NO.			
SIDE ENTRY, 2.50 MM PCB ROW SPACING				PCB-B-XX-SA-25			
REF: S00043T				SCALE: NTS			
				SHEET 1 OF 1			

ROHS
COMPLIANT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PCB-B-20-SA-25](#) [PCB-B-18-SA-25](#) [PCB-B-08-SA-25](#) [PCB-B-04-SA-25](#) [PCB-B-24-SA-25](#) [PCB-B-06-SA-25](#) [PCB-B-14-SA-25](#) [PCB-B-28-SA-25](#) [PCB-B-19-SA-25](#)