

USB-C to HDMI Over Cat6 Extender/Adapter with POC, 150 ft. (45 m)

MODEL NUMBER: U444-CAT-H



Extends a USB Type-C audio/video signal up to 150 ft. to an HDMI display via Cat6 cable, while also charging the USB-C source device.

Features

USB-C to HDMI Extender for Displaying Video in Boardrooms and Conference Rooms This complete transmitter and receiver system is recommended for video presentations in conference rooms, schools, trade shows, meeting facilities, houses of worship, retail settings and digital signage applications where the source and display are farther apart than conventional A/V cables allow. The U444-CAT-H extends 1080p video and stereo audio signals from a USB-C source device to an HDMI display up to 150-ft. (45.72 m) away via user-supplied Cat6 cabling.

Built-In PoC Technology Provides Receiver Power to Avoid Bulky External Power Bricks Built-in Power over Cable (PoC) technology powers the low-profile receiver over Cat6 cable. Green and orange LEDs on both the transmitter and receiver will light up to indicate the system is receiving power and a signal is being transmitted.

Keep Your Source Device Constantly Charged to Avoid Unintentional Signal Loss The transmitter's USB-C port charges your laptop, tablet or other source device to avoid battery drain and untimely shutdowns. Just connect the source's included power supply or power adapter between the USB-C port and an available AC outlet to prevent the source from running out of juice prematurely.

Fine-Tune the High-Resolution Image to Meet Your Personal Standards Use the included screwdriver to adjust the equalization control on the receiver. You can choose from eight different settings to make sure the most effective 1080p image is displayed.

Plug-and-Play Operation for Quick Setup and Immediate Use The included transmitter and receiver units work right out of the box with no software or external power supply required. Connect the receiver to the HDMI display and the transmitter to the USB-C source with the units' built-in cables. Then, connect the two units using Cat6 patch cable, such as Tripp Lite N202-Series cable (sold separately). Connect an optional display to the transmitter's local HDMI output to monitor the image connected to the receiver up to 150-ft. (45.72 m) away.

Highlights

- Extends high-definition 1080p video up to 150-ft. (45.72 m) away from the source
- Power over Cable (PoC) technology provides power to the receiver
- Transmitter's local HDMI port allows you to see the high-def image being displayed
- Built-in equalization (EQ) control lets you fine-tune the digital image to your satisfaction
- USB-C port charges the source device to avoid battery drain and untimely shutdowns

Applications

- Connect a desktop computer, tablet, laptop, notebook, MacBook, Chromebook or smartphone for a video or PowerPoint presentation in a large conference room or meeting room
- Improve and upgrade the video quality of your trade show presentation or digital signage installation in a commercial or educational setting

System Requirements

- Source device with USB-C output (computer, laptop, tablet)
- Display device with HDMI input (HDTV, projector, monitor)

Package Includes

- Transmitter unit
- Receiver unit



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Mini screwdriver
- Owner's manual

Specifications

| OVERVIEW | |
|---------------------------------------|---|
| UPC Code | 037332238801 |
| Product Type | Extender Kit |
| Technology | HDMI; POC |
| VIDEO | |
| Max Supported Video Resolution | 1920x1080 (1080p @ 60Hz) |
| Max 1280 x 720 (720p) Range (ft) | 150 |
| Max 1920 x 1080 (1080p) Range (ft) | 15 |
| Transmitter Video Input | USB-C |
| Transmitter - Number of Video Outputs | 1 |
| Transmitter - Local Display Output | HDMI |
| Receiver/Transceiver Video Output | HDMI |
| Receiver - Number of Video Outputs | 1 |
| Recommended Cabling | Solid Wire Cat6 Cables (Tripp Lite's N202-Series) |
| Max Supported Color Depth | 24-bit True Color |
| 3D Video Supported | Yes |
| Chroma Sub Sampling | 4:4:4 |
| Maximum Signal Range (ft) | 150 |
| Maximum Signal Range (m) | 46 |
| AUDIO | |
| Audio Input | USB-C |
| Audio Output | HDMI |
| Audio Specification | PCM 7.1, DTS & Dolby 5.1 |
| BATTERY | |
| Battery Charging (5V/1.5A Port) | No |
| POWER | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|--|
| Power Source | Receiver end only (Optional) |
| Power Source Type | USB |
| Power Over Cable (PoC) Support | Yes |
| USER INTERFACE, ALERTS & CONTROLS | |
| LED Indicators | TX & RX: Green = Power; Orange = Signal Transmission |
| PHYSICAL | |
| Color | Black |
| Material of Construction | ABS |
| Number of Displays | 1 |
| Form Factor/Mounting Options | Pigtail |
| Receiver Unit Dimensions (hwd / in.) | 0.93 x 2.36 x 2 |
| Receiver Unit Weight (lbs.) | 0.154 |
| Shipping Dimensions (hwd / in.) | 1.73 x 7.87 x 5.60 |
| Shipping Weight (lbs.) | 0.49 |
| Transmitter Unit Dimensions (hwd / in.) | 1.02 x 3 x 2.42 |
| Transmitter Unit Weight (lbs.) | 0.154 |
| Unit Packaging Type | Box |
| Housing | Plastic |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32 to 104 °F (0 to 40 °C) |
| Storage Temperature Range | 5 to 122 °F (-15 to 50 °C) |
| Relative Humidity | 0% to 85% RH, Non-Condensing |
| COMMUNICATIONS | |
| Signal Range (ft.) | 150 |
| Signal Range (m) | 46 |
| EDID Compatible | Yes |
| Consumer Electronics Control (CEC) Supported | Yes |
| USB Extension Support | No |
| CONNECTIONS | |
| Side A - Connector 1 | USB C (MALE) |
| Side A - Connector 2 | USB Type-C (FEMALE) |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--------------------------------------|--|
| Side A - Connector 3 | RJ45 (FEMALE) |
| Side A - Connector 4 | HDMI (FEMALE) |
| Side B - Connector 1 | RJ45 (FEMALE) |
| Side B - Connector 2 | HDMI (MALE) |
| Side B - Connector 3 | MICRO-USB B (FEMALE) |
| Connector Plating | Nickel |
| FEATURES & SPECIFICATIONS | |
| HDCP Specification | 1.4 |
| USB Specification | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps) |
| Driver Required | No |
| Recommended Category Cable | Cat6/Cat6a |
| Built-In Equalizer | Yes |
| STANDARDS & COMPLIANCE | |
| Certifications | Tested to FCC, CE, RoHS, REACH |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U444-CAT-H](#)