


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/9/08	
A		UPDATE DRAWING	4/22/20	AY/RC



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 3 Amp.

Contact resistance: 20 mohms max.

Insulation resistance: 5,000 Mohms min.

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant

Positions: 04 thru 80

A = .100 [2.54] x No. of Positions per Row

B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS DATE

DRAWN SS 7/9/08

CHECKED

APPROVED

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE
 .100 x .100 DUAL ROW RECEPTACLE STRIP
 DUAL ENTRY, .197 [5.00] HEIGHT, SMT

SIZE	PART NO.	REV.
X	RS2BE-XX-G-SMT	A

REF: S00059T SCALE: NTS SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

<u>RS2BE-12-G-SMT</u>	<u>RS2BE-32-G-SMT</u>	<u>RS2BE-26-G-SMT</u>	<u>RS2BE-20-G-SMT</u>	<u>RS2BE-14-G-SMT</u>	<u>RS2BE-06-G-SMT</u>
<u>RS2BE-04-G-SMT</u>	<u>RS2BE-10-G-SMT</u>	<u>RS2BE-08-G-SMT</u>	<u>RS2BE-30-G-SMT</u>	<u>RS2BE-18-G-SMT</u>	<u>RS2BE-02-G-SMT</u>
<u>RS2BE-36-G-SMT</u>	<u>RS2BE-16-G-SMT</u>				