





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	-	RELEASED	8/13/12	
A	-	REVISED DIM.	10/3/12	



PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating: Gold flash over Nickel underplate overall.
Electrical: Current rating: 1 Amp max.
Contact resistance: 15 mohms max. initial
Insulation resistance: 5,000 Mohms min.
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant

Positions: 6 thru 100
A = .031 [0.80] x No. of Positions Per Row
B = .031 [0.80] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
INCHES	HOLES	ØXX	±.10	SIZE	PART NO.	REV.	
.X ±.10	ØXX ±.10	XX ±.020	ØXXX ±.015	X	SPH2-XX-U-SMT	A	
.XXX ±.015	ØXXX ±.010	APPROVALS	DATE	REF:	S00039T	SCALE:	NIS
DRAWN	TW	8/13/12		SIZE			
CHECKED	AY	8/13/12					
APPROVED							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[SPH2-18-U-SMT](#) [SPH2-08-U-SMT](#) [SPH2-14-U-SMT](#) [SPH2-10-U-SMT](#) [SPH2-02-U-SMT](#) [SPH2-20-U-SMT](#) [PH2-14-U-SMT-.230/.150-PP-T/R](#) [PH2-14-UB-SMT](#) [SPH2-06-U-SMT](#) [SPH2-12-U-SMT](#) [SPH2-16-U-SMT](#) [SPH2-04-U-SMT](#)
[PH2-14-U-SMT-.177/.155-PT](#)