






APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	08/25/08	BAS
A		REDRAWN	8/6/14	AV/LL



Recommended PCB Layout



SPECIFICATIONS:

Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Shell: Brass, Nickel plated
Plating: Gold flash over Nickel underplate on contact area, Tin over Copper underplate on PCB tails
Electrical: Operating voltage: 250 VAC max.
Current rating: 1.5 Amp max.
Contact resistance: 30 mohms max.
Insulation resistance: 1000 Mohms min. @ 500 VDC
Dielectric withstanding voltage: 750 VAC for 1 minute
Environmental: Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

USB TYPE B, VERTICAL, SMT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				TITLE			
.X	± .10	Ø.X	± .10	USB TYPE B, VERTICAL, SMT			
.XX	± .020	Ø.XX	± .015				
.XXX	± .015	Ø.XXX	± .010				
.XXX	± .010	Ø.XXX	± .010				
APPROVALS				DATE			
DRAWN	DY		8/22/08	SIZE PART NO. USB-B-S-VT-TSMT			
CHECKED	BAS		08/25/08				
APPROVED							
REF: S00035T				SCALE: NTS SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-B-S-VT-TSMT](#)