Resin-Molded Chip, Improved Reliability J-Lead





FEATURES

- · Compliant to the RoHS3 directive 2015/863/EU
- · Compliant to AEC-Q200
- Improved Reliability FR=0.5%/1000hrs
- · 100% Surge Current Tested
- · SMD J-lead

LEAD-FREE LEAD-FREE COMPATIBLE COMPONENT



APPLICATIONS


- · Automotive Electronics(Engine ECU)
- · Industrial Equipment


CASE DIMENSIONS:


millimeters (inches)


MARKING

Code	EIA Code	EIA Metric	L	W ₁	W ₂	Н	S
Α	1206	3216-18	3.20 ± 0.20 (0.126 ± 0.008)	1.60 ± 0.20 (0.063 ± 0.008)	1.20 ± 0.10 (0.047 ± 0.004)	1.60 ± 0.20 (0.063 ± 0.008)	0.80 ± 0.20 (0.031 ± 0.008)
В	1210	3528-21	3.50 ± 0.20 (0.138 ± 0.008)	2.80 ± 0.20 (0.110 ± 0.008)	2.20 ± 0.10 (0.087 ± 0.004)	1.90 ± 0.20 (0.075 ± 0.008)	0.80 ± 0.20 (0.031 ± 0.008)
С	2312	6032-27	6.00 ± 0.20 (0.236 ± 0.008)	3.20 ± 0.20 (0.126 ± 0.008)	2.20 ± 0.10 (0.087 ± 0.004)	2.50 ± 0.20 (0.098 ± 0.008)	1.30 ± 0.20 (0.051 ± 0.008)
N	2917	7343-30	7.30 ± 0.20 (0.287 ± 0.008)	4.30 ± 0.20 (0.169 ± 0.008)	2.40 ± 0.10 (0.094 ± 0.004)	2.80 ± 0.20 (0.110 ±0.008)	1.30 ± 0.20 (0.051 ± 0.008)










HOW TO ORDER





Code
pF code: 1st two digits
represent significant figures,
3rd digit represents multiplier
(number of zeros to follow)







TECHNICAL SPECIFICATIONS

Category Temperature Range:	-55 to +125°C
Rated Temperature:	+85°C
Capacitance Tolerance:	±20%, ±10% at 120Hz
Dissipation Factor:	Refer to next page
ESR 100kHz:	Refer to next page
Leakage Current:	After 1 minute's application of rated voltage, leakage current at 20°C is not more than 0.01CV or 0.5µA, whichever is greater.
	After 1 minute's application of rated voltage, leakage current at 85°C is not more than 0.1CV or 5µA, whichever is greater.
	After 1 minute's application of derated voltage, leakage current at 125°C is not more than 0.125CV or 6.3µA, whichever is greater.
Capacitance Change By	+15% Max. at +125°C
Temperature	+10% Max. at +85°C
	-10% Max. at -55°C






CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)


Capac	itance	Rated Voltage									
μF	Code	6.3V (0J)	10V (1A)	16V (1C)	20V (1D)	25V (1E)	35V (1V)				
0.33	334						Α				
0.47	474						Α				
0.68	684					Α	Α				
1.0	105			Α	Α	Α	В				
1.5	155				Α		В				
2.2	225		Α	Α	Α	В	В				
3.3	335	Α	Α	Α	В	В	С				
4.7	475		A/B	A/B	A/B		С				
6.8	685		В	В	С	С	N				
10	106		A/B	A/B/C	С	C/N	N				
15	156	В	В		N	N					
22	226	A/B	A/B	B/C/N	C/N	N					
33	336	A/C	B/C/N	B/C/N							
47	476	B/C	B/C/N	C/N							
68	686		N								
100	107		С								
150	157	С									

Released ratings

Please contact to your local AVX sales office when these series are being designed in your application.

Voltage vs Temperature Rating





Resin-Molded Chip, Improved Reliability J-Lead



RATINGS & PART NUMBER REFERENCE

AVV Dest No	0 0:-	Capacitance	Rated	DCL	DF@	ESR @	100k	Hz RMS Current	(mA)	*1 ∆C/C	MOL
AVX Part No.	Case Size	(µF)	Voltage (V)	(μ A)	120Hz (%)		25°C	85°C	125°C	(%)	MSL
					6.3	Volt					
F970J335#AA	A	3.3	6.3	0.5	4	4.5	129	116	52	*	3
F970J156#BA	В	15	6.3	0.9	6	2.0	206	186	82	*	3
F970J226#AA	A	22	6.3	1.4	12	2.5	173	156	69	*	3
F970J226#BA	В	22	6.3	1.4	8	1.9	212	190	85	*	3
F970J336#AA	A	33	6.3	2.1	12	2.5	173	156	69	*	3
F970J336#CC	С	33	6.3	2.1	6	1.1	316	285	126	*	3
F970J476#BA	B	47 47	6.3 6.3	3.0	6	0.9	292 350	262 315	117 140	*	3
F970J476#CC F970J157#CC	C	150	6.3	9.5	12	0.9	396	357	159	*	3
19703137#66		130	0.5	9.0		Volt	390	337	139		3
F971A225#AA	A	2.2	10	0.5	4	5.0	122	110	49	*	3
F971A335#AA	A	3.3	10	0.5	4	4.5	129	116	52	*	3
F971A475#AA	A	4.7	10	0.5	6	4.0	137	123	55	*	3
F971A475#BA	В	4.7	10	0.5	6	2.8	174	157	70	*	3
F971A685#BA	В	6.8	10	0.7	6	2.5	184	166	74	*	3
F971A106#AA	Α	10	10	1.0	6	3.0	158	142	63	*	3
F971A106#BA	В	10	10	1.0	6	2.0	206	186	82	*	3
F971A156#BA	В	15	10	1.5	6	2.0	206	186	82	*	3
F971A226#AA	A	22	10	2.2	15	3.0	158	142	63	*	3
F971A226#BA	В	22	10	2.2	8	1.9	212	190	85	*	3
F971A336#BA	В	33	10	3.3	8	1.9	212	190	85	*	3
F971A336#CC	С	33	10	3.3	6	1.1	316	285	126	*	3
F971A336#NC	N	33	10	3.3	6	0.7	463	417	185	*	3
F971A476#BA	В	47	10	4.7	10	1.0	292	262	117	*	3
F971A476#CC	C	47	10	4.7	8	0.9	350	315	140	*	3
F971A476#NC	N N	47	10	4.7	6	0.7	463	417	185	*	3
F971A686#NC F971A107#CC	C	68 100	10 10	6.8 10.0	6 10	0.6 0.7	500 396	450 357	200 159	*	3
F9/ IA 10/#CC	0	100	10	10.0		Volt	390	337	1 1 1 3 9		<u> </u>
F971C105#AA	A	1	16	0.5	4	7.5	100	90	40	*	3
F971C105#AA	A	2.2	16	0.5	4	5.0	122	110	49	*	3
F971C335#AA	A	3.3	16	0.5	4	4.5	129	116	52	*	3
F971C475#AA	A	4.7	16	0.8	8	4.0	137	123	55	*	3
F971C475#BA	В	4.7	16	0.8	6	2.8	174	157	70	*	3
F971C685#BA	В	6.8	16	1.1	6	2.5	184	166	74	*	3
F971C106#AA	А	10	16	1.6	8	3.5	146	132	59	*	3
F971C106#BA	В	10	16	1.6	6	2.1	201	181	80	*	3
F971C106#CC	С	10	16	1.6	6	1.5	271	244	108	*	3
F971C226#BA	В	22	16	3.5	8	1.9	212	190	85	*	3
F971C226#CC	С	22	16	3.5	8	1.1	316	285	126	*	3
F971C226#NC	N	22	16	3.5	6	0.7	463	417	185	*	3
F971C336#BA	В	33	16	5.3	10	2.1	201	181	80	*	3
F971C336#CC	С	33	16	5.3	8	1.1	316	285	126	*	3
F971C336#NC F971C476#CC	N	33	16	5.3	6	0.7	463	417	185	*	3
	C N	47 47	16	7.5	10	1.1	316	285	126	*	3
F971C476#NC	I IN	4/	16	7.5	8	0.7 Volt	463	417	185		3
F971D105#AA	A	1	20	0.5	4	7.5	100	90	40	*	3
F971D105#AA	A	1.5	20	0.5	4	6.7	106	95	42	*	3
F971D133#AA F971D225#AA	A	2.2	20	0.5	6	6.3	109	98	44	*	3
F971D335#BA	В	3.3	20	0.7	4	3.1	166	146	66	*	3
F971D475#AA	A	4.7	20	0.9	8	4.0	137	123	55	*	3
F971D475#BA	В	4.7	20	0.9	6	2.8	174	157	70	*	3
F971D685#CC	С	6.8	20	1.4	6	1.8	247	222	99	*	3
F971D106#CC	С	10	20	2.0	6	1.5	271	244	108	*	3
F971D156#NC	N	15	20	3.0	6	0.7	463	417	185	*	3
F971D226#CC	С	22	20	4.4	8	1.1	316	285	126	*	3
F971D226#NC	N	22	20	4.4	6	0.7	463	417	185	*	3
					25	Volt					
F971E684#AA	Α	0.68	25	0.5	4	7.6	99	89	40	*	3
F971E105#AA	Α	1	25	0.5	4	7.5	100	90	40	*	3
F971E225#BA	В	2.2	25	0.6	4	3.8	150	135	60	*	3
F971E335#BA	В	3.3	25	0.8	4	3.5	156	140	62	*	3
F971E685#CC	С	6.8	25	1.7	6	1.8	247	222	99	*	3
F971E106#NC	N	10	25	2.5	6	1.0	387	349	155	*	3
F971E156#NC	N	15	25	3.8	6	0.7	463	417	185	*	3
F971E226#NC	N	22	25	5.5	6	0.7	463	417	185	*	3

Resin-Molded Chip, Improved Reliability J-Lead



RATINGS & PART NUMBER REFERENCE

AVX Part No.	Case Size	Capacitance	Rated	DCL	DF@	ESR @	100k	Hz RMS Current	(mA)	*1 ∆C/C	MSL
AVA Falt NO.	Case Size	(μF)	Voltage (V)	(μΑ)	120Hz (%)	100kHz (Ω)	25°C	85°C	125°C	(%)	IVIOL
	35 Volt										
F971V334#AA	Α	0.33	35	0.5	4	12.0	79	71	32	*	3
F971V474#AA	Α	0.47	35	0.5	4	10.0	87	78	35	*	3
F971V684#AA	Α	0.68	35	0.5	4	7.6	99	89	40	*	3
F971V105#BA	В	1	35	0.5	4	4.0	146	131	58	*	3
F971V155#BA	В	1.5	35	0.5	4	4.0	146	131	58	*	3
F971V225#BA	В	2.2	35	0.8	4	3.8	150	135	60	*	3
F971V335#CC	С	3.3	35	1.2	4	2.0	235	211	94	*	3
F971V475#CC	С	4.7	35	1.6	6	1.8	247	222	99	*	3
F971V685#NC	N	6.8	35	2.4	6	1.0	387	349	155	*	3
F971V106#NC	N	10	35	3.5	6	1.0	387	349	155	*	3

^{*1: \(\}Delta C/C \) Marked "*"

#: "M" for ±20% tolerance, "K" for ± 10% tolerance.

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

Item	All Case (%)
Damp Heat	±10
Temperature cycles	±5
Resistance soldering heat	±5
Surge	±5
Endurance	±10
Load Humidity	±10


QUALIFICATION TABLE

TEST	F97 series (Temperature range -55°C to +125°C)	
IEST	Condition	
Damp Heat (Steady State)	At 85°C, 85% R.H., 1000 hours (No voltage applied) Capacitance ChangeRefer to page 110 (*1) Dissipation FactorInitial specified value or less Leakage Current125% or less than the initial specified value	
Load Humidity	After 1000 hour's application of rated voltage in series with a 33Ω resistor at 85° C, 85° R.H., capacitors meet the characteristics requirements table below. Capacitance Change	
Temperature Cycles	At -55°C / +125°C, 30 minutes each, 1000 cycles Capacitance ChangeRefer to page 109 (*1) Dissipation FactorInitial specified value or less Leakage CurrentInitial specified value or less	
Resistance to Soldering Heat	10 seconds reflow at 260°C, 5 seconds immersion at 260°C. Capacitance Change	
Solderability	After immersing capacitors completely into a solder pot at 245°C for 2 to 3 seconds, more than 3/4 of their electrode area shall remain covered with new solder.	
Surge	After application of surge voltage in series with a 33Ω resistor at the rate of 30 seconds ON, 30 seconds OFF, for 1000 successive test cycles at 85°C, capacitors shall meet the characteristic requirements in the table above. Capacitance Change	
Endurance	After 2000 hours' application of rated voltage in series with a 3Ω resistor at 85°C, or derated voltage in series with a 3Ω resistor at 125°C, capacitors shall meet the characteristic requirements in the table above. Capacitance Change	
Shear Test	After applying the pressure load of 17.7N for 60 seconds horizontally to the center of capacitor side body which has no electrode and has been soldered beforehand on a substrate, there shall be found neither exfoliation nor its sign at the terminal electrode	17.7N (1.8kg • f) For 60 seconds
Terminal Strength	Keeping a capacitor surface-mounted on a substrate upside down and supporting the substrate at both of the opposite bottom points 45mm apart from the center of capacitor, the pressure strength is applied with a specified jig at the center of the substrate so that substrate may bend by1mm as illustrated. Then, there shall be found no remarkable abnormality on the capacitor terminals.	H230 20 45 45 45
Failure Rate	0.5% per 1000 hours at 85°C, V _R with 0.1Ω/V series impedance, 60% confidence level.	


Resin-Molded Chip, Improved Reliability J-Lead




AVX SOLID ELECTROLYTIC CAPACITOR ROADMAP



FIVE CAPACITOR CONSTRUCTION STYLES





Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kyocera AVX:

```
        F971C336MCC
        F971D475MBA
        F971C226KCC
        F971D225KAA
        F971E225KBA
        F971V684MAA
        F971A336KBA

        F971C106MBA
        F971V475KCC
        F971A226MBA
        F971D156MNC
        F971V334MAA
        F971A686KNC
        F971E335MBA

        F971C106MCC
        F971C105MAA
        F971C106KBA
        F971C475MAA
        F971E105MAA
        F971D475MAA
        F971A476MNC

        F971C226MCC
        F971V105MBA
        F971E684MAA
        F971A335KAA
        F971A336MBA
        F970J336MCC
        F971C336MBA

        F970J476MBA
        F971C336MNC
        F970J336KAA
        F971E156MNC
        F971C336KCC
        F970J476MCC
        F971C335KAA

        F971A226MAA
        F971D226MCC
        F971A685KBA
        F971V225KBA
        F971C475MBA
        F971D105KAA
        F971A106MAA

        F970J476KCC
        F971A335MAA
        F970J476KBA
        F971D155KAA
        F971D105KAA
        F971D105KAA
```