

TCR Series



Professional Conductive Polymer Chip Capacitors



FEATURES

- Conductive polymer electrode
- Benign failure mode under recommended use conditions
- Robust design for long operation lifetime
- AVX maverick part control Q-process with statistical screening
- Improved basic reliability 0.5%/1000hrs
- Humidity 85°C/85%RH, Vr (up to 500 or 1000 hours see reference table)
- -55 to +125°C operation temperature
- DCL 0.1 CxV, 0.05CV on selected codes
- 3x reflow 260°C compatible
- Low ESR




SnPb termination option is not RoHS compliant.

APPLICATIONS


- Long life time DC/DC converter applications in Telecommunications, Industrial, Avionics

For additional information on Q-process please consult the AVX technical publication "Reaching the Highest Reliability for Tantalum Capacitors" (see the link: <http://www.avx.com/docs/techinfo/Qprocess.pdf>)



MARKING

B, D, T, Y CASE



CASE DIMENSIONS: millimeters (inches)

Code	EIA Code	EIA Metric	L±0.20 (0.008)	W±0.20 (0.008) -0.10 (0.004)	H±0.20 (0.008) -0.10 (0.004)	W ₁ ±0.20 (0.008)	A±0.30 (0.012) -0.20 (0.008)	S Min.
B	1210	3528-21	3.50 (0.138)	2.80 (0.110)	1.90 (0.075)	2.20 (0.087)	0.80 (0.031)	1.40 (0.055)
D	2917	7343-31	7.30 (0.287)	4.30 (0.169)	2.90 (0.114)	2.40 (0.094)	1.30 (0.051)	4.40 (0.173)
T	1210	3528-12	3.50 (0.138)	2.80 (0.110)	1.20 (0.047) max.	2.20 (0.087)	0.80 (0.031)	1.40 (0.055)
Y	2917	7343-20	7.30 (0.287)	4.30 (0.169)	2.00 (0.079) max.	2.40 (0.094)	1.30 (0.051)	4.40 (0.173)

W1 dimension applies to the termination width for A dimensional area only.

*Codes under development

HOW TO ORDER

TCR

Type

D

Case Size
See table above

476

Capacitance Code
pF code: 1st two digits represent significant figures, 3rd digit represents multiplier (number of zeros to follow)

M

Tolerance
M = ±20%

016

Rated DC Voltage
004 = 4Vdc
006 = 6.3Vdc
010 = 10Vdc
016 = 16Vdc
020 = 20Vdc
025 = 25Vdc
035 = 35Vdc
050 = 50Vdc

#

Packaging
R = Pure Tin 7" Reel
S = Pure Tin 13" Reel
H = Tin Lead 7" Reel (contact manufacturer)
K = Tin Lead 13" Reel (contact manufacturer)

0070

ESR in mΩ

J

DCL
J = 0.1CV

TECHNICAL SPECIFICATIONS

Technical Data:	All technical data relate to an ambient temperature of +25°C
Capacitance Range:	10µF to 220µF
Capacitance Tolerance:	±20%
Leakage Current DCL:	(J) 0.1CV
Temperature Range:	-55°C to +125°C
Basic Reliability:	0.5% per 1000 hours at 85°C, Vr with 0.1ΩV series impedance, 60% confidence level
Termination Finish:	Sn Plating (standard) and SnPb Plating upon request

NOTE: Conductive Polymer Capacitors are designed to operate within the limits of the environmental conditions specified for each series. If operated continuously at their maximum temperature and / or humidity limit, or beyond these limits, capacitors may exhibit a parametric shift in capacitance and increases in ESR. These changes may occur earlier if the specified environmental conditions are exceeded. Similarly, their normal operational time period will be significantly extended if their general duty cycle includes operation below maximum temperature within humidity controlled environments. Careful attention should be paid to maximum temperature with associated high humidity environments as well as voltage derating, ripple current and current surges. Please reference the AVX Conductive Polymer Capacitor Guidelines for more information or contact factory for application assistance.



CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

Capacitance		Rated Voltage DC (V _a)							
μF	Code	4V (G)	6.3V (J)	10V (A)	16V (C)	20V (D)	25V (E)	35V (V)	50V (T)
10	106							D(70)	D(120)
15	156						D(70)		
22	226		B(70)			D(70)			
33	336		B(70)	T(70)*	D(70)				
47	476		B(70)		D(70)				
68	686			D(70)					
100	107			D(70)					
150	157		D(40)						
220	227	D(40), Y(40)							

Available Ratings, (ESR ratings in mOhms in brackets)

Engineering samples - please contact manufacturer

*Codes under development – subject to change

Note: Voltage ratings are minimum values. AVX reserves the right to supply higher ratings in the same case size, to the same reliability standards.

RATINGS & PART NUMBER REFERENCE

AVX Part No.	Case Size	Capacitance (μF)	Rated Voltage (V)	Maximum Operating Temperature (°C)	DCL Max. (μA)	DF Max. (%)	ESR Max @ 100kHz (mΩ)	MSL	100kHz RMS Current (mA)				Humidity 85°C/85%RH, Vr (hrs)
									45°C	85°C	105°C	125°C	
4 Volt													
TCRD227M004#0040J	D	220	4	125	88	6	40	3	2400	1700	1100	600	1000
TCRY227M004#0040J	Y	220	4	125	88	6	40	3	2200	1500	1000	600	500
6.3 Volt													
TCRB226M006#0070J	B	22	6.3	125	13	6	70	3	1300	900	600	300	500
TCRB336M006#0070J	B	33	6.3	125	19	6	70	3	1300	900	600	300	500
TCRB476M006#0070J	B	47	6.3	125	28	6	70	3	1300	900	600	300	500
TCRD157M006#0040J	D	150	6.3	125	90	6	40	3	2400	1700	1100	600	1000
10 Volt													
TCRD686M010#0070J	D	68	10	125	68	6	70	3	1800	1300	800	500	1000
TCRD107M010#0070J	D	100	10	125	100	6	70	3	1800	1300	800	500	1000
16 Volt													
TCRD336M016#0070J	D	33	16	125	52	6	70	3	1800	1300	800	500	1000
TCRD476M016#0070J	D	47	16	125	75	6	70	3	1800	1300	800	500	1000
20 Volt													
TCRD226M020#0070J	D	22	20	125	44	8	70	3	1800	1300	800	500	1000
25 Volt													
TCRD156M025#0070J	D	15	25	125	37	8	70	3	1800	1300	800	500	1000
35 Volt													
TCRD106M035#0070J	D	10	35	125	35	8	70	3	1800	1300	800	500	1000
50 Volt													
TCRD106M050#0120J	D	10	50	125	50	10	120	3	1400	1000	600	400	500

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

ESR allowed to move up to 1.25 times catalog limit post mounting.

For typical weight and composition see page 226.

NOTE: AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.

TCR Series





Professional Conductive Polymer Chip Capacitors

RECOMMENDED DERATING FACTOR

Voltage and temperature derating as percentage of Vr.

Rated voltage	Operating Temperature		
	≤85°C	105°C	125°C
≤10V	90%	90%	60%
≥16V	80%	80%	54%



QUALIFICATION TABLE

TEST	TCR series (Temperature range -55°C to +125°C)													
	Condition			Characteristics										
Endurance	Determine after application of rated voltage for 2000 +48/-0 hours at 105±2°C. Also determine after application of 125°C temperature, 2/3 rated voltage for 2000 +48/-0 hours. After test leaving 1-2 hours at room temperature. Power supply impedance to be ≤0.1Ω/V.			Visual examination	no visible damage									
				DCL	2 x initial limit									
				ΔC/C	within +20/-30% of initial value									
				DF	2 x initial limit									
				ESR	2 x initial limit									
Storage Life	125°C, 0V, 2000h			Visual examination	no visible damage									
				DCL	2 x initial limit									
				ΔC/C	within ±20% of initial value									
				DF	2 x initial limit									
				ESR	2 x initial limit									
Biased Humidity	Determine after leaving for 500 or 1000 hours at 85±2°C, 85% relative humidity and rated voltage and then recovery 1-2 hours at room temperature.			Visual examination	no visible damage									
				DCL	3 x initial limit									
				ΔC/C	within +30/-20% of initial value									
				DF	1.5 x initial limit									
				ESR	2 x initial limit									
Temperature Stability	Step	Temperature°C	Duration(min)											
	1	+20±2	15	DCL	+20°C	-55°C	+20°C	+85°C	+125°C	+20°C				
	2	-55+0/-3	15		IL*	n/a	IL*	10 x IL*	12.5 x IL*	IL*				
	3	+20±2	15	ΔC/C	n/a	±20%	±5%	±20%	±30%	±5%				
	4	+85+3/-0	15		DF	IL*	1.5 x IL*	IL*	1.5 x IL*	2 x IL*	IL*			
	5	+125+3/-0	15	Visual examination	no visible damage									
	6	+20±2	15		DCL	initial limit								
Surge Voltage	Test temperature: 125°C+3/0°C Surge voltage: 1.3 x 2/3 rated voltage Charge/Discharge resistance: 1000±100Ω Number of cycles: 1000x Cycle duration: 6 min; 30 sec charge, 5 min 30 sec discharge			ΔC/C	within +20/-30% of initial value									
				DF	1.25 x initial limit									
				ESR	1.25 x initial limit									
				Mechanical Shock/Vibration	MIL-STD-202, Method 213, Condition I, 100 G peak MIL-STD-202, Method 204, Condition D, 10 Hz to 2,000 Hz, 20 G peak			Visual examination	no visible damage					
								DCL	initial limit					
ΔC/C	within ±10% of initial value													
DF	initial limit													
ESR	1.25 x initial limit													

*Initial Limit

For use outside of recommended conditions and special request, please contact manufacturer.
Initial measurement max. 1hr after the removal from dry pack or after pretreatment at 85°C for 24 hours.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kyocera AVX:

[TCRD686M010R0070J](#) [TCRD476M016R0070J](#) [TCRD227M004R0040J](#) [TCRY227M004R0040J](#)
[TCRB226M006R0070J](#) [TCRB336M006R0070J](#) [TCRB476M006R0070J](#) [TCRD157M006R0040J](#)
[TCRD107M010R0070J](#) [TCRD336M016R0070J](#) [TCRD226M020R0070J](#) [TCRD156M025R0070J](#)
[TCRD106M035R0070J](#) [TCRD106M050R0120J](#)