


# Linking Contact System: BTB

70-9159



STRIPT™ or naked contacts have been proven to provide high performance at a lower cost structure than traditional insulated connectors. Adding to the list of UL certified contacts already on the market from AVX, the new high spring force “C-Clip” designed SMT contact can be linked together with a bridging contact to provide ultra-reliability in linear BTB connections. In addition to robustness, this three-piece component set absorbs mating tolerances between the boards and can handle 20 amps of continuous current.

## APPLICATIONS

- Linear LED Board-to-Board connections
- Co-Planar PCB mating

## FEATURES AND BENEFITS

- Fatigue resistant phosphor bronze material which generates and maintains high mating forces
- Integral dimples on the bridge contact provides positive retention in the c-clip contact
- Center placed attachment tang prevents the bridge contact from moving forward or backwards

## ELECTRICAL

- Current Rating: 20 Amps
- Voltage Rating: 300 V

## ENVIRONMENTAL

- Operating Temperature: -40°C to +125°C

## MECHANICAL

- Contact Material: Phosphor Bronze
- Plating: Lead-Free Matte Tin Over Nickel
- Durability: 5 Cycles

## HOW TO ORDER


<b>70</b>	<b>9159</b>	<b>001</b>	<b>3XX</b>	<b>006</b>
Prefix	Series	No. of Ways 001 = 1	Contact Description 302 = SMT Contact 311 = Bridge Contact	Plating Option 006 = Tin Over Nickel

Certification: UL File #E90723


# Linking Contact System: BTB

70-9159

## LOW PROFILE HIGH CURRENT SURFACE MOUNT CONTACT



## BRIDGE CONTACT 9159 SERIES SPECIAL



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kyocera AVX:](#)

[709159001302006](#) [709159001311006](#)