




# Clock Oscillators Surface Mount Type KC5032A-C2 Series (High Frequency)



CMOS/ 2.5V, 3.3V/ 5.0×3.2mm



RoHS Compliant

## Features

- Wide operating voltage range 2.5 to 3.3V
- $\pm 25 \times 10^{-6}$  available
- Highly reliable with seam welding
- Miniature ceramic package
- CMOS output

Table 1

| Freq. Tol.<br>Code | Tol. $\times 10^{-6}$ | Operating Temperature Range (°C) | Note                          |
|--------------------|-----------------------|----------------------------------|-------------------------------|
| 0                  | $\pm 50$              | -10 to +70                       | Standard specifications       |
| S                  | $\pm 30$              |                                  |                               |
| U                  | $\pm 25$              | -40 to +85                       | With only certain frequencies |
| F                  | $\pm 100$             |                                  |                               |
| G                  | $\pm 50$              | -40 to +105                      |                               |
| 6                  | $\pm 50$              |                                  |                               |

## How to Order

KC5032A 150.000 C 2 0 E 00  
① ② ③ ④ ⑤ ⑥ ⑦

- ① Type (5.0×3.2mm SMD)
- ② Output Frequency
- ③ Output Type (CMOS)
- ④ Supply Voltage (2.5V, 3.3V Compatible)
- ⑤ Frequency Tolerance (See Table 1)
- ⑥ Symmetry/ INH Function (45/ 55%, Stand-by)
- ⑦ Customer Special Model Suffix (STD Specification is "00")

Packaging (Tape & Reel 1000 pcs./ reel)

## Specifications


| Item                                                                        | Symbol             | Conditions                                                                                                                                | Min.                                                 | Max.                | Units |
|-----------------------------------------------------------------------------|--------------------|-------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------|---------------------|-------|
| Output Frequency Range                                                      | fo                 | fo>135MHz                                                                                                                                 | 135                                                  | 170                 | MHz   |
| Frequency Tolerance                                                         | f <sub>tol</sub>   | Initial tolerance, Operating temperature range, Rated power supply voltage change, Load change, Aging (1 year @25°C), Shock and vibration | Op. Temp.: -40 to +85°C                              | -100                | +100  |
|                                                                             |                    |                                                                                                                                           | Op. Temp.: -10 to +70°C/ -40 to +85°C/ -40 to +105°C | -50                 | +50   |
|                                                                             |                    |                                                                                                                                           | Op. Temp.: -10 to +70°C                              | -30                 | +30   |
|                                                                             |                    |                                                                                                                                           | Op. Temp.: -10 to +70°C                              | -25                 | +25   |
| Storage Temperature Range                                                   | T <sub>stg</sub>   |                                                                                                                                           | -55                                                  | +125                | °C    |
| Operating Temperature Range                                                 | T <sub>use</sub>   |                                                                                                                                           | -40                                                  | +105                | °C    |
| Max. Supply Voltage                                                         | —                  |                                                                                                                                           | -0.3                                                 | +4.0                | V     |
| Supply Voltage                                                              | V <sub>cc</sub>    |                                                                                                                                           | +2.25                                                | +3.63               | V     |
| Current Consumption (Loaded) (2.25<V <sub>cc</sub> ≤2.8V)                   | I <sub>cc</sub>    | 135<fo≤150MHz                                                                                                                             | —                                                    | 19                  | mA    |
| Current Consumption (Loaded) (2.8<V <sub>cc</sub> ≤3.63V)                   |                    | 150<fo≤170MHz                                                                                                                             | —                                                    | 23                  |       |
| Current Consumption (Loaded) (2.8<V <sub>cc</sub> ≤3.63V)                   |                    | 135<fo≤150MHz                                                                                                                             | —                                                    | 21                  |       |
| Current Consumption (Loaded) (2.8<V <sub>cc</sub> ≤3.63V)                   |                    | 150<fo≤170MHz                                                                                                                             | —                                                    | 25                  |       |
| Stand-by Current                                                            | I <sub>std</sub>   |                                                                                                                                           | —                                                    | 10                  | μA    |
| Symmetry                                                                    | SYM                | @50% V <sub>cc</sub>                                                                                                                      | 45                                                   | 55                  | %     |
| Rise/ Fall Time (10% V <sub>cc</sub> to 90% V <sub>cc</sub> Maximum Loaded) | tr/ tf             | 2.25≤V <sub>cc</sub> ≤2.8V                                                                                                                | —                                                    | 3.0                 | ns    |
|                                                                             |                    | 2.8≤V <sub>cc</sub> ≤3.63V                                                                                                                | —                                                    | 2.5                 |       |
| Low Level Output Voltage                                                    | V <sub>OL</sub>    | I <sub>OL</sub> =4mA                                                                                                                      | —                                                    | 10% V <sub>cc</sub> | V     |
| High Level Output Voltage                                                   | V <sub>OH</sub>    | I <sub>OH</sub> =-4mA                                                                                                                     | 90% V <sub>cc</sub>                                  | —                   | V     |
| Output Load                                                                 | L <sub>CMOS</sub>  | 2.25≤V <sub>cc</sub> ≤3.63V                                                                                                               | —                                                    | 15                  | pF    |
| Input Voltage Range                                                         | V <sub>IN</sub>    |                                                                                                                                           | 0                                                    | V <sub>cc</sub>     | V     |
| Low Level Input Voltage                                                     | V <sub>IL</sub>    |                                                                                                                                           | —                                                    | 30% V <sub>cc</sub> | V     |
| High Level Input Voltage                                                    | V <sub>IH</sub>    |                                                                                                                                           | 70% V <sub>cc</sub>                                  | —                   | V     |
| Disable Time                                                                | t <sub>dis</sub>   |                                                                                                                                           | —                                                    | 150                 | ns    |
| Enable Time                                                                 | t <sub>ena</sub>   |                                                                                                                                           | —                                                    | 5                   | ms    |
| Start-up Time                                                               | t <sub>str</sub>   | @Minimum operating voltage to be 0 sec.                                                                                                   | —                                                    | 10                  | ms    |
| 1 Sigma Jitter                                                              | J <sub>Sigma</sub> | Measured with Wavecrest SIA-3000                                                                                                          | —                                                    | 4                   | ps    |
| Peak to Peak Jitter                                                         | J <sub>PK-PK</sub> |                                                                                                                                           | —                                                    | 30                  | ps    |

Note: All electrical characteristics are defined at the maximum load and operating temperature range.

Please contact us for inquiry about operating temperature range, available frequencies and other conditions.


## Dimensions

(Unit: mm)



## Recommended Land Pattern

(Unit: mm)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kyocera AVX:](#)

[KC5032A150.000C20E00](#) [KC5032A150.000C2GE00](#)