


Automotive MLCC, KAM Series

General Specifications



GENERAL DESCRIPTION

KYOCERA AVX has supported the Automotive Industry requirements for Multilayer Ceramic Capacitors consistently for more than 25 years. Products have been developed and tested specifically for automotive applications and all manufacturing facilities are QS9000 and VDA 6.4 approved.

KYOCERA AVX is using AECQ200 as the qualification vehicle for this transition. A detailed qualification package is available on request and contains results on a range of part numbers.

The KAM series are plated with a Nickel/Tin finish. For FLEXITERM® please refer to the KAF series datasheet

HOW TO ORDER

KAM	31	G	R7	1H	475	K	U
Series AEC-Q200 Tin Nickel Finish	Size 05 = 0402 15 = 0603 21 = 0805 31 = 1206 32 = 1210 42 = 1808 43 = 1812 55 = 2220	Thickness See Cap Chart	Dielectric CG = COG R7 = X7R S7 = X7S T7 = X7T R8 = X8R L8 = X8L G8 = X8G	Voltage 0J = 6.3V 1A = 10V 1C = 16V 1E = 25V 1H = 50V 2A = 100V 2D = 200V 2E = 250V 2H = 500V 2J = 630V 3A = 1000V 3N = 1500V 3D = 2000V 3E = 2500V 3U = 3000V	Capacitance Code Code (in pF) 2 Significant Digits +Number of zeros eg 10uF = 106 10nF = 103 47pF = 470	Capacitance Tolerance B = $\pm 0.1\text{pF}$ ($<10\text{pF}$)* C = $\pm 0.25\text{pF}$ ($<10\text{pF}$)* D = $\pm 0.5\text{pF}$ ($<10\text{pF}$)* F = $\pm 1\%$ * G = $\pm 2\%$ * J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$ *COG only	Packaging See Table Below

PACKAGING CODES

Code	EIA (inch)	IEC(mm)	7" Paper	7" Embossed	13" Paper	13" Embossed
05	0402	1005	H		N	
15	0603	1608	T	U	M	L
21	0805	2012	T	U	M	L
31	1206	3216	T	U	M	L
32	1210	3225	T	U	M	L
42	1808	4520		Y		K
43	1812	4532		V		S
55	2220	5750		V		S

COMMERCIAL VS AUTOMOTIVE MLCC PROCESS COMPARISON

	Commercial	Automotive
Administrative	Standard Part Numbers. No restriction on who purchases these parts.	Specific Automotive Part Number. Used to control supply of product to Automotive customers.
Lot Qualification (Destructive Physical Analysis - DPA)	As per EIA RS469	Increased sample plan stricter criteria.
Visual/Cosmetic Quality	Standard process and inspection	100% inspection
Application Robustness	Standard sampling for accelerated wave solder	Increased sampling for accelerated wave solder followed by lot by lot reliability testing.

All Tests have Accept/Reject Criteria 0/1



The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

TDS-SMDMLCC-0033 | Rev 1

– SURFACE MOUNT CERAMIC CAPACITOR PRODUCTS –

Automotive MLCC - NP0
Capacitance Range



Case Size		0402				0603				0805							1206							1210						
Length (L)	mm (in.)	1.00 ± 0.10 (0.040 ± 0.004)				1.60 ± 0.15 (0.063 ± 0.006)				2.01 ± 0.20 0.079 ± 0.008							3.20 ± 0.20 (0.126 ± 0.008)							3.20 ± 0.20 (0.126 ± 0.008)						
Width (W)	mm (in.)	0.50 ± 0.10 (0.020 ± 0.004)				0.81 ± 0.15 (0.032 ± 0.006)				1.25 ± 0.20 (0.049 ± 0.008)							1.60 ± 0.20 (0.063 ± 0.008)							2.50 ± 0.20 (0.098 ± 0.008)						
Terminal (t)	mm (in.)	0.25 ± 0.15 (0.010 ± 0.006)				0.35 ± 0.15 (0.014 ± 0.006)				0.50 ± 0.25 (0.020 ± 0.010)							0.50 ± 0.25 (0.020 ± 0.010)							0.50 ± 0.25 (0.020 ± 0.010)						
WVDC		25V	50V	100V	25V	50V	100V	200V	250V	25V	50V	100V	200V	250V	500V	630V	50V	100V	200V	250V	500V	630V	1000V	50V	100V	200V	250V	500V	630V	1000V
095	0.5	A	A	A	A	A	A	A	A	B	B	B	B	B	B	B	B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
1R0	1.0	A	A	A	A	A	A	A	A	B	B	B	B	B	B	B	B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
100	10	A	A	A	A	A	A	A	A	B	B	B	B	B	B	B	B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
120	12	A	A	A	A	A	A	A	A	B	B	B	B	B	B		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
150	15	A	A	A	A	A	A	A	A	B	B	B	B	B	B		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
180	18	A	A	A	A	A	A	A	A	B	B	B	B	B	B		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
220	22	A	A	A	A	A	A	A	A	B	B	B	B	B	B		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
270	27	A	A	A	A	A	A	A	A	B	B	B	B	B	B		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
330	33	A	A	A	A	A	A	A	A	B	B	B	B	B	B		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
390	39	A	A	A	A	A	A	A	A	B	B	B	B	B	B		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
470	47	A	A		A	A	A	A	A	B	B	B	B	B	B		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
560	56	A	A		A	A	A	A		B	B	B	B	B	A		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
680	68	A	A		A	A	A	A		B	B	B	B	B	A		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
820	82	A	A		A	A	A	A		B	B	B	B	B	A		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
101	100	A	A		A	A	A	A		B	B	B	B	B	A		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
121	120				A	A	A			B	B	B	B	B	A		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
151	150				A	A	A			B	B	B	B	B	A		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
181	180				A	A	A			B	B	B	B	B	A		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
221	220				A	A	A			B	B	B	B	B	A		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
271	270				A	A	A			B	B	B	B	B	A		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
331	330				A	A	A			B	B	B	B	B	A		B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
391	390				A	A	A			B	B	B	B	B			B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
471	470				A	A				B	B	B	B	B			B	B	B	B	B	G	G	Q	Q	Q	Q	Q	Q	Q
561	560				A	A				B	B	B	B	B			B	B	B	B	N	G	G	Q	Q	Q	Q	Q	Q	Q
681	680				A	A				B	B	B					B	B	B	N	G	G	Q	Q	Q	Q	Q	Q	Q	Q
821	820				A	A				B	B	B	B				B	B	B	N	G	G	Q	Q	Q	Q	Q	Q	Q	Q
102	1000				A	A				B	B	B	B				B	B	N	N	G	G	Q	Q	Q	Q	Q	Q	Q	Q
122	1200				A	A				B	B	B					D	D	D	D	D	D	Q	Q	Q	Q	Q	Q	Q	Q
152	1500				A	A				B	B	B					D	D	D	D	D	D	Q	Q	Q	Q	Q	Q	Q	Q
222	2200				A					B	A						N	N	N	N	N	N	Q	Q	Q	Q	Q	Q	Q	Q
272	2700				A												N	N	N	N	N	N	G	G	G	G	G	G	G	G
332	3300				A												G	G	G	G	G	G	G	G	G	G	G	G	G	G
392	3900				A												G	G	G	G	G	G	G	G	G	G	G	G	G	G
472	4700				A												G	G	G	G	G	G	G	G	G	G	G	G	G	G
562	5600				A												G	G	G	G	G	G	G	G	G	G	G	G	G	G
682	6800				A												G	G	G	G	G	G	G	G	G	G	G	G	G	G
822	8200				A												G	G	G	G	G	G	G	G	G	G	G	G	G	G
103	10000				A												G	G	G	G	G	G		K	K	K	K	K	K	L
123	12000																G	G	G	G				K	K	K	K	K	K	K
153	15000																G	G	G	G				L	L	L	L	L	L	L
183	18000																G	G	G	G				L	L	L	L	L	L	L
223	22000																							L	L	L	L	L	L	L
273	27000																							L	L	L	L	L	L	L
333	33000																							L	L	L	L	L	L	L
393	39000																													
473	47000																													
563	56000																													
683	68000																													
823	82000																													
104	100000																													
100,000	104																													
WVDC		25V	50V	100V	25V	50V	100V	200V	250V	25V	50V	100V	200V	250V	500V	630V	50V	100V	200V	250V	500V	630V	1000V	50V	100V	200V	250V	500V	630V	1000V
Case Size		0402				0603				0805							1206							1210						

Case Size	0402 (KAM05)	0603 (KAM15)	0805 (KAM21)		1206 (KAM31)				1210 (KAM32)					
Thickness Letter	A	A	B	A	B	N	D	G	Q	B	F	G	K	L
Max Thickness (mm)	0.56	0.90	0.94	1.45	0.94	1.27	1.45	1.78	0.94	1.02	1.52	1.78	2.29	2.80
Carrier Tape	PAPER	PAPER	PAPER	EMB	PAPER	EMB	EMB	EMB	PAPER	EMB	EMB	EMB	EMB	EMB
Packaging Code 7" reel	H	T	T	U	T	U	U	U	T	U	U	U	U	U
Packaging Code 13" reel	N	M	M	L	M	L	L	L	M	L	L	L	L	L
PAPER					EMBOSSED (EMB)									

Automotive MLCC - X7R, 4V to 500V
Capacitance Range



SIZE		0402					0603					0805					1206					1210					1812		2220							
Soldering		Reflow/Wave					Reflow/Wave					Reflow/Wave					Reflow/Wave					Reflow Only					Reflow Only		Reflow Only							
(L) Length	mm	1 ± 0.1 (0.04 ± 0.004)					1.6 ± 0.15 (0.063 ± 0.006)					2.01 ± 0.2 (0.079 ± 0.008)					3.2 ± 0.2 (0.126 ± 0.008)					3.2 ± 0.2 (0.126 ± 0.008)					4.5 ± 0.3 (0.177 ± 0.012)		5.7 ± 0.5 (0.224 ± 0.02)							
(W) Width	mm	0.5 ± 0.1 (0.02 ± 0.004)					0.81 ± 0.15 (0.032 ± 0.006)					1.25 ± 0.2 (0.049 ± 0.008)					1.6 ± 0.2 (0.063 ± 0.008)					2.5 ± 0.2 (0.098 ± 0.008)					3.2 ± 0.2 (0.126 ± 0.008)		5 ± 0.4 (0.197 ± 0.016)							
(t) Terminal	mm	0.25 ± 0.15 (0.01 ± 0.006)					0.35 ± 0.15 (0.014 ± 0.006)					0.5 ± 0.25 (0.02 ± 0.01)					0.5 ± 0.25 (0.02 ± 0.01)					0.5 ± 0.25 (0.02 ± 0.01)					0.61 ± 0.36 (0.024 ± 0.014)		0.64 ± 0.39 (0.025 ± 0.015)							
WVDC		4V	6.3V	16V	25V	50V	6.3V	10V	16V	25V	50V	100V	200V	250V	6.3V	10V	16V	25V	50V	100V	200V	250V	16V	25V	50V	100V	200V	250V	50V	100V	25V	50V	100V	200V	250V	500V
101	100																																			
221	220			A	A	A																														
271	270			A	A	A																														
331	330			A	A	A																														
391	390			A	A	A																														
471	470			A	A	A																														
561	560			A	A	A																														
681	680			A	A	A																														
821	820			A	A	A																														
102	1000			A	A	A		A	A	A	A	A	A	A			B	B	B	B	B	B	B	B	B	B	B	Q	Q	Q	Q	Q	Q	Q	Y	Y
122	1220			A	A	A		A	A	A	A	A	A	A			B	B	B	B	B	B	B	B	B	B	B	Q	Q	Q	Q	Q	Q	Q	Y	Y
152	1500			A	A	A		A	A	A	A	A	A	A			B	B	B	B	B	B	B	B	B	B	B	Q	Q	Q	Q	Q	Q	Q	Y	Y
182	1800			A	A	A		A	A	A	A	A	A	A			B	B	B	B	B	B	B	B	B	B	B	Q	Q	Q	Q	Q	Q	Q	Y	Y
222	2200			A	A	A		A	A	A	A	A	A	A			B	B	B	B	B	B	B	B	B	B	B	Q	Q	Q	Q	Q	Q	Q	Y	Y
272	2700			A	A	A		A	A	A	A	A	A	A			B	B	B	B	B	B	B	B	B	B	B	Q	Q	Q	Q	Q	Q	Q	Y	Y
332	3300			A	A	A		A	A	A	A	A	A	A			B	B	B	B	B	B	B	B	B	B	B	Q	Q	Q	Q	Q	Q	Q	Y	Y
392	3900			A	A	A		A	A	A	A	A	A	A			B	B	B	B	B	B	B	B	B	B	B	Q	Q	Q	Q	Q	Q	Q	Y	Y
472	4700			A	A	A		A	A	A	A	A	A	A			B	B	B	B	B	B	B	B	B	B	B	Q	Q	Q	Q	Q	Q	Q	Y	Y
562	5600			A	A	A		A	A	A	A	A	A	A			B	B	B	B	B	B	B	B	B	B	B	Q	Q	Q	Q	Q	Q	Q	Y	Y
682	6800			A	A	A		A	A	A	A	A	A	A			B	B	B	B	B	B	B	B	B	B	B	Q	Q	Q	Q	Q	Q	Q	Y	Y
822	8200			A	A	A		A	A	A	A	A	A	A			B	B	B	B	B	B	B	B	B	B	B	Q	Q	Q	Q	Q	Q	Q	Y	Y
103	Cap .001			A	A	A		A	A	A	A	A	A	A			B	B	B	B	B	B	B	B	B	B	G	Q	Q	Q	Q	Q	Q	Y	Y	
123	(F) 0.012			A				A	A	A	A	A					B	B	B	B	B	K	B	B	B	B	N		Q	Q	Q	Q	Q	G	Y	
153	0.015			A				A	A	A	A	A					B	B	B	B	B	K	B	B	B	B	N		Q	Q	Q	Q	Q	G	Y	
183	0.018			A				A	A	A	A	A					B	B	B	B	K	K	B	B	B	B	N		Q	Q	Q	Q	Q	G	Y	
223	0.022			A				A	A	A	A	A					B	B	B	B	K	K	B	B	B	B	G		Q	Q	Q	Q	Q	G	Y	
273	0.027			A				A	A	A	A	B					B	B	B	B	K	K	B	B	B	B	G		Q	Q	Q	Q	Q	G	Y	
333	0.033			A				A	A	A	A	B					B	B	B	K	K	K	B	B	B	B	G		Q	Q	Q	Q	Q	G	Y	
393	0.039							A	A	A	A	B					B	B	B	K	K	K	B	B	B	B	G		Q	Q	Q	Q	Q	G	Y	
473	0.047							A	A	A	A	B					B	B	B	K	K	K	B	B	B	N	G		Q	Q	Q	Q	Q	G	Y	
563	0.056							A	A	A	A	B					B	B	B	K			B	B	B	N	G		Q	Q	Q	Q	C	G	Y	
683	0.068							A	A	A	A	B					B	B	B	K			B	B	B	N	G		Q	Q	Q	Q	C	G	Y	
823	0.082							A	A	A	A	B					B	B	B	K			B	B	B	N	G		Q	Q	Q	Q	G	G	Y	
104	0.1							A	A	A	A	B					B	B	B	K			B	B	B	N	G		Q	Q	Q	Q	G	G	Y	
124	0.12							A	B	B							B	B	K	K			B	B	B	N	G		Q	Q	Q	F	G	G	Y	
154	0.15							A	B	B							B	B	K	K			B	B	B	N	G		Q	Q	Q	F	K	G	Y	
224	0.22							A	B	B							J	K	K	K			B	B	B	G	G		Q	Q	Q	F	G	G	Z	
334	0.33																K	K	K	K			B	N	E	G	G		Q	Q	Q	G	L	L	G	
474	0.47																K	K	K	K			N	N	E	G			F	F	F	G		G	G	
684	0.68																K	K	K	K			N	G	G	G			F	F	G	K		G	G	
105	1.0		A														K	K	K	K			N	G	G	G			F	G	G	L		G	G	
155	1.5																K	K	K				G	G	G	G			F	G	L	L		G	G	
225	2.2		C(X7T)														K	K	K				G	G	G	G			L	L	L	L		J	J	
335	3.3																						G	G	G			K	L	L	L	L		J	C	
475	4.7																						G	G	G			K	L	L	L	L		J	C	
106	10		C(X7T)				C(X7T)																G					L	L	L				J	C	
226	22																																			C
WVDC		4V	6.3V	16V	25V	50V	6.3V	10V	16V	25V	50V	100V	200V	250V	6.3V	10V	16V	25V	50V	100V	200V	250V	16V	25V	50V	100V	200V	250V	50V	100V	25V	50V	100V	200V	250V	500V
Size		0402					0603					0805					1206					1210					1812		2220							
Case Size		0402(KAM05)		0603(KAM15)			0805(KAM21)					1206(KAM31)				1210(KAM32)					1812(KAM43)				2220(KAM55)											
Thickness Letter		A	C	A	B	C	B	J	K	A	B	N	E	G	Q	C	F	G	K	L	Y	Z	G	J	A	C										
Max Thickness(mm)		0.56	0.70	0.90	0.95	1.00	0.94	1.27	1.40	1.45	0.94	1.27	1.52	1.78	0.94	1.27	1.52	1.78	2.29	2.80	1.02	1.27	2.29	2.80	2.29	2.80										
Carrier Tape		PAPER	PAPER	PAPER	PAPER	PAPER	PAPER	EMB	EMB	EMB	PAPER	EMB	EMB	EMB	PAPER	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	
Packaging Code 7"reel		H	H	T	T	T	T	U	U	U	T	U	U	U	T	U	U	U	U	U	V	V	V	V	V	V	V	V	V	V	V	V	V	V		
Packaging Code 13"reel		N	N	M	M	M	M	L	L	L	M	L	L	L	M	L	L	L	L	L	S	S	S	S	S	S	S	S	S	S	S	S	S	S		
		PAPER													EMBOSSED (EMB)																					

Automotive MLCC - X7R, 630V to 3000V

Capacitance Range



PREFERRED SIZES ARE SHADED

Case Size	1206					1210				1808						1812						2220					
Soldering	Reflow/Wave					Reflow/Wave				Reflow Only						Reflow Only						Reflow Only					
(L) Length	mm (in.)	3.2 ± 0.2 (0.126 ± 0.008)					3.2 ± 0.2 (0.126 ± 0.008)				4.57 ± 0.25 (0.18 ± 0.01)						4.5 ± 0.3 (0.177 ± 0.012)						5.7 ± 0.5 (0.224 ± 0.02)				
(W) Width	mm (in.)	1.6 ± 0.2 (0.063 ± 0.008)					2.5 ± 0.2 (0.098 ± 0.008)				2.03 ± 0.25 (0.08 ± 0.01)						3.2 ± 0.2 (0.126 ± 0.008)						5 ± 0.4 (0.197 ± 0.016)				
(t) Terminal	mm max	0.5 ± 0.25 (0.02 ± 0.01)					0.5 ± 0.25 (0.02 ± 0.01)				0.61 ± 0.36 (0.024 ± 0.014)						0.61 ± 0.36 (0.024 ± 0.014)						0.64 ± 0.39 (0.025 ± 0.015)				
Voltage (V)		630	1000	1500	2000	2500	630	1000	1500	2000	630	1000	1500	2000	2500	3000	630	1000	1500	2000	2500	3000	630	1000	1500	2000	3000
Cap (pF)	101 100	B	B	B	B	B																					
	121 120	B	B	B	B	B																					
	151 150	B	B	B	B	B																					
	181 180	B	B	B	B	B																					
	221 220	B	B	B	B	B					B	B	B	B	B	B											
	271 270	B	B	B	B	B	H	H	H	H	B	B	B	B	B	B											
	331 330	B	B	B	B	B	H	H	H	H	B	B	B	B	B	B	E										
	391 390	B	B	B	B	B	H	H	H	H	B	B	B	B	B	B	E										
	471 470	B	B	B	B	B	H	H	H	H	B	B	B	B	B	B	E	E	E	E	E	E					
	561 560	B	B	B	B	B	H	H	H	H	B	B	B	B	B	B	E	E	E	E	E	E					
	681 680	B	B	B	B	B	H	H	H	H	B	B	B	B	B	B	E	E	E	E	E	E					
	821 820	B	B	B	B	B	H	H	H	H	B	B	C	C	C	C	E	E	E	E	E	E					
	102 1000	B	B	B	B	B	H	H	H	H	B	B	C	C	C	C	E	E	E	E	E	E	Z	Z	Z	Z	C
	122 1220	D	A	A	A		H	H	H	H							F	F	F	F	F	F	Z	Z	Z	Z	C
	152 1500	D	A	A	A		H	H	H	H							F	F	F	F	F	F	Z	Z	Z	Z	C
	182 1800	D	A	A			H	H	H	H							F	F	F	F	F	F	Z	Z	Z	Z	C
	222 2200	D	A	A			H	H	H	H							F	F	F	F	F	F	Z	Z	Z	Z	C
	272 2700	D	A	A			H	H	H	H							F	F	F	F	F	F	Z	Z	Z	Z	C
	332 3300	D	A				H	H	H	H							F	F	F	F			Z	Z	Z	Z	
	392 3900	D	A				H	H	H								F	F	F	F			Z	Z	Z	Z	
	472 4700	D	A				H	H	H								F	F	J	J			Z	Z	Z	Z	
	562 5600	D	A				H	H	H								F	F	J	J			Z	Z	Z	Z	
	682 6800	A	A				H	H									F	F	J	J			Z	Z	Z	Z	
	822 8200	A					H	H									F	F	J	J			Z	Z	C	C	
	103 0.01	A					H	H									F	F	J				C	C	C	C	
	123 0.012						H	H									F	F	J				C	C	C	C	
	153 0.015						H	H									F	F	J				C	C	C	C	
	183 0.018						H	H									F	F	J				C	C	C	C	
	223 0.022						H										F	F					C	C	C	C	
	273 0.027						H										F	F					C	C	C	C	
	333 0.033																F						C	C			
	393 0.039																F						C	C			
	473 0.047																F						C	C			
	563 0.056																						C	C			
	683 0.068																						C	C			
	823 0.082																						C	C			
	104 0.1																						C	C			
	124 0.12																						C				
	154 0.15																						C				
	224 0.22																										
	334 0.33																										
	474 0.47																										
	684 0.68																										
	105 1																										
	155 1.5																										
	225 2.2																										
	335 3.3																										
	475 4.7																										
	106 10																										
	226 22																										
WVDC		630	1000	1500	2000	2500	630	1000	1500	2000	630	1000	1500	2000	2500	3000	630	1000	1500	2000	2500	3000	630	1000	1500	2000	3000
Size		1206					1210				1808						1812						2220				

NOTE: Contact factory for non-specified capacitance values

Case Size	1206(KAM31)			1210(KAM32)	1808(KAM42)		1812(KAM43)			2220(KAM55)	
Thickness Letter	B	D	A	H	B	C	E	F	J	Z	C
Max Thickness	0.94	1.45	1.80	1.80	1.80	2.21	1.80	2.21	2.80	2.21	2.80
Carrier Tape	PAPER	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB
Packaging Code 7"reel	T	U	U	U	Y	Y	V	V	V	V	V
Packaging Code 13"reel	M	L	L	L	K	K	S	S	S	S	S
Paper						EMBOSSED (EMB)					

Automotive MLCC - X8R / X8L

Capacitance Range

KYOCERA AVX has developed a range of multilayer ceramic capacitors designed for use in applications up to 150°C. These capacitors are manufactured with an X8R and an X8L dielectric material. X8R material has capacitance variation of $\pm 15\%$ between -55°C and +150°C. The X8L material has capacitance variation of $\pm 15\%$ between -55°C to 125°C to 125°C and +15/40% from +125°C to +150°C.

The need for X8R and X8L performance has been driven by customer requirements for parts that operate at elevated temperatures. They provide a highly reliable capacitor with low loss and stable capacitance over temperature.

They are ideal for automotive under the hood sensors, and various industrial applications. Typical industrial application would be drilling monitoring system. They can also be used as bulk capacitors for high temperature camera modules.

X8R

SIZE		0402		0603		0805			1206			
Soldering		Reflow/Wave		Reflow/Wave		Reflow/Wave			Reflow/Wave			
(L) Length	mm (in.)	1.0 ± 0.1 (0.04 ± 0.1)		1.6 ± 0.15 (0.063 ± 0.006)		2.01 ± 0.2 (0.079 ± 0.008)			3.2 ± 0.2 (0.126 ± 0.008)			
(W) Width	mm (in.)	0.5 ± 0.1 (0.02 ± 0.004)		0.81 ± 0.15 (0.032 ± 0.006)		1.25 ± 0.2 (0.049 ± 0.008)			1.6 ± 0.2 (0.063 ± 0.008)			
(t) Terminal	mm (in.)	0.25 ± 0.15 (0.01 ± 0.006)		0.35 ± 0.15 (0.014 ± 0.006)		0.5 ± 0.25 (0.02 ± 0.01)			0.5 ± 0.25 (0.02 ± 0.01)			
WVDC		50V		25V	50V	100V	25V	50V	100V	25V	50V	100V
271	Cap 270	A	A	A	A							
331	(pF) 330	A	A	A	A	B	B	B				
471	470	A	A	A	A	B	B	B				
681	680	A	A	A	A	B	B	B				
102	1000	A	A	A	A	B	B	B	B	B	B	B
152	1500	A	A	A	A	B	B	B	B	B	B	B
182	1800	A	A	A	A	B	B	B	B	B	B	B
222	2200	A	A	A	A	B	B	B	B	B	B	B
272	2700	A	A	A	A	B	B	B	B	B	B	B
332	3300	A	A	A	A	B	B	B	B	B	B	B
392	3900	A	A	A	A	B	B	B	B	B	B	B
472	4700	A	A	A	A	B	B	B	B	B	B	B
562	5600		A	A	A	B	B	B	B	B	B	B
682	6800		A	A	A	B	B	B	B	B	B	B
822	8200		A	A	A	B	B	B	B	B	B	B
103	Cap 0.01		A	A	A	B	B	B	B	B	B	B
123	(uF) 0.012		A	A		B	B	B	B	B	B	B
153	0.015		A	A		B	B	A	B	B	B	B
183	0.018		A	A		B	B	A	B	B	B	B
223	0.022		A	A		B	B	A	B	B	B	B
273	0.027		A	A		B	B		B	B	B	B
333	0.033		A	A		B	B		B	B	B	B
393	0.039		A	A		B	B		B	B	B	B
473	0.047		A	A		B	B		B	B	B	B
563	0.056		A			A	A		N	N	N	N
683	0.068		A			A	A		N	N	N	N
823	0.082					A	A		N	N	N	N
104	0.1					A	A		N	N	N	N
124	0.12					A	A		N	N	N	N
154	0.15					A	A		N	N	N	N
184	0.18					A			N	N		
224	0.22					A			N	N		
274	0.27								N	N		
334	0.33								N	N		
394	0.39								E	G		
474	0.47								E	G		
684	0.68								G	G		
824	0.82								G	G		
105	1								G	G		
WVDC		50V		25V	50V	100V	25V	50V	100V	25V	50V	100V
SIZE		0402		0603		0805			1206			
Case Size		0402(KAM05)		0603(KAM15)		0805(KAM21)		1206(KAM31)			1210(KAM32)	
Thickness Letter		A	A	B	B	A	B	N	E	G	L	
Max Thickness		0.56	0.90	0.95	0.94	1.45	0.94	1.27	1.52	1.78	2.79	
Carrier Tape		PAPER	PAPER	PAPER	PAPER	EMB	PAPER	EMB	EMB	EMB	EMB	
Packaging Code 7"reel		H	T	T	T	U	T	U	U	U	U	
Packaging Code 13"reel		N	M	M	M	L	M	L	L	L	L	
Paper						EMBOSSED (EMB)						

X8L

SIZE		0603		0805		1206		1210	
Soldering		Reflow/Wave		Reflow/Wave		Reflow/Wave		Reflow/Wave	
(L) Length	mm (in.)	1.6 ± 0.15 (0.063 ± 0.006)		2.01 ± 0.2 (0.079 ± 0.008)		3.2 ± 0.2 (0.126 ± 0.008)		3.2 ± 0.2 (0.126 ± 0.008)	
(W) Width	mm (in.)	0.81 ± 0.15 (0.032 ± 0.006)		1.25 ± 0.2 (0.049 ± 0.008)		1.6 ± 0.2 (0.063 ± 0.008)		2.5 ± 0.2 (0.098 ± 0.008)	
(t) Terminal	mm (in.)	0.35 ± 0.15 (0.014 ± 0.006)		0.5 ± 0.25 (0.02 ± 0.01)		0.5 ± 0.25 (0.02 ± 0.01)		0.5 ± 0.25 (0.02 ± 0.01)	
WVDC		25V 50V 100V		25V 50V 100V		16V 25V 50V 100V		10V 25V 50V 100V	
271	Cap 270	A	A						
331	(pF) 330	A	A	A	B	B	B		
471	470	A	A	A	B	B	B		
681	680	A	A	A	B	B	B		
102	1000	A	A	A	B	B	B		
152	1500	A	A	A	B	B	B		
182	1800	A	A	A	B	B	B		
222	2200	A	A	A	B	B	B		
272	2700	A	A	A	B	B	B		
332	3300	A	A	A	B	B	B		
392	3900	A	A	A	B	B	B		
472	4700	A	A	A	B	B	B		
562	5600	A	A	A	B	B	B		
682	6800	A	A	A	B	B	B		
822	8200	A	A	A	B	B	B		
103	Cap 0.01	A	A	A	B	B	B		
123	(uF) 0.012	A	A	A	B	B	B		
153	0.015	A	A	A	B	B	B		
183	0.018	A	A	A	B	B	B		
223	0.022	A	A	A	B	B	B		
273	0.027	A	A	A	B	B	B		
333	0.033	A	A	B	B	B	A		
393	0.039	A	A		B	B	A		
473	0.047	A	A		B	B	A		
563	0.056	A	A		B	B	A		
683	0.068	A	A		B	B	A		
823	0.082	A	A		B	B	A		
104	0.1	A	A		B	B	A		
124	0.12				B	A			
154	0.15				B	A			
184	0.18				A	A			
224	0.22				A	A			
274	0.27				A				
334	0.33				A				
394	0.39				A				
474	0.47				A				
684	0.68				A				
824	0.82				A				
105	1				A				
155	1.5				A				
225	2.2				A				
475	4.7								L
106	10								L
WVDC		25V 50V 100V		25V 50V 100V		16V 25V 50V 100V		10V 25V 50V 100V	
SIZE		0603		0805		1206		1210	

Automotive MLCC - X8R / X8L

General Specifications


APPLICATIONS FOR X8R AND X8L CAPACITORS

- All market sectors with a 150°C requirement
- Automotive on engine applications
- Oil exploration applications
- Hybrid automotive applications
 - Battery control
 - Inverter / converter circuits
 - Motor control applications
 - Water pump
- Hybrid commercial applications
 - Emergency circuits
 - Sensors
 - Temperature regulation




ADVANTAGES OF X8R AND X8L MLC CAPACITORS

- Both ranges are qualified to the highest automotive AEC-Q200 standards
- Excellent reliability compared to other capacitor technologies
- RoHS compliant
- Low ESR / ESL compared to other technologies
- Tin solder finish
- FLEXITERM® available
- 100V range available



ENGINEERING TOOLS FOR HIGH VOLTAGE MLC CAPACITORS

- Samples
- Technical Articles
- Application Engineering
- Application Support



Automotive X8G (-55°C to 150°C , ±30ppm/°C)

Capacitance Range



SIZE		0402		0603		0805	
Soldering		Reflow/Wave		Reflow/Wave		Reflow/Wave	
(L) Length	mm (in.)	1 ± 0.1 (0.04 ± 0.004)		1.6 ± 0.15 (0.063 ± 0.006)		2.01 ± 0.2 (0.079 ± 0.008)	
(W) Width	mm (in.)	0.5 ± 0.1 (0.02 ± 0.004)		0.81 ± 0.15 (0.032 ± 0.006)		1.25 ± 0.2 (0.049 ± 0.008)	
(t) Terminal	mm (in.)	0.25 ± 0.15 (0.01 ± 0.006)		0.35 ± 0.15 (0.014 ± 0.006)		0.5 ± 0.25 (0.02 ± 0.01)	
WVDC		25V	50V	25V	50V	50V	100V
0R5	0.5			A	A	B	B
1R0	1.0			A	A	B	B
1R2	1.2			A	A	B	B
1R5	1.5			A	A	B	B
1R8	1.8			A	A	B	B
2R2	2.2			A	A	B	B
2R7	2.7			A	A	B	B
3R3	3.3			A	A	B	B
3R9	3.9			A	A	B	B
4R7	4.7			A	A	B	B
5R0	5			A	A	B	B
5R6	5.6			A	A	B	B
6R8	6.8			A	A	B	B
8R2	8.2			A	A	B	B
100	10			A	A	B	B
120	12			A	A	B	B
150	15			A	A	B	B
180	18			A	A	B	B
220	22			A	A	B	B
270	27			A	A	B	B
330	33			A	A	B	B
390	39			A	A	B	B
470	47	A	A	A	A	B	B
510	51	A	A	A	A	B	B
560	56	A	A	A	A	B	B
680	68	A	A	A	A	B	B
820	82	A	A	A	A	B	B
101	100	A	A	A	A	B	B
121	120			A	A	B	B
151	150			A	A	B	B
181	180			A	A	B	B
221	220			A	A	B	B
271	270			A	A		
331	330			A	A		
391	390			A	A		
471	470			A	A		
561	560						
681	680						
821	820						
102	1000						
122	1200						
152	1500						
182	1800						
222	2200						
272	2700						
332	3300						
392	3900						
472	4700						
562	5600						
682	6800						
103	10nF						
WVDC		25V	50V	25V	50V	50V	100V
Size		0402		0603		0805	

Case Size	0402(KAM05)	0603(KAM15)	0805(KAM21)
Letter	A	A	B
Max Thickness mm	0.56	0.90	0.94
Carrier Tape	Paper	Paper	Paper
Packaging Code 7"reel	H	T	T
Packaging Code 13"reel	N	M	M
	Paper		



The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KYOCERA AVX:](#)

[KAM15AR71C105KT](#) [KAM05CR71A105KH](#) [KAM05AR71A474KH](#) [KAM05AR70J474KH](#) [KAM15AR70J105KT](#)
[KAM15AR71A225KT](#) [KAM15AR70J225KT](#) [KAM15AR71A105KT](#) [KAM15CR70J475KT](#) [KAM05ACG1H2R7CH](#)