



TQQ1030

Band 30 BAW Duplexer


Product Description

The TQQ1030 is a compact, high-performance duplexer module optimized to meet the stringent OOB attenuation requirements along with excellent insertion loss performance, which is a key enabler to co-banding.

The TQQ1030 is built up on Qorvo's high performance NoDrift™ Bulk Acoustic Wave (BAW) technology in order to allow meeting stringent OOB attenuation requirements over temperature extremes.

The TQQ1030 uses Qorvo's unique Wafer-Level-Packaging (WLP) techniques to enable a compact 1.8 mm x 1.4 mm x 0.73 mm Typ footprint.

Functional Block Diagram



Top View



8 Pin: 1.8 mm x 1.4 mm x 0.73 mm Package

Key Features

- Compact form-factor: 1.8 mm x 1.4 mm
- Insertion loss – Enabling true co-banding
 - Tx band, 2305 – 2315 MHz: 1.7 dB Typ
 - Rx band, 2350 – 2360 MHz: 1.9 dB Typ
- Best in class close OOB attenuation across Temp
- High ISM band rejection
- Single-ended (SE) 50 Ohm receive & transmit ports
- RoHS compliant, Pb-free

Applications

- LTE handsets, data cards & mobile routers

Ordering Information

Part Number	Description
TQQ1030	B30 BAW Duplexer
TQQ1030-EVB	Evaluation Board

Standard T/R size = 2500 pieces on a 7" reel.

Absolute Maximum Ratings

Parameter	Rating
Storage Temperature	-40 to +85 °C
RF Input Power applied to pin 3 (CW, 50 Ω , 55 °C, 5000hrs)	+30 dBm
RF Input Power applied to pin 3 (Instantaneous)	+36 dBm

Operation of this device outside the parameter ranges given above may cause permanent damage.

Recommended Operating Conditions

Parameter	Min.	Typ.	Max.	Unit
T _{CASE}	-20		+90	°C

The duplexer will function over the recommended range without degradation in reliability or permanent change in performance.

Electrical Specifications¹ Antenna – Transmit

Unless otherwise noted: Operating Temp. = -20 °C to +90 °C.

Parameter	Condition	Min.	Typ.	Max.	Unit
Insertion Loss	2305 – 2315 MHz	–	1.7	2.3	dB
Amplitude Ripple	2305 – 2315 MHz	–	0.2	0.9	dB
Group Delay	2300 – 2315 MHz	–	31	40	ns
VSWR (in/out)	2305 – 2315 MHz	–	1.3:1	2:1	–
ANT Impedance		–	50//5.1 nH ²	–	Ohms
Tx Impedance		–	50	–	Ohms
Attenuation	1225 –1250 MHz	40	44	–	dB
	1559 –1563 MHz	40	44	–	
	1565.42 –1573.374 MHz	40	44	–	
	1573.3 –1577.466 MHz	40	44	–	
	1577.466 –1585.42 MHz	40	44	–	
	1597.5515 –1605.886 MHz	40	44	–	
	2200 – 2288 MHz	10 ³	18	–	
	2288 – 2292 MHz	7	13	–	
	2292 – 2296 MHz	3	8	–	
	2320 – 2324 MHz	2	3	–	
	2324 – 2328 MHz	3	7	–	
	2328 – 2332 MHz	6.5	10	–	
	2332 – 2350 MHz	10 ³	19	–	
	2350 – 2360 MHz	47	53	–	
	2400 – 2485 MHz	40	48	–	
	4610 – 4630 MHz	35	40	–	
	4900 – 5950 MHz	20	24	–	
	6915 – 6945 MHz	30	35	–	

Notes:

1. All specifications are based on the Qorvo schematic for the main reference design.
2. Matching value based on simulation results.
3. Relative rejection to max insertion loss

Electrical Specifications¹ Receive

Parameter	Condition	Min.	Typ.	Max.	Unit
Insertion Loss	2350 – 2360 MHz	–	1.9	2.8	dB
Amplitude Ripple	2350 – 2360 MHz	–	0.2	0.9	
Group Delay	2350 – 2360 MHz	–	34	40	ns
VSWR (in/out)	2350 – 2360 MHz	–	1.3:1	2:1	–
ANT Impedance		–	50/5.1 nH ²	–	Ohms
Rx Impedance		–	50	–	Ohms
Attenuation	699 – 716 MHz	40	45	–	dB
	824 – 849 MHz	40	45	–	
	1710 – 1755 MHz	35	40	–	
	1850 – 1910 MHz	35	41	–	
	2305 – 2315 MHz	50	57	–	
	2327 – 2337 MHz	10	18	–	
	2336.2 – 2341.3 MHz	3	7	–	
	2400 – 6000 MHz	32	40	–	
	2400 – 2500 MHz	40	45	–	
	4900 – 5950 MHz	30	35	–	

Notes:

1. All specifications are based on the Qorvo schematic for the main reference design.
2. Matching value based on simulation results.


Electrical Specifications¹ - Isolation

Parameter	Condition	Min.	Typ.	Max.	Unit
Isolation	2305 – 2315 MHz	55	58	–	dB
	2350 – 2360 MHz	52	57	–	dB
	1574 – 1577 MHz	50	54	–	dB


Notes:

1. All specifications are based on the Qorvo schematic for the main reference design.


Transmit Performance Plots – Temp = 25 °C




Receive Performance Plots – Temp = 25 °C



Isolation Plots – Temp = 25 °C




Schematic



Bill of Materials – EVB

Reference Des.	Value	Description	Manuf.	Part Number
U1	N/A	B30 BAW Duplexer	Qorvo	TQQ1030
U2	5.1 nH	Shunt Inductor at ANT	Murata	LQP03TN5N1H02

Package, Marking, and Dimensions





Line 1: Product name

1030

Line 2: Assembly Lot Code#

XXX = Qorvo assembly number (3 characters only, starting from right side)



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN MILLIMETERS



DECIMAL	ANGULAR
X.X ± 0.1	±1°
X.XX ± 0.05	
X.XXX ± 0.025	

- Notes:
1. All dimensions are in millimeters. Angles are in degrees.
 2. Except where noted, this part outline conforms to JEDEC standard MO-220, Issue E (Variation VGGC) for thermally enhanced plastic very thin fine pitch quad flat no lead package (QFN).
 3. Dimension and tolerance formats conform to ASME Y14.4M-1994

Tape and Reel Information

Standard T/R size = 2,500 units/reel. All dimensions are in millimeters.

Cavity (mm)				Distance Between Centerline (mm)		Carrier Tape (mm)	Cover Tape (mm)
Length (A0) ±0.05	Width (B0) ±0.05	Depth (K0) ±0.05	Pitch (P1)	Length Direction (P2)	Width Direction (F)	Width (W)	Width (W)
1.60	2.0	0.95	4.0	2.00	3.50	8.0	5.4



Handling Precautions

PARAMETER	RATING	STANDARD
ESD – Human Body Model (HBM)	Class 1B	ESDA/JEDEC JS-001
ESD – Charged Device Model (CDM)	Class C3	ESDA/JEDEC JS-002
MSL – Moisture Sensitivity Level	Level 3	IPC/JEDEC J-STD-020



Caution!

ESD sensitive device

Solderability

Compatible with both lead-free (260 °C max. reflow temperature) and tin/lead (245 °C max. reflow temperature) soldering processes.
Package lead plating: Plated Au over Ni

RoHS Compliance

This part is compliant with the 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment), as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead free
- Halogen Free (Chlorine, Bromine)
- Antimony Free
- TBBP-A (C₁₅H₁₂Br₄O₂) Free
- SVHC Free



REVISION HISTORY

Revision	Description
Rev J	Updated Power Handling from +29dBm to +30dBm, Converted to Qorvo template

Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Web: www.qorvo.com

Tel: 1-844-890-8163

Email: customer.support@qorvo.com

Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.** Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

Copyright 2016 © Qorvo, Inc. | Qorvo is a registered trademark of Qorvo, Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qorvo:](#)
[TQQ1030](#)