

# TBJ Series



## CWR11 - MIL-PRF-55365/8 Established Reliability, COTS-Plus & Space Level




Fully qualified to MIL-PRF-55365/8, the CWR11 is the military version of EIA-535BAAC, with four case sizes designed for maximum packaging efficiency on 8mm & 12mm tape for high volume production (ensuring no TCE mismatch with any substrate). This construction is compatible with a wide range of SMT board assembly processes including wave or reflow solder, conductive epoxy or compression bonding techniques. The part also carries full polarity, capacitance / voltage and JAN brand marking.

For Space Level applications, AVX SRC9000 qualification is recommended (see ratings table for part number availability).

There are four termination finishes available: solder plated, fused solder plated, hot solder dipped and gold plated (these are "H", "K", "C" and "B" termination, respectively, per MIL-PRF-55365).

The molding compound has been selected to meet the requirements of UL94V-0 (Flame Retardancy) and outgassing requirements of NASA SP-R-0022A.

The series is qualified to MIL-PRF-55365 Weibull "B", "C", "D" and "T" levels, with all surge options ("A", "B" & "C") available.



### MARKING

(Brown marking on gold body)



Polarity Stripe (+)

"J" for "JAN" Brand Capacitance Code

Rated Voltage  
Manufacturer's ID

### CASE DIMENSIONS: millimeters (inches)

Case Code	EIA Metric	Length (L)	Width (W)	Height (H)	Term. Width (W <sub>1</sub> ) ±0.10 (±0.004)	Term. Length A ±0.30(±0.012)	S min
A	3216-18	3.20±0.20 (0.126±0.008)	1.60±0.20 (0.063±0.008)	1.60±0.20 (0.063±0.008)	1.20 (0.047)	0.80 (0.031)	1.80 (0.071)
B	3528-21	3.50±0.20 (0.138±0.008)	2.80±0.20 (0.110±0.008)	1.90±0.20 (0.075±0.008)	2.20 (0.087)	0.80 (0.031)	1.40 (0.055)
C	6032-28	6.00±0.30 (0.236±0.012)	3.20±0.30 (0.126±0.012)	2.50±0.30 (0.098±0.012)	2.20 (0.087)	1.30 (0.051)	2.90 (0.114)
D	7343-31	7.30±0.30 (0.287±0.012)	4.30±0.30 (0.169±0.012)	2.80±0.30 (0.110±0.012)	2.40 (0.094)	1.30 (0.051)	4.40 (0.173)

### CAPACITANCE AND RATED VOLTAGE, V<sub>R</sub> (MIL VOLTAGE CODE) RANGE CASE SIZE

Capacitance		Rated voltage DC (V <sub>R</sub> ) to 85°C							
μF	Code	4V (C)	6V (D)	10V (F)	15V (H)	20V (J)	25V (K)	35V (M)	50V (N)
0.10	104							A	A
0.15	154							A	B
0.22	224							A	B
0.33	334						A	A	B
0.47	474					A	A	B	C
0.68	684				A	A	B	B	C
1.0	105			A	A	A	B	B	C
1.5	155		A	A	A	B	B	C	D
2.2	225	A	A	A	B	B	C	C	D
3.3	335		A	B	B	B	C	C	D
4.7	475	A	B	B	B	C	C	D	D
6.8	685	B	B	B	B	C	D	D	
10	106	B	B		C		D		
15	156	B	C	C		D	D		
22	226		C		D	D			
33	336	C		D	D				
47	476		D						
68	686	D	D						
100	107	D							
150	157								
220	227								
330	337								



# TBJ Series



## CWR11 - MIL-PRF-55365/8 Established Reliability, COTS-Plus & Space Level

### HOW TO ORDER

#### COTS-PLUS & MIL QPL (CWR11):

<b>TBJ</b>	<b>D</b>	<b>686</b>	<b>*</b>	<b>006</b>	<b>C</b>	<b>□</b>	<b>#</b>	<b>@</b>	<b>0</b>	<b>^</b>	<b>++</b>
<b>Type</b>	<b>Case Size</b>	<b>Capacitance Code</b> pF code: 1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow)	<b>Capacitance Tolerance</b> M = ±20% K = ±10% J = ±5%	<b>Voltage Code</b> 004 = 4Vdc 006 = 6Vdc 010 = 10Vdc 015 = 15Vdc 020 = 20Vdc 025 = 25Vdc 035 = 35Vdc 050 = 50Vdc	<b>Standard or Low ESR Range</b> C = Std ESR L = Low ESR	<b>Packaging</b> B = Bulk R = 7" T&R S = 13" T&R W = Waffle  See page 7 for additional packaging options.	<b>Inspection Level</b> S = Std. Conformance L = Group A  M = MIL (JAN) CWR11	<b>Reliability Grade</b> Weibull: B = 0.1%/1000 hrs. 90% conf. C = 0.01%/1000 hrs. 90% conf. D = 0.001%/1000 hrs. 90% conf. Z = Non-ER	<b>Qualification Level</b> 0 = N/A T = T Level  9 = SRC9000	<b>Termination Finish</b> H = Solder Plated 0 = Fused Solder Plated 8 = Hot Solder Dipped 9 = Gold Plated 7 = Matte Sn (COTS-Plus only)	<b>Surge Test Option</b> 00 = None 23 = 10 Cycles, +25°C 24 = 10 Cycles, -55°C & +85°C 45 = 10 cycles, -55°C & +85°C before Weibull

**Not RoHS Compliant**

LEAD-FREE LEAD-FREE COMPATIBLE COMPONENT  
For RoHS compliant products, please select correct termination style.

#### CWR11 P/N CROSS REFERENCE:

<b>CWR11</b>	<b>D</b>	<b>^</b>	<b>686</b>	<b>*</b>	<b>@</b>	<b>+</b>	<b>□</b>
<b>Type</b>	<b>Voltage Code</b> C = 4Vdc D = 6Vdc F = 10Vdc H = 15Vdc J = 20Vdc K = 25Vdc M = 35Vdc N = 50Vdc	<b>Termination Finish</b> H = Solder Plated K = Solder Fused C = Hot Solder Dipped B = Gold Plated	<b>Capacitance Code</b> pF code: 1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow)	<b>Capacitance Tolerance</b> M = ±20% K = ±10% J = ±5%	<b>Reliability Grade</b> Weibull: B = 0.1%/1000 hrs. 90% conf. C = 0.01%/1000 hrs. 90% conf. D = 0.001%/1000 hrs. 90% conf. T = T Level A = Non-ER	<b>Surge Test Option</b> A = 10 cycles, +25°C B = 10 cycles, -55°C & +85°C C = 10 cycles, -55°C & +85°C before Weibull  If blank, None required	<b>Packaging</b> Bulk = Standard TR = 7" T&R TR13 = 13" T&R W = Waffle  See page 7 for additional packaging options.

**Not RoHS Compliant**

#### SPACE LEVEL OPTIONS TO SRC9000\*:

<b>TBJ</b>	<b>D</b>	<b>686</b>	<b>*</b>	<b>006</b>	<b>C</b>	<b>□</b>	<b>L</b>	<b>@</b>	<b>9</b>	<b>^</b>	<b>++</b>
<b>Type</b>	<b>Case Size</b>	<b>Capacitance Code</b> pF code: 1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow)	<b>Capacitance Tolerance</b> M = ±20% K = ±10% J = ±5%	<b>Voltage Code</b> 004 = 4Vdc 006 = 6Vdc 010 = 10Vdc 015 = 15Vdc 020 = 20Vdc 025 = 25Vdc 035 = 35Vdc 050 = 50Vdc	<b>Standard or Low ESR Range</b> C = Std ESR L = Low ESR	<b>Packaging</b> B = Bulk R = 7" T&R S = 13" T&R W = Waffle  See page 7 for additional packaging options.	<b>Inspection Level</b> L = Group A	<b>Reliability Grade</b> Weibull: B = 0.1%/1000 hrs. 90% conf. C = 0.01%/1000 hrs. 90% conf. D = 0.001%/1000 hrs. 90% conf.	<b>Qualification Level</b> 9 = SRC9000	<b>Termination Finish</b> H = Solder Plated 0 = Fused Solder Plated 8 = Hot Solder Dipped 9 = Gold Plated	<b>Surge Test Option</b> 45 = 10 cycles, -55°C & +85°C before Weibull

**Not RoHS Compliant**

\*Contact factory for AVX SRC9000 Space Level SCD details.

### TECHNICAL SPECIFICATIONS

Technical Data:	Unless otherwise specified, all technical data relate to an ambient temperature of 25°C									
Capacitance Range:	0.1 µF to 100 µF									
Capacitance Tolerance:	±5%; ±10%; ±20%									
Rated Voltage: (V <sub>R</sub> )	≤85°C:	4	6	10	16	20	25	35	50	
Category Voltage: (V <sub>C</sub> )	125°C:	2.7	4	6.7	10	13.3	16.7	23.3	33.3	
Surge Voltage: (V <sub>S</sub> )	≤85°C:	5.3	8	13.3	20	26.7	33.3	46.7	66.7	
	125°C:	3.5	5.3	8.7	13.3	17.8	22.2	31.1	44.5	
Temperature Range:	-55°C to +125°C									





# TBJ Series



## CWR11 - MIL-PRF-55365/8 Established Reliability, COTS-Plus & Space Level

RATING & PART NUMBER REFERENCE				Parametric Specifications by Rating per MIL-PRF-55365/8									Typical Ripple Data by Rating						
				Cap @ 120Hz μF @ 25°C	DC Rated Voltage V @ +85°C	ESR @ 100kHz Ohms @ +25°C	DCL max			DF Max			Power Dissipation W	25°C Ripple A (100kHz)	85°C Ripple A (100kHz)	125°C Ripple A (100kHz)	25°C Ripple V (100kHz)	85°C Ripple V (100kHz)	125°C Ripple V (100kHz)
							+25°C (μA)	+85°C (μA)	+125°C (μA)	+25°C (%)	+(85/125)°C (%)	-55°C (%)							
CWR11K^106^@+□	TBJ D 106 * 025 C □ # @ 0 ^ ++	TBJ D 106 * 025 C □ L @ 9 ^ ++	D	10	25	1.2	2.5	25	30	6	8	9	0.150	0.35	0.32	0.14	0.42	0.38	0.17
CWR11K^156^@+□	TBJ D 156 * 025 C □ # @ 0 ^ ++	TBJ D 156 * 025 C □ L @ 9 ^ ++	D	15	25	1	3.8	38	45.6	6	9	9	0.150	0.39	0.35	0.15	0.39	0.35	0.15
CWR11M^104^@+□	TBJ A 104 * 035 C □ # @ 0 ^ ++	TBJ A 104 * 035 C □ L @ 9 ^ ++	A	0.1	35	24	0.5	5	6	4	6	6	0.075	0.06	0.05	0.02	1.34	1.21	0.54
CWR11M^154^@+□	TBJ A 154 * 035 C □ # @ 0 ^ ++	TBJ A 154 * 035 C □ L @ 9 ^ ++	A	0.15	35	21	0.5	5	6	4	6	6	0.075	0.06	0.05	0.02	1.25	1.13	0.50
CWR11M^224^@+□	TBJ A 224 * 035 C □ # @ 0 ^ ++	TBJ A 224 * 035 C □ L @ 9 ^ ++	A	0.22	35	18	0.5	5	6	4	6	6	0.075	0.06	0.06	0.03	1.16	1.05	0.46
CWR11M^334^@+□	TBJ A 334 * 035 C □ # @ 0 ^ ++	TBJ A 334 * 035 C □ L @ 9 ^ ++	A	0.33	35	15	0.5	5	6	4	6	6	0.075	0.07	0.06	0.03	1.06	0.95	0.42
CWR11M^474^@+□	TBJ B 474 * 035 C □ # @ 0 ^ ++	TBJ B 474 * 035 C □ L @ 9 ^ ++	B	0.47	35	10	0.5	5	6	4	6	6	0.085	0.09	0.08	0.04	0.92	0.83	0.37
CWR11M^684^@+□	TBJ B 684 * 035 C □ # @ 0 ^ ++	TBJ B 684 * 035 C □ L @ 9 ^ ++	B	0.68	35	8	0.5	5	6	4	6	6	0.085	0.10	0.09	0.04	0.82	0.74	0.33
CWR11M^105^@+□	TBJ B 105 * 035 C □ # @ 0 ^ ++	TBJ B 105 * 035 C □ L @ 9 ^ ++	B	1	35	6.5	0.5	5	6	4	6	6	0.085	0.11	0.10	0.05	0.74	0.67	0.30
CWR11M^155^@+□	TBJ C 155 * 035 C □ # @ 0 ^ ++	TBJ C 155 * 035 C □ L @ 9 ^ ++	C	1.5	35	4.5	0.5	5	6	6	8	9	0.110	0.16	0.14	0.06	0.70	0.63	0.28
CWR11M^225^@+□	TBJ C 225 * 035 C □ # @ 0 ^ ++	TBJ C 225 * 035 C □ L @ 9 ^ ++	C	2.2	35	3.5	0.8	8	9.6	6	8	9	0.110	0.18	0.16	0.07	0.62	0.56	0.25
CWR11M^335^@+□	TBJ C 335 * 035 C □ # @ 0 ^ ++	TBJ C 335 * 035 C □ L @ 9 ^ ++	C	3.3	35	2.5	1.2	12	14.4	6	8	9	0.110	0.21	0.19	0.08	0.52	0.47	0.21
CWR11M^475^@+□	TBJ D 475 * 035 C □ # @ 0 ^ ++	TBJ D 475 * 035 C □ L @ 9 ^ ++	D	4.7	35	1.5	1.7	17	20.4	6	8	9	0.150	0.32	0.28	0.13	0.47	0.43	0.19
CWR11M^685^@+□	TBJ D 685 * 035 C □ # @ 0 ^ ++	TBJ D 685 * 035 C □ L @ 9 ^ ++	D	6.8	35	1.3	2.4	24	28.8	6	9	9	0.150	0.34	0.31	0.14	0.44	0.40	0.18
CWR11N^104^@+□	TBJ A 104 * 050 C □ # @ 0 ^ ++	TBJ A 104 * 050 C □ L @ 9 ^ ++	A	0.1	50	22	0.5	5	12	6	8	8	0.075	0.06	0.05	0.02	1.28	1.16	0.51
CWR11N^154^@+□	TBJ B 154 * 050 C □ # @ 0 ^ ++	TBJ B 154 * 050 C □ L @ 9 ^ ++	B	0.15	50	17	0.5	5	6	4	6	6	0.085	0.07	0.06	0.03	1.20	1.08	0.48
CWR11N^224^@+□	TBJ B 224 * 050 C □ # @ 0 ^ ++	TBJ B 224 * 050 C □ L @ 9 ^ ++	B	0.22	50	14	0.5	5	6	4	6	6	0.085	0.08	0.07	0.03	1.09	0.98	0.44
CWR11N^334^@+□	TBJ B 334 * 050 C □ # @ 0 ^ ++	TBJ B 334 * 050 C □ L @ 9 ^ ++	B	0.33	50	12	0.5	5	6	4	6	6	0.085	0.08	0.08	0.03	1.01	0.91	0.40
CWR11N^474^@+□	TBJ C 474 * 050 C □ # @ 0 ^ ++	TBJ C 474 * 050 C □ L @ 9 ^ ++	C	0.47	50	8	0.5	5	6	4	6	6	0.110	0.12	0.11	0.05	0.94	0.84	0.38
CWR11N^684^@+□	TBJ C 684 * 050 C □ # @ 0 ^ ++	TBJ C 684 * 050 C □ L @ 9 ^ ++	C	0.68	50	7	0.5	5	6	4	6	6	0.110	0.13	0.11	0.05	0.88	0.79	0.35
CWR11N^105^@+□	TBJ C 105 * 050 C □ # @ 0 ^ ++	TBJ C 105 * 050 C □ L @ 9 ^ ++	C	1	50	6	0.5	5	6	4	6	6	0.110	0.14	0.12	0.05	0.81	0.73	0.32
CWR11N^155^@+□	TBJ D 155 * 050 C □ # @ 0 ^ ++	TBJ D 155 * 050 C □ L @ 9 ^ ++	D	1.5	50	4	0.8	8	9.6	6	8	9	0.150	0.19	0.17	0.08	0.77	0.70	0.31
CWR11N^225^@+□	TBJ D 225 * 050 C □ # @ 0 ^ ++	TBJ D 225 * 050 C □ L @ 9 ^ ++	D	2.2	50	2.5	1.1	11	13.2	6	8	9	0.150	0.24	0.22	0.10	0.61	0.55	0.24
CWR11N^335^@+□	TBJ D 335 * 050 C □ # @ 0 ^ ++	TBJ D 335 * 050 C □ L @ 9 ^ ++	D	3.3	50	2	1.7	17	20.4	6	9	9	0.150	0.27	0.25	0.11	0.55	0.49	0.22
CWR11N^475^@+□	TBJ D 475 * 050 C □ # @ 0 ^ ++	TBJ D 475 * 050 C □ L @ 9 ^ ++	D	4.7	50	1.5	2.4	24	28.8	6	9	9	0.150	0.32	0.28	0.13	0.47	0.43	0.19

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

**NOTE:** AVX reserves the right to supply a higher voltage rating or tighter tolerance part in the same case size, to the same reliability standards.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## AVX:

[TBJE686K020LBLC9000](#) [TBJE337K010LBLC9801](#) [TBJA105K020CBLB9812](#) [TBJB225K020CBLB9812](#)  
[TBJD106K025CBLB9812](#) [TBJE107K016LBLC9000](#) [TBJE107K015LBLC9000](#) [TBJB106K020LBLC9801](#)  
[TBJD336M035LBLC9000](#) [TBJD106K035LBLC9801](#) [TBJD336M035LBLC9045](#) [TBJA105K020CBLC9000](#)  
[TBJB105K035CBLC9000](#) [TBJB106K010CBLB9045](#) [TBJB106K020LBLC9884](#) [TBJB106K020LRLC9884](#)  
[TBJB475J010CRLB9045](#) [TBJB475K010CBLB9000](#) [TBJB475K010CBLB9045](#) [TBJC106K035CBLC9000](#)  
[TBJC156K035LBLC9845](#) [TBJC336K016LBLC9000](#) [TBJC336K020CBLB9845](#) [TBJC475K035LBLC9045](#)  
[TBJC476K016CBLC9055](#) [TBJD106K035CBLC9H45](#) [TBJD106K035LRLC9801](#) [TBJD107K016CBLB9945](#)  
[TBJD107K016LBDD0845](#) [TBJD156K035LBLC9000](#) [TBJD157M016LBLC9045](#) [TBJD157M016LBLC9055](#)  
[TBJD157M016LBLC9884](#) [TBJD226J016CBLB9812](#) [TBJD226K025LBLC9000](#) [TBJD475K050CBLC9000](#)  
[TBJD475K050LBLC9845](#) [TBJD476K016CBLC9H45](#) [TBJD477K006CRLB9945](#) [TBJD685J025CBLB9812](#)  
[TBJE107K016LBLC9045](#) [TBJE107M016LBLE9045](#) [TBJE337K010LBDB9845](#) [TBJE337K010LBLE9800](#)  
[TBJE337K010LRLE9800](#) [TBJE337K010LRLC9845](#) [TBJE476M035CRLC9845](#) [TBJE476M035LBLC9H45](#)  
[TBJE477M010LBLC9H45](#) [TBJE477M010LRLC9045](#) [TBJE686K025LBLC9055](#) [TBJD106K025CBLB9H45](#)  
[TBJD476K010CRLC9045](#) [TBJD107K016CBLD0845](#) [TBJV337M010LRDD0845](#) [TBJV157K016LRDD0845](#)  
[TBJE477M010LRDD0845](#) [TBJE477M006LRDD0H24](#) [TBJE227K010LRDD0823](#) [TBJE477M010LBDD0845](#)  
[TBJD157M016CBLD0024](#) [TBJD685K050LBDD0845](#) [TBJD107K016LRDD0845](#) [TBJE686K020LRSD0700](#)  
[TBJE337K010LRDD0824](#) [TBJC336K016LBLE0945](#) [TBJE477M010LRDD0H24](#) [TBJD335K050LRDD0845](#)  
[TBJD335K050LBDD0845](#) [TBJD156K035LRDD0845](#) [TBJD107K010LRLE0700](#) [TBJD685K050LRDD0845](#)  
[TBJD476M025LRDD0845](#) [TBJD107K016LBDD0824](#) [TBJD476K016LBLE9000](#) [TBJD336K025LRDD0845](#)  
[TBJD337M010CRDD0800](#) [TBJD337M010CRDD0824](#) [TBJD337M010CRDD0845](#) [TBJD337M010CRDD0823](#)  
[TBJE337K010LRDD0845](#) [TBJA104M050CRSB0000](#) [TBJB225M015CBSB0000](#) [TBJC105K050CBSD0700](#)  
[TBJA105K020CBSD0000](#) [TBJA105K020CRSD0000](#) [TBJD107M010LBDC0H00](#) [TBJD227K010LRLE0024](#)  
[TBJD337M010CBDD0800](#) [TBJD336K025LBLC0845](#) [TBJA106K010LBLC0045](#) [TBJA336K010LRLE0045](#)  
[TBJC106K015CBLC0845](#) [TBJC106K015CRLC0845](#) [TBJB476K006LBLC0045](#) [TBJD106K025CWLC0845](#)  
[TBJC685K025CBDD0H00](#) [TBJA106K010LRLE0045](#) [TBJB226K006LWLC0045](#) [TBJA225K016CRLC0045](#)