



2.0 × 1.6mm for Consumer Products/ Automotive



AEC-Q200 RoHS Compliant
PSL: R4Y MSL1

How to Order

CX2016SA 25000 D0 G S S HH
① ② ③④ ⑤ ⑥ ⑦ ⑧

- ① Series (Type and Size)
② Frequency (16,000 to 60,000kHz)
③④ Load Capacitance (Unit:pF) Ex.: D1:8.1pF

③ Integer part		④ After the decimal point	
D	8	0	.0
E	9	1	.1
F	10	2	.2
G	11	3	.3
H	12	4	.4
Z	Special suffix	5	.5
		6	.6
		7	.7
		8	.8
		9	.9

Packaging
(Tape & Reel 3000/ 15000 pcs./ reel)

⑤ Frequency Tolerance

F	±10×10 ⁻⁶
G	±15×10 ⁻⁶
H	±20×10 ⁻⁶
J	±25×10 ⁻⁶
K	±30×10 ⁻⁶
M	±40×10 ⁻⁶
P	±50×10 ⁻⁶
W	All Over
Z	Special suffix

Features

- Support a wide range of applications
- Ultra-miniature and low profile
(2.05 × 1.65 × 0.45mm)
- Ceramic package
- Reflow compatible

Applications

- ECU • Automotive Camera
- Digital Electronics • Consumer Products

⑥ Operating Temp. Range ⑦ Frequency Temp. Stability

⑥ \ ⑦		Q	R	S	T	V	W
		±30ppm	±40ppm	±50ppm	±100ppm	±150ppm	±200ppm
L	-30 to 85°C	✓	✓	✓	✓	✓	✓
P	-40 to 85°C	✓	✓	✓	✓	✓	✓
R	-40 to 105°C	✓	✓	✓	✓	✓	✓
S	-40 to 125°C			✓	✓	✓	✓
T	-40 to 150°C				✓	✓	✓

⑧ Individual Specification (STD Specification is “HH” .)

Specifications

Item	Symbol	Specification	Unit	Remarks
Frequency Range	f _{nom}	16000 to 60000	kHz	Please contact us for other frequency range.
Overtone Order	OT	Fundamental	—	
Load Capacitance	CL	8	pF	Please contact us for other CL requirements.
Frequency Tolerance	f _{tol}	±15	×10 ⁻⁶	25° C ± 3° C
Motional Series Resistance	R1	Table 1	ohm	
Drive Level	DL	10μW(200μW max.)	μW	
Operating Temp. Range	T _{use}	-40 to +125 -40 to +150 -30 to +85	°C	
Storage Temp. Range	T _{stg}	-40 to +150	°C	
Frequency Temp. Characteristics	f _{tem}	±50 ±200 ±20	×10 ⁻⁶	Freq. deviation from the value at 25° C
Shunt capacitance	C0	2.0max.	pF	


Please contact us for other specifications.

◆Table 1
Motional Series Resistance ESR (C1)

Frequency(MHz)	ESR (Ohm)
16≤F<18	200
18≤F<20	150
20≤F<24	100
24≤F<26	80
26≤F<40	60
40≤F≤60	50

Dimensions

(Unit: mm)



Recommended Land Pattern

(Unit: mm)

