

Noise Absorber

Controlled ESR Type

YNA Series

Type:	YNA15	1005 [0402 inch]
	YNA18	1608 [0603 inch]
	YNA21	2012 [0805 inch]

* Dimensions Code JIS[EIA]

○ All specifications are subject to change without notice.

○ Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.

Noise Absorber

Controlled ESR Type

Conformity to RoHS Directive
Lead-free Compatible

Overview of YNA Series

FEATURES

- The special laminated interior structure means ESR values can be controlled.
- An impedance waveform with no pole means anti-resonance is controlled.
- Without decreasing power efficiency, EMI measures can be taken.

APPLICATIONS

Countermeasures against ringing of switching power supply for smart phones, tablet PCs, etc.
Countermeasures against anti-resonance of impedance inside a decoupling circuit

PART NUMBER IDENTIFICATION

YNA	15		B	1C	0J		105		M	T	□□	0		N				
Series name	LxW dimensions		Product internal code	ESR value*	Rated voltage		Capacitance		Tolerance	Taping	TDK internal code	Reel size		Internal electrode Ni				
	Code	mm			Code	V	Code	pF				Code	mm					
	15	1.0×0.5			B	2-terminal (with NC terminal)	0G	4				105	1,000.000 (1.0μF)		M	±20%	0	ø178
	18	1.6×0.8				0J	6.3	9									ø330	
21	2.0×1.2	1A	10															
					1C	16												

* An ESR value is shown in two characters with a mΩ unit. The first digit is the multiplier of the ESR value: 1: 10, 2: 100, and 3: 1000.
The second digit shows the significant figure of the ESR value. A: 1.0, B: 1.5, C: 2.0, D: 2.5, E: 3.0, F: 3.5, G: 4.0, H: 4.5,
J: 5.0, K: 5.5, L: 6.0, M: 6.5, N: 7.0, P: 7.5, Q: 8.0, R: 8.5, S: 9.0, T: 9.5, U: 1.2

SPECIFICATIONS

Type	Specifications	
	Operating temperature range	Storage temperature range(After mount)
YNA15	-55 to +85	-55 to +85
YNA18	-55 to +85	-55 to +85
YNA21	-55 to +85	-55 to +85

PACKAGING STYLE AND SPECIFICATIONS

Type	Package quantity (piece/reel)		Single weight (g)
	ø178	ø330	
YNA15	10,000	50,000	0.0008
YNA18	4,000	10,000	0.0038
YNA21	4,000	10,000	0.0095

○ Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.


○ Please contact our Sales office when your application is considered the following:
The device's failure or malfunction may directly endanger human life (e.g. application for automobile/aircraft/medical/nuclear power devices, etc.)

○ All specifications are subject to change without notice.


Overview of YNA Series

RECOMMENDED SOLDERING CONDITION

REFLOW SOLDERING



HAND SOLDERING




PRECAUTIONS FOR USE


- Before soldering, be sure to preheat components. The ΔT preheating temperature must be 150°C max. with attention paid to thermal shock.
- Natural cooling of components in the air is recommended. On the other hand, when dipping them in a solvent for purposes, such as cleaning, make sure that the temperature difference (ΔT) is 100°.
- When performing hand soldering for circuit modification, apply the soldering iron to the copper foil area of the printed circuit board for 3 seconds or less. The temperature of the iron tip should not exceed 300°C.
- Use a wrist band to discharge static electricity in your body through the grounding wire.
- When incorporating the printed circuit board on which this product is mounted into a frame, etc., do not apply stress to the product through local bending of the board by tightening of screws, etc.

YNA Series YNA15 Type

SHAPES AND DIMENSIONS



RECOMMENDED LAND PATTERN



The lateral terminals are not connected.

ELECTRICAL CHARACTERISTICS

CHARACTERISTICS SPECIFICATION TABLE

Part No.	Capacitance (μF)	Tolerance (%)	Rated voltage Edc (V)	ESR (mΩ)
YNA15B1J0G105MT00□N*	1	20	4	50 (±30%)
YNA15B2A0G105MT00□N	1	20	4	100 (±30%)
YNA15B2C0G105MT00□N	1	20	4	200 (±30%)
YNA15B2J0G105MT00□N	1	20	4	500 (±30%)
YNA15B3A0G105MT00□N	1	20	4	1000 (±30%)


* Any ESR value can be set if it is the same as or smaller than the maximum ESR value. Contact us if you need an ESR value other than ones shown in the table.

* □: Please specify reel size code, 0 (ø178) or 9 (ø330)

ELECTRICAL CHARACTERISTICS GRAPH (EXAMPLE)


IMPEDANCE vs. FREQUENCY CHARACTERISTICS

YNA15B□□0G105M




ATTENUATION vs. FREQUENCY CHARACTERISTICS

YNA15B□□0G105M




YNA Series YNA18 Type

SHAPES AND DIMENSIONS



RECOMMENDED LAND PATTERN



ELECTRICAL CHARACTERISTICS

CHARACTERISTICS SPECIFICATION TABLE


Part No.	Capacitance (μF)	Tolerance (%)	Rated voltage E _{dc} (V)	ESR (mΩ)
YNA18B1J0G105MT00□N*	1	20	4	50 (±30%)
YNA18B2A0G105MT00□N	1	20	4	100 (±30%)
YNA18B2C0G105MT00□N	1	20	4	200 (±30%)
YNA18B2J0G105MT00□N	1	20	4	500 (±30%)
YNA18B3A0G105MT00□N	1	20	4	1000 (±30%)
YNA18B3U0G105MT00□N	1	20	4	1200 (±30%)

* Any ESR value can be set if it is the same as or smaller than the maximum ESR value. Contact us if you need an ESR value other than ones shown in the table.


* □: Please specify reel size code, 0 (ø178) or 9 (ø330)

ELECTRICAL CHARACTERISTICS GRAPH (EXAMPLE)

IMPEDANCE vs. FREQUENCY CHARACTERISTICS




ATTENUATION vs. FREQUENCY CHARACTERISTICS




YNA Series YNA21 Type

SHAPES AND DIMENSIONS



RECOMMENDED LAND PATTERN



The lateral terminals are not connected.

ELECTRICAL CHARACTERISTICS

CHARACTERISTICS SPECIFICATION TABLE


Part No.	Capacitance (μF)	Tolerance (%)	Rated voltage E _{dc} (V)	ESR (mΩ)
YNA21B1J0G106MT00□N*	10	20	4	50 (±30%)
YNA21B2A0G106MT00□N	10	20	4	100 (±30%)
YNA21B2C0G106MT00□N	10	20	4	200 (±30%)
YNA21B2J0G106MT00□N	10	20	4	500 (±30%)

* Any ESR value can be set if it is the same as or smaller than the maximum ESR value. Contact us if you need an ESR value other than ones shown in the table.


* □: Please specify reel size code, 0 (ø178) or 9 (ø330)

ELECTRICAL CHARACTERISTICS GRAPH (EXAMPLE)

IMPEDANCE vs. FREQUENCY CHARACTERISTICS




ATTENUATION vs. FREQUENCY CHARACTERISTICS



YNA Series Packing Style


REEL DIMENSIONS



Dimensions in mm

Reel	A	B	C	D	E	W	t	r
ø178	ø178±2.0	ø60±2.0	ø13±0.5	ø21±0.8	2.0±0.5	9.0±0.3	2.0±0.5	1.0
ø382	ø382 max.(ø330 nom.)	ø50 min.	ø13±0.5	ø21±0.8	2.0±0.5	10.0±1.5	2.0±0.5	1.0

TAPE DIMENSIONS



Dimensions in mm

Type	A	B	C	D	E	F	G	H	J	t
YNA15	0.62 typ.	1.12 typ.	8.0±0.3	3.5±0.05	1.75±0.1	2.0±0.1	2.0±0.05	4.0±0.1	ø1.5+0.10/-0	1.1 max.
YNA18	1.10 typ.	1.90 typ.	8.0±0.3	3.5±0.05	1.75±0.1	4.0±0.1	2.0±0.05	4.0±0.1	ø1.5+0.10/-0	1.1 max.
YNA21	1.50 typ.	2.3 typ.	8.0±0.3	3.5±0.05	1.75±0.1	4.0±0.1	2.0±0.05	4.0±0.1	ø1.5+0.10/-0	1.1 max.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TDK:](#)

[CERD1CX5R0G106M](#) [YNA21B1J0G106M](#) [YNA21B2J0G106M](#) [YNA21B1C0G106M](#) [YNA21B2C0G106M](#)
[YNA21B2A0G106M](#) [YNA18B2C0G105M](#) [YNA18B3U0G105M](#) [YNA18B2M0G105M](#) [YNA15B2J0G105M](#)
[YNA15B2A0G105M](#) [YNA15B1J0G105M](#) [YNA15B3A0G105M](#) [YNA15B2C0G105M](#) [YNA15B2A0G105MT000N](#)
[YNA15B1J0G105MT000N](#) [YNA18B3U0G105MT000N](#) [YNA15B2C0G105MT000N](#) [YNA15B2J0G105MT000N](#)
[YNA18B2C0G105MT000N](#) [YNA15B3A0G105MT000N](#) [YNA18B2M0G105MT000N](#)