


Slotted Optical Switch

OPB852A1, OPB852A2, OPB852A3
OPB853A1, OPB853A2, OPB853A3



Features:

- Inexpensive opaque plastic housing
- Choice of transistor (OPB852) or photodarlington (OPB853) output
- 0.125" (3.18 mm) slot width
- 0.290" (7.37 mm) lead spacing
- Apertured for high resolution



Description:

Slotted optical switches in the **OPB852**, and **OPB853** series consist of an infrared emitting diode and a NPN silicon phototransistor or photodarlington, mounted on opposite sides of a 0.125" (3.175 mm) wide slot. The **OPB852A**, **OPB852B** and **OPB852C** have phototransistor output, while the **OPB853A**, **OPB853B** and **OPB853C** have photodarlington output.

On each of these devices, the emitter has a molded-in aperture of 0.050" x 0.050" (1.270 mm x 1.270 mm) and the phototransistor (**OPB852**) or photodarlington (**OPB853**) has a molded-in aperture of 0.010" x 0.050" (0.254 mm x 1.270 mm).




Phototransistor or photodarlington switching occurs when an opaque object passes through the slot.

Custom electrical, wire and cabling and connectors are available. Contact your local representative or OPTEK for more information.

Applications:

- Non-contact interruptive object sensing
- Assembly line automation
- Machine automation
- Equipment security
- Machine safety

Part Number	LED Peak Wavelength	Sensor	Slot Width/ Depth	Aperture Emitter/ Sensor	Lead Length / Spacing
OPB852A1	890 nm	Transistor	0.120" / 0.315"	0.05" / 0.01"	0.425" / 0.290"
OPB852A2					
OPB852A3					
OPB853A1		Darlington			
OPB853A2					
OPB853A3					



Pin #	Description
1	Anode
2	Cathode
3	Collector
4	Emitter



RoHS

OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.

Slotted Optical Switch
OPB852A1, OPB852A2, OPB852A3
OPB853A1, OPB853A2, OPB853A3



Absolute Maximum Ratings ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

Storage & Operating Temperature Range	-40°C to +85° C
Lead Soldering Temperature [1/16 inch (1.6mm) from the case for 5 sec. with soldering iron]	260° C ⁽¹⁾

Input Diode

Forward DC Current	40 mA
Peak Forward Current (1 μs pulse width, 300 pps)	3 A
Reverse DC Voltage	2 V
Power Dissipation	100 mW ⁽²⁾

Output Phototransistor

Collector-Emitter Voltage	30 V
Emitter-Collector Voltage	5 V
Power Dissipation	100 mW ⁽²⁾

Electrical Characteristics ($T_A = 25^{\circ}\text{C}$ unless otherwise noted)

SYMBOL	PARAMETER	MIN	TYP	MAX	UNITS	TEST CONDITIONS
--------	-----------	-----	-----	-----	-------	-----------------

Input Diode (see OP140 for additional information—OPB852A_, OP245 for additional information—OPB853A)

V_F	Forward Voltage	-	-	1.7	V	$I_F = 20 \text{ mA}$
I_R	Reverse Current	-	-	100	μA	$V_R = 2 \text{ V}$

Output Phototransistor (see OP550 for additional information—OPB852A_, OP565 for additional information—OPB853A)

$V_{(BR)CEO}$	Collector-Emitter Breakdown Voltage	30 15	-	-	V	$I_C = 1 \text{ mA}$ $I_C = 1 \text{ mA}$
	OPB852A1, OPB852A2, OPB852A3 OPB853A1, OPB853A2, OPB853A3					
$V_{(BR)ECO}$	Emitter-Collector Breakdown Voltage	5	-	-	V	$I_E = 100 \mu\text{A}$
I_{CEO}	Collector-Emitter Dark Current	-	-	100	nA	$V_{CE} = 10 \text{ V}$

Combined

$V_{CE(SAT)}$	Saturation Voltage	-	-	0.4	V	$I_C = 500 \mu\text{A}, I_F = 20 \text{ mA}$ $I_C = 1.8 \text{ mA}, I_F = 20 \text{ mA}$ $I_C = 1.8 \text{ mA}, I_F = 10 \text{ mA}$
	OPB852A1, OPB852A2					
	OPB852A3					
	OPB853A1, OPB853A2, OPB853A3					
$I_{C(ON)}$	On-State Collector Current	1.0 2.0 4.0 2.5 5.0 10.0	-	-	mA	$V_{CE} = 5 \text{ V}, I_F = 20 \text{ mA}$ $V_{CE} = 5 \text{ V}, I_F = 20 \text{ mA}$ $V_{CE} = 5 \text{ V}, I_F = 20 \text{ mA}$ $V_{CE} = 1.5 \text{ V}, I_F = 5 \text{ mA}$ $V_{CE} = 1.5 \text{ V}, I_F = 5 \text{ mA}$ $V_{CE} = 1.5 \text{ V}, I_F = 5 \text{ mA}$
	OPB852A1					
	OPB852A2					
	OPB852A3					
	OPB853A1					
	OPB853A2					
	OPB853A3					





Notes:

- (1) RMA flux is recommended. Duration can be extended to 10 seconds maximum when flow soldering.
- (2) Derate linearly 1.67 mW/ $^{\circ}\text{C}$ above 25° C.
- (3) Methanol and isopropanol are recommended as cleaning agents. Housings are soluble in chlorinated hydrocarbons and ketones. Highly activated, water soluble fluxes may attack housings in some situations.
- (4) All parameters tested using pulse technique.

OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.

Slotted Optical Switch

OPB852A1, OPB852A2, OPB852A3
OPB853A1, OPB853A2, OPB853A3



OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TT Electronics:](#)

[OPB852A2](#) [OPB853A1](#) [OPB853A3](#)