

500-1500W Industrial Power supplies

<https://product.tdk.com/en/power/lzsa>

www.emea.lambda.tdk.com/lzsa



Industrial



COTS



Test



COMM



Broadcast

The LZSA series offers a unique feature set not commonly found with standard off-the-shelf supplies. Compliance to the MIL-STD-810E standards for shock and vibration and board coating make the LZSA power supplies ideal for use in a variety of harsh environment applications. They also comply with the tough ring wave lightning surge test per IEEE C62.41. Features include remote on/off, remote sense, frequency synchronization and a wide operating temperature range of -40°C to +71°C. The series also has a wide adjustment range which can be programmed using an external voltage or resistance.

Features	Benefits
• Rugged Mechanical Design With Coating on PCBs	• High Reliability in Harsh Environments
• Superior Thermal Design	• Long Life Even at 71°C Operation
• Wide Range, Programmable Output Adjustment	• Reduces The Need For custom Outputs
• Input Voltage Transient Protection	• Reduced System Filtering

Model Selector					
Part Number for Ordering	Model Number*	Nominal Output Voltage (V)	Adjustment Range (V)	Maximum Current (A)	Maximum Power (W)
LZSA-1000-2	LZS-A1000-2	12	10 - 15.75	84	1008
LZSA-500-3	LZS-A500-3	24	18 - 29.4	21	504
LZSA-1000-3	LZS-A1000-3	24	18 - 29.4	42	1008
LZSA-1500-3-001	LZS-A1500-3-001	24	18 - 29.4	63	1512 (3)
LZSA-1500-4	LZS-A1500-4	48	36 - 56	31.5	1512 (3)

* This part number is listed on the LZSA rating label and safety files

Specification					
Model	LZSA500		LZSA1000		LZSA1500
Input					
Input Voltage Range (Operating)	Vac	85 - 265			
Nominal Input Voltage Range	Vac	100-240 (Note: Safety certified for 90-264Vac)			
Input Frequency (2)	Hz	47-440 (Note: Safety certified for 47-63Hz only)			
DC Input Voltage range (1)	Vdc	100-380V (Note: Safety certified for AC input only)			
Input Current Maximum (100Vac)	A	8	15	18	
Inrush Current (110 / 220Vac)	A	25 / 45	30 / 40		
Leakage Current	uA	<500 at 265Vac, 60Hz			
Power Factor	-	EN61000-3-2 Class A			
Harmonics	-	EN61000-3-2 Compliant			
Hold Up Time at 110Vac Input	ms	20 hold up, 20 ride through			
Efficiency (Typical)	-	84			
Emissions	-	EN55032/EN55011 Class B, EN61000-3-3, MIL STD 461/462D, CE102			
Immunity	-	See Immunity Table			
Line Dip	-	SEMI F47 Compliant (4)			
Safety Certifications and Markings	-	IEC/EN/UL/CSA62368-1, 60950-1, UL508, CE Mark, UKCA Mark			

Immunity				
Test	Standard	Test Level	Criteria	Notes
ESD	IEC 61000-4-2	±8kV air discharge, ±6kV contact discharge	B	See test report on website
Radiated Susceptibility	IEC 61000-4-3	10V/m, 80 - 1000MHz (80% AM at 1kHz)	A	
Electrical Fast Transient Burst	IEC 61000-4-4	AC line pulses of ±2 kV; I/O line pulses of ±2kV>3m	A	
Surge	IEC 61000-4-5	±2kV common mode, ±1kV differential mode	A	
Conducted Susceptibility	IEC 61000-4-6	10Vrms, 150kHz - 80 MHz 1kHz 80% AM	A	
Magnetic fields	IEC 61000-4-8	30Arms/m @ 50Hz	A	
Voltage Dips and Input Interruptions	IEC 61000-4-11	Voltage Dips of 30%, 60% and 100%; Interruptions of >95%	A & B	
Ring Wave	IEEE C62.41	6kV/30 ohms	A	
SEMI F47 Line Dip	SEMI F47			See installation manual on website


Specification

Model	LZSA500		LZSA1000		LZSA1500
Output					
Line Regulation	%	0.10			
Load Regulation	%	0.10			
Transient Response	-	±1% deviation, recovering to ±0.2% in <1.25ms (25% load change)			
Temperature Coefficient	ppm/°C	100			
Ripple & Noise (pk-pk) (max.)	mV	75	75	24V: 75, 48V: 150	
Minimum Load	A	None			
Overcurrent Protection	%	110-130			
Overvoltage Protection	-	User adjustable from front panel			
Overtemperature Protection	-	Internal thermostat. Cycle AC to reset.			
Remote Sense	-	Compensates for a total of 1V cable drop			
Remote On/Off	-	TTL compatible, active high			
Remote Adjust	-	Using front panel potentiometer, Resistance (1k/V), or Voltage (1V/V)			
Input Power Good	-	Opto coupled, conducts up to 1mA @ <0.4V when active			
DC Good	-	Opto coupled, conducts up to 1mA @ <0.4V when active			
Inverter good	-	Opto coupled, conducts up to 1mA @ <0.4V when active			
Synchronization (Sync)	-	Auxiliary signal at approximately 200kHz used for synchronizing with other equipment.			
Indicators	-	Green LED indicates output good; red LED indicates overvoltage, overtemperature, or overcurrent			
Parallel Operation	-	Single wire current share			
Series Operation	-	See Installation Manual			
Environmental					
Operating Temperature	°C	-40 to +71, derate linearly to 60% load from 60 - 71° (A 20 minute warm up period needed for <30°)			
Storage Temperature	°C	-40 to +85			
Humidity (non condensing)	%RH	10 - 90			
Cooling	-	Variable speed, ball bearing fan			
Altitude	m	3,000 operating, 12,000 non-operating			
Withstand Voltage	VDC	Input to Ground 2,121, Input to Output 4,242, Output to Ground 500			
Vibration	-	MIL-STD-810E, Method 514.4, Category 1, 9			
Shock	-	MIL-STD-810E, Method 516.4, Procedure I, II, IV, VI			
Other					
Weight (Typ)	lbs / kg	6.6 / 2.95		8.1 / 3.7	
Size (WxHxD) (excluding bus bars)	mm	108 x 121 x 260		143 x 121 x 267	
Size (WxHxD) (excluding bus bars)	Inches	4.25 x 4.75 x 10.25		5.62 x 4.75 x 10.5	
MTBF - Bellcore	Hours	132,958		99,039	99,039
Warranty	Years	5			


Notes

- (1) Startup >110VDC
- (2) Reduced power factor above 63Hz
- (3) 1512W @ 180-265Vac, 1200W @ 120Vac, 1104W @ 100Vac, 1008W @ 85Vac
- (4) See website for detailed specifications, test methods and installation manual


Derating Charts




LZSA 500 Outline Drawing



LZSA 1000 Outline Drawing



LZSA 1500 Outline Drawing



**TDK-Lambda France SAS**

Tel: +33 1 60 12 71 65
 tlf.fr.powersolutions@tdk.com
 www.emea.lambda.tdk.com/fr

**Italy Sales Office**

Tel: +39 02 61 29 38 63
 tlf.it.powersolutions@tdk.com
 www.emea.lambda.tdk.com/it

**Netherlands**

tlf.nl.powersolutions@tdk.com
 www.emea.lambda.tdk.com/nl

**TDK-Lambda Germany GmbH**

Tel: +49 7841 666 0
 tlg.powersolutions@tdk.com
 www.emea.lambda.tdk.com/de

**Austria Sales Office**

Tel: +43 2256 655 84
 tlg.at.powersolutions@tdk.com
 www.emea.lambda.tdk.com/at

**Switzerland Sales Office**

Tel: +41 44 850 53 53
 tlg.ch.powersolutions@tdk.com
 www.emea.lambda.tdk.com/ch

**Nordic Sales Office**

Tel: +45 8853 8086
 tlg.dk.powersolutions@tdk.com
 www.emea.lambda.tdk.com/dk

**TDK-Lambda UK Ltd.**

Tel: +44 (0) 12 71 85 66 66
 tlu.powersolutions@tdk.com
 www.emea.lambda.tdk.com/uk

**TDK-Lambda Ltd.**

Tel: +9 723 902 4333
 tli.powersolutions@tdk.com
 www.emea.lambda.tdk.com/il-en

**TDK-Lambda Americas**

Tel: +1 800-LAMBDA-4 or 1-800-526-2324
 tla.powersolutions@tdk.com
 www.us.lambda.tdk.com

**TDK Electronics do Brasil Ltda**

Tel: +55 11 3289-9599
 sales.br@tdk-electronics.tdk.com
 www.tdk-electronics.tdk.com/en

**TDK-Lambda Corporation**

Tel: +81-3-6778-1113
 www.jp.lambda.tdk.com

**TDK-Lambda (China) Electronics Co. Ltd.**

Tel: +86 21 6485-0777
 tlc.powersolutions@tdk.com
 www.lambda.tdk.com.cn

**TDK-Lambda Singapore Pte Ltd.**

Tel: +65 6251 7211
 tls.marketing@tdk.com
 www.sg.lambda.tdk.com

**TDK India Private Limited, Power Supply Division**

Tel: +91 80 4039-0660
 mathew.philip@tdk.com
 www.sg.lambda.tdk.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TDK-Lambda:](#)

[LZSA-1000-2](#) [LZSA-1500-3-001](#) [LZSA-1500-4](#) [LZSA-500-3](#) [LZSA-1000-3](#)