

High Current Low Profile Surface Mount Inductors

Model HM65

Features and Benefits

- Operating Temperature Range -40°C to +130°C
- Operating Frequency Up to 3MHz
- RoHS Compliant



Specifications / Packaging

Part Number	Inductance ⁽¹⁾ Nominal μH ± 20%	Rated DC Current ⁽²⁾ (Amps)		Heating Current ⁽³⁾ (Amps)	DC Resistance ⁽⁴⁾ (Amps)		Case Size	Ht Height mm Max.	13" reel Qty (Units)
		25°C	130°C		mΩ Typ.	mΩ Max.			
HM65-H1R0LF	1.0	20.0	13.5	19.9	1.7	2.5	Standard	5.6	400
HM65-H1R8LF	1.8	15.3	11.5	15.2	2.9	3.4	Standard	5.6	400
HM65-H2R8LF	2.8	12.3	10.5	12.1	4.6	5.4	Standard	5.6	400
HM65-H3R9LF	3.9	10.5	8.3	11.4	5.2	8.0	Standard	5.6	400
HM65-H4R0LF	4.0	10.3	8.0	11.4	5.2	8.0	Standard	5.6	400
HM65-H5R6LF	5.6	8.8	7.5	8.1	10.2	11.4	Standard	5.6	400
HM65-H6R0LF	6.0	8.0	6.5	8.1	10.2	11.4	Standard	5.6	400
HM65-H7R2LF	7.2	7.8	6.0	7.8	11.4	13.5	Standard	6.0	400
HM65-1R5LF	1.5	14.0	10.5	17.1	1.7	2.5	Standard	5.6	400
HM65-2R5LF	2.5	10.0	8.0	15.2	2.9	3.4	Standard	5.6	400
HM65-6R0LF	6.0	6.7	4.5	11.5	5.1	8.0	Standard	5.6	400
HM65-8R2LF	8.2	5.8	4.5	8.1	10.2	11.4	Standard	5.6	400
HM65-100LF	10.0	5.0	4.0	7.8	11.3	13.5	Standard	5.6	400
HM65-P1R0LF	1.0	20.0	20.0	19.9	1.7	2.5	Standard	6.0	400
HM65-P1R2LF	1.2	18.0	18.0	19.9	1.7	2.5	Standard	6.0	400
HM65-P1R8LF	1.8	16.0	16.0	15.2	2.9	3.4	Standard	6.0	400
HM65-P2R5LF	2.5	10.0	10.0	15.2	2.9	3.4	Standard	6.0	400
HM65-M0R5LF	0.5	29.0	24.0	16.3	1.8	3.0	Mini	5.6	500
HM65-M0R8LF	0.8	20.0	16.0	16.3	1.8	3.0	Mini	5.6	500
HM65-M2R5LF	2.5	12.0	10.0	9.3	5.5	6.8	Mini	5.6	500

Notes: (1) Inductance is measured at 100kHz, 0.1V without DC current.

(2) Rated DC current is the approximate current at which inductance will be decreased by 25% from its initial (zero DC) value.

(3) Heating current is the DC current which causes the inductor temperature to increase by approximately 40°C.

(4) DC resistance is measured at 25°C.

Outline Dimensions (mm)

Top View

Side View

Refer to Specifications
Table

Bottom View

Recommended
Solder Pad Layout

Case Size	A	B	C	D	E	F	G	H	I	J	K	L	M	N	P
Standard	12.5	13.5	7.3	2.6	2.6	2.6	2.6	7.4	13.9	4.4	6.9	3.0	3.8	3.2	3.0
Mini	10.4	10.4	6.7	2.6	1.5	2.3	1.1	5.5	10.8	2.5	6.5	1.8	2.8	1.5	3.0





General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.

All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

Model HM65

Electrical Characteristic @ 25°C



Ordering Information

Model Series HM65 - H 1R0 LF TR13

Type: H = High Current
P = Premium Core Material
M = Mini-Package

TR - Tape & Reel Packing
13 - 13" reel

Lead-Free

Inductance Code:
First 2 digits are significant. Last digit denotes the number of trailing zeros. For values below 10µH, "R" denotes the decimal point

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TT Electronics:](#)

[HM65-8R2LFTR13](#) [HM65-H4R0LFTR13](#)