
Resistors

Heatsink Mount High Power Resistors



WMHP Series

- AEC-Q200 (WMHP35)
- TO-220 & TO-247 standard power packages
- Very low thermal resistance
- Non-inductive thick film technology
- 20 to 100 watt high power resistors
- Single screw mounting to heatsink
- Tailored heatsink WMHP-HS available
- Suitable for high frequency / fast pulse use



All parts are Pb-free and comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

Electrical Data

		WMHP20	WMHP35	WMHP50	WMHP100	Conditions
Package style			TO-220		TO-247	
Power rating	watts	20	35	50	100	Heatsink with 25°C flange temperature
Power rating	watts	1.5 2.5 3 3.5		Without heatsink, in free air 25°C		
Limiting element voltage	volts	350 700		dc or ac rms		
Resistance range	ohms	R05 – 10K R05 to 100K		to 100K		
Dielectric strength	volts	1800		ac rms for 60s		
Working temperature range	°C	-65 to 150		-65 to 175		
Insulation resistance	ohms	>10G		Between terminals and tab		
Tolerances	%	≤1R0: ±5 >1R0: ±1, ±5				
TCR	ppm/°C	≤R20: ±1000 >R20-3R0: ±300 >3R0-10R: ±100 >10R: ±50			25 to 105°C	
Standard values		E24 preferred				

Physical Data

D	imensions (mm) & Weight (g)					
	TO-220	TO-247		- A	- C	A	- c
Α	10.16 ±0.25	15.75 ±0.26			J		
В	15 ±0.3	20.7 ±0.26			TK A	D	
С	4.6 ±0.2	4.95 ±0.26	D -			K	
D	3.85 ±0.15	3.63 ±0.1		В			
Е	13.75 ±0.5	14.48 ±1.27					
F	4 max	2.79 ±0.76					
G	5.08 ±0.25	3.63 ±0.18				+ + + +	
Н	0.78 ±0.08	1.52 ±0.1		F →		G F	H
J	1.3 ±0.1	10.16 ±0.26		E			
K	6.4 ±0.25	5.33 ±0.26					
L	0.51 ±0.15	0.81 ±0.26		U U <u>t</u>	l II	<u> </u>	Н
M	2.27 ±0.25	2.41 ±0.26]	G -		н	L
Wt	2.0 nom	3.7 nom	TO-220	— Н	→ M -	TO-247	- M -

Performance Data

Test				
Load at Rated Power: 2000hrs at rated power	±ΔR%	1		
Short Term Overload: 2 x rated power with applied voltage not to exceed 1.5 x maximum continuous operating voltage for 5 seconds	±ΔR%	0.5		
Damp Heat with Load: 40 ±2°C, 90 – 95% RH, maximum working voltage 1.5 hours on, 0.5 hours off, 1000 hours	±ΔR%	1		
Thermal Shock: -65°C/150°C, 100cycles	±ΔR%	0.3		
Terminal Strength: 2.4N pull test	±ΔR%	0.2		


General Note

BI Technologies IRC Welwyn

Heatsink Mount High Power Resistors



WMHP Series




Mounting


The resistor should be mounted to a heatsink using a suitable thermal interface material. The maximum tightening torque for the M3 mounting screw is 0.9Nm.

A tailored heatsink is available which accommodates both TO-220 and TO-247 package styles. This is WMHP-HS and product data is available at $\,$

https://www.TTelectronics.com/TTElectronics/media/ProductFiles/Resistors/Datasheets/WMHP-HS.pdf



Typical High Frequency Performance



Typical high frequency characteristics for WMHP35-220R. Self resonant frequency is 1GHz.

Pulse performance for durations ≥1s is dependent on mounting conditions. The short term overload power limit is 2 x power rating for 5s.

Ordering Procedure

Example: WMHP35-10KJ (WMHP35 at 10 kilohms ±5%, Pb-free)

W M H P	3 5	-	1	0	K	J
1	2			3		4

1	2	3	4	
Туре	Rating	Value	Tolerance	Packing
WMHP	20	3 / 4 characters	F = ±1%	Plastic tubes
	35	R = ohms	J = ±5%	TO-220: 50/tube
	50	K = kilohms		TO-247: 30/tube
	100			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

WMHP100-10KF
WMHP100-R33J
WMHP50-22RJ
WMHP100-51RJ
WMHP100-2K2J
WMHP35-2R0F
WMHP100-R20J

R20J
WMHP100-22RJ
WMHP100-4R7J
WMHP100-2R7F
WMHP20-R10J
WMHP20-4K7F
WMHP100-20RJ

WMHP20-1R0J
WMHP100-R56J
WMHP100-20RF
WMHP20-2R0J
WMHP35-51RJ
WMHP20-27RJ
WMHP100-100-100RJ

100RF
WMHP100-10RJ
WMHP100-1R0J
WMHP100-1R0J
WMHP35-27RJ
WMHP50-1K0F
WMHP20-12RF
WMHP100-15RF
WMHP20-330RJ

WMHP100-10RJ
WMHP100-3R3F
WMHP35-27RJ
WMHP50-1K0F
WMHP20-12RF
WMHP100-15RF
WMHP20-1K0F

56RF
WMHP35-24RJ
WMHP35-15RJ
WMHP50-200RF
WMHP100-1K0J
WMHP20-1K0F
WMHP20-1K0J
WMHP20-1K0F

WMHP35-330RJ
WMHP50-10RJ
WMHP35-10RJ
WMHP20-5R6F
WMHP100-7R5F
WMHP20-1CRF
WMHP20-22RF
WMHP20-10RF
WMHP35-1R0J
WMHP20-10RF
WMHP20-10RF
WMHP20-10RF
WMHP35-1R0J
WMHP100-12RF
WMHP20-10RF
WMHP50-10RF
WMHP50-10RF
WMHP50-10RF
WMHP50-12RF
WMHP50-33RF
WMHP50-10RF</t