- Source or sink:
  - 2,000W of pulsed power (±40V, ±50A)
  - 200W of DC power (±10V@±20A, ±20V@±10A, ±40V@±5A)
- Easily connect two units (in series or parallel) to create solutions up to ±100A or ±80V
- 1pA resolution enables precise measurement of very low leakage currents
- 1µs per point (1MHz),
  18-bit sampling, accurately
  characterizes transient behavior
- 1% to 100% pulse duty cycle for pulse width modulated (PWM) drive schemes and devicespecific drive stimulus
- Combines a precision power supply, current source, DMM, arbitrary waveform generator, V or I pulse generator with measurement, electronic load, and trigger controller—all in one instrument
- Includes TSP<sup>®</sup> Express I-V characterization software, LabVIEW<sup>®</sup> driver, and Keithley's Test Script Builder software development environment

# **APPLICATIONS**

- Power semiconductor, HBLED, and optical device characterization and testing
- Characterization of GaN, SiC, and other compound materials and devices
- Semiconductor junction temperature characterization
- High speed, high precision digitization
- Electromigration studies
- High current, high power device testing

# 50A, High Power System SourceMeter<sup>®</sup> Instrument



The high power Model 2651A is the newest addition to the Series 2600A family of System SourceMeter instruments. Specifically designed to characterize and test high power electronics, these source measurement unit (SMU) instruments can help you improve productivity in applications across the R&D, reliability, and production spectrums, including high brightness LEDs, power semiconductors, DC-DC converters, batteries, and other high power materials, components, modules, and subassemblies.

The Model 2651A, like every Series 2600A SourceMeter instrument, offers a highly flexible, fourquadrant voltage and current source/load coupled with precision voltage and current meters. It can be used as a:

- Semiconductor characterization instrument
- V or I waveform generator
- V or I pulse generator
- · Precision power supply
- True current source
- Digital multimeter (DCV, DCI, ohms, and power with 61/2-digit resolution)
- Precision electronic load



The Model 2651A can source or sink up to  $\pm$ 40V and  $\pm$ 50A.

# Two Measurement Modes: Digitizing or Integrating

Precisely characterize transient and steady-state behavior, including rapidly changing thermal effects, with the two measurement modes in the Model 2651A. Each mode is defined by its independent analog-to-digital (A/D) converters.

The Digitizing Measurement mode enables 1 $\mu$ s per point measurements. Its 18-bit A/D converters allow you to precisely measure transient characteristics. For more accurate measurements, use its Integrating Measurement mode, which is based on 22-bit A/D converters. The Integrating Measurement mode is provided in all Series 2600A instruments.



# Ordering information

2651A High Power System SourceMeter® Instrument

# **Accessories Supplied**

2651A-KIT-1A: Low Impedance Cable Assembly (1m) CS-1592-2: High Current Phoenix Connector (male) CS-1626-2: High Current Phoenix Connector (female) CA-557-1: Sense Line Cable Assembly (1m) 7709-308A: Digital I/O Connector CA-180-3A: TSP-Link/Ethernet Cable Documentation CD Software Tools and Drivers CD

# ACCESSORIES AVAILABLE

| 2600-KIT  | Low Impedance CAble Assemble, 1m (3.3 ft) |
|-----------|---|
| ACS-BASIC | Component Charaterization Software        |
| 4299-6    | Rack Mount Kit                            |
| 8011      | Test Socket Kit                           |

Two A/D converters are used with each measurement mode (one for current and the other for voltage), which run simultaneously for accurate source readback that does not sacrifice test throughput.



The dual digitizing A/D converters sample at up to 1µs/point, enabling full simultaneous characterization of both current and voltage waveforms.

# **High Speed Pulsing**

The Model 2651A minimizes the unwanted effects of self heating during tests by accurately sourcing and measuring pulses as short as  $100\mu s$ . Additional control flexibility enables you to program the pulse width from  $100\mu s$  to DC and the duty cycle from 1% to 100%. A single

1.888.KEITHLEY (U.S. only) www.keithley.com

# 50A, High Power System SourceMeter<sup>®</sup> Instrument

unit can pulse up to 50A; combine two units to pulse up to 100A.

# **Expansion Capabilities**

Through TSP-Link<sup>®</sup> technology, multiple Model 2651As and other Series 2600A instruments can be combined to form a larger integrated system with up to 64 channels. Precision timing and tight channel synchronization are guaranteed with built-in 500ns trigger controllers. True SMU instrument-per-pin testing is assured with the fully isolated, independent channels of the SourceMeter instruments.



Keithley's TSP and TSP-Link technology enables true SMU-per-pin testing without the power and/or channel limitations of a mainframe-based system.

Also, when two Model 2651As are connected in parallel with TSP-Link technology, the current range is expanded from 50A to 100A. When two units are connected in series, the voltage range is expanded from 40V to 80V. Built-in intelligence simplifies testing by enabling the units to be addressed as a single instrument, thus creating an industry-best dynamic range (100A to 1pA). This capability enables you to test a much wider range of power semiconductors and other devices.



Precision measurements to 50A (100A with two units) enable a more complete and accurate characterization.



1µV measurement resolution and current sourcing up to 50A (100A with two units) enable low-level Rds measurements to support next-generation devices.

# Standard Capabilities of Series 2600A Instruments

Each Model 2651A includes all the features and capabilities provided in the other Series 2600A instruments, such as:

- Ability to be used as either a bench-top I-V characterization tool or as a building block component of multiple-channel I-V test systems
- TSP Express software to quickly and easily perform common I-V tests without programming or installing software
- ACS Basic Edition software for semiconductor component characterization (optional).
   ACS Basic now features a Trace mode for generating a suite of characteristic curves.
- Keithley's Test Script Processor (TSP<sup>®</sup>), which enables creation of custom user test scripts to further automate testing, and also supports the creation of programming sequences that allow the instrument to operate asynchronously without direct PC control.
- Parallel test execution and precision timing when multiple Series 2600A instruments are connected together in a system
- LXI Class C compliance
- 14 digital I/O lines for direct interaction with probe stations, component handlers, or other automation tools
- USB port for extra data and test program storage via USB memory device

**SMU INSTRUMENTS** 



# 50A, High Power System SourceMeter<sup>®</sup> Instrument

# **Specification Conditions**

This document contains specifications and supplemental information for the Model 2651A High Power System SourceMeter instrument. Specifications are the standards against which the Model 2651A is tested. Upon leaving the factory, the Model 2651A meets these specifications. Supplemental and typical values are non-warranted, apply at 23°C, and are provided solely as useful information.

Accuracy specifications are applicable for both normal and high-capacitance modes.

Source and measurement accuracies are specified at the Model 2651A terminals under these conditions:

MEASURE

- $23^{\circ} \pm 5^{\circ}$ C, <70 percent relative humidity
- · After two-hour warm-up
- Speed normal (1 NPLC)
- A/D autozero enabled
- · Remote sense operation or properly zeroed local operation
- · Calibration period: One year

| VOLTAGE ACCURACY SPECIFICATIONS 1, 2 |                           |                                  |  |                                  |   |  |  |  |
|--------------------------------------|---------------------------|----------------------------------|--|----------------------------------|---|--|--|--|
|                                      |                           | SOURCE                           |  | MEASURE                          |   |  |  |  |
| Range                                | Programming<br>Resolution | Accuracy<br>±(% reading + volts) | Noise (Vpp) (typical)<br>0.1 Hz to 10 Hz | Default<br>Display<br>Resolution | Integrating ADC Accuracy <sup>3</sup><br>±(% reading + volts) | High-Speed ADC Accuracy⁴<br>±(% reading + volts) |  |  |
| 100.000 mV                           | 5 μV                      | $0.02\% + 500 \ \mu V$           | 100 µV                                   | 1 µV                             | $0.02\% + 300 \ \mu V$  | $0.05\% + 600 \ \mu V$                           |  |  |
| 1.00000 V                            | 50 µV                     | $0.02\% + 500 \ \mu V$           | 500 µV                                   | $10 \mu V$                       | $0.02\% + 300 \ \mu V$  | $0.05\% + 600 \ \mu V$                           |  |  |
| 10.0000 V                            | 500 μV                    | 0.02% + 5  mV                    | 1 mV                                     | $100 \mu\text{V}$                | 0.02% + 3 mV  | 0.05% + 8 mV                                     |  |  |
| 20.0000 V                            | 500 μV                    | 0.02% + 5  mV                    | 1 mV                                     | $100 \mu\text{V}$                | 0.02% + 5  mV   | 0.05% + 8 mV                                     |  |  |
| 40.0000 V                            | 500 μV                    | 0.02% + 12  mV                   | 2 mV                                     | $100 \mu\text{V}$                | 0.02% + 12 mV   | 0.05% + 15 mV                                    |  |  |

### **CURRENT ACCURACY SPECIFICATIONS 5** SOURCE

| Range             | Programming<br>Resolution | Accuracy<br>±(% reading + amps) | Noise (Ipp) (typical)<br>0.1Hz to 10Hz | Default<br>Display<br>Resolution | Integrating ADC Accuracy <sup>3</sup><br>±(% reading + amps) | High-Speed ADC Accuracy⁴<br>±(% reading + amps) |  |
|-------------------|---------------------------|---------------------------------|--|----------------------------------|--|---|--|
| 100.000 nA        | 2 pA                      | 0.1 % + 500 pA                  | 50 pA                                  | 1 pA                             | 0.08% + 500 pA   | 0.08% + 800 pA                                  |  |
| 1.00000 µA        | 20 pA                     | 0.1 % + 2 nA                    | 250 pA                                 | 10 pA                            | 0.08% + 2 nA   | 0.08% + 4 nA                                    |  |
| $10.0000 \ \mu A$ | 200 pA                    | 0.1 % + 10 nA                   | 500 pA                                 | 100 pA                           | 0.08% + 8 nA   | 0.08% + 10 nA                                   |  |
| 100.000 $\mu$ A   | 2 nA                      | 0.03% + 60 nA                   | 5 nA                                   | 1 nA                             | 0.02% + 25 nA  | 0.05% + 60 nA                                   |  |
| 1.00000 mA        | 20 nA                     | 0.03% +300 nA                   | 10 nA                                  | 10 nA                            | 0.02% + 200 nA   | 0.05% + 500 nA                                  |  |
| 10.0000 mA        | 200 nA                    | $0.03\% + 8 \mu A$              | 500 nA                                 | 100 nA                           | $0.02\% + 2.5 \mu A$   | $0.05\% + 10 \mu A$                             |  |
| 100.000 mA        | 2 µA                      | $0.03\% + 30 \mu A$             | $1 \mu\text{A}$                        | $1 \mu$ A                        | $0.02\% + 20 \mu A$  | $0.05\% + 50 \mu A$                             |  |
| 1.00000 A         | 200 µA                    | 0.08% + 3.5 mA                  | 300 µA                                 | $10 \mu\text{A}$                 | 0.05% + 3 mA   | 0.05% + 5 mA                                    |  |
| 5.00000 A         | 200 µA                    | 0.08% + 3.5 mA                  | 300 µA                                 | $10 \mu\text{A}$                 | 0.05% + 3 mA   | 0.05% + 5 mA                                    |  |
| 10.0000 A         | 500 μA                    | 0.15% + 6 mA                    | 500 µA                                 | $100 \mu\text{A}$                | 0.12% + 6 mA   | 0.12% + 12 mA                                   |  |
| 20.0000 A         | 500 μA                    | 0.15% + 8 mA                    | 500 µA                                 | $100 \mu\text{A}$                | 0.08% + 8 mA   | 0.08% + 15 mA                                   |  |
| 50.0000 A 6       | 2 mA                      | 0.15% + 80 mA                   | N/A                                    | $100 \mu\text{A}$                | $0.05\% + 50 \text{ mA}^7$                                   | 0.05% + 90 mA <sup>8</sup>                      |  |

### NOTES

Model 2651A specifications

1. Add 50µV to source accuracy specifications per volt of HI lead drop.

2. For temperatures 0° to 18°C and 28° to 50°C, accuracy is degraded by  $\pm (0.15 \times \text{accuracy specification})/°C$ .

High-capacitance mode accuracy is applicable at 23° ±5°C only.

Derate accuracy specification for NPLC setting <1 by increasing error term. Add appropriate typical percent of range term for resistive loads using the table below.

|              |             | -                | -           |                     |                  |
|--------------|-------------|------------------|-------------|---------------------|------------------|
| NPLC Setting | 100mV Range | 1V to 40V Ranges | 100nA Range | 1µA to 100mA Ranges | 1A to 20A Ranges |
| 0.1          | 0.01%       | 0.01%            | 0.01%       | 0.01%               | 0.01%            |
| 0.01         | 0.08%       | 0.07%            | 0.1 %       | 0.05%               | 0.1 %            |
| 0.001        | 0.8 %       | 0.6 %            | 1 %         | 0.5 %               | 1.8 %            |
|              |             |                  |             |                     |                  |

18-bit ADC. Average of 1000 samples taken at  $1\mu s$  intervals.

At temperatures 0° to 18°C and 28° to 50°C; 100nA to 10 $\mu$ A accuracy is degraded by ±(0.35 × accuracy specification)/°C. 100 $\mu$ A to 50A accuracy is degraded by ±(0.15 × accuracy specification)/°C. High-capacitance mode accuracy is applicable at 23° ±5°C only.

50A range accessible only in pulse mode.

50A range accuracy measurements are taken at 0.008 NPLC.

8. Average of 100 samples taken at  $1\mu s$  intervals.





# 50A, High Power System SourceMeter® Instrument

### **DC POWER SPECIFICATIONS**

MAXIMUM OUTPUT POWER: 202W maximum. SOURCE/SINK LIMITS <sup>1</sup>:

- **Voltage:**  $\pm 10.1$ V at  $\pm 20.0$ A,  $\pm 20.2$ V at  $\pm 10.0$ A,  $\pm 40.4$ V at  $\pm 5.0$ A<sup>2</sup>. Four-quadrant source or sink operation.
- **Current:**  $\pm 5.05$ A at  $\pm 40V^2$ ,  $\pm 10.1$ A at  $\pm 20V$ ,  $\pm 20.2$ A at  $\pm 10V$ Four surdanate source of side of points.

Four-quadrant source or sink operation.

**CAUTION:** Carefully consider and configure the appropriate output-off state and source and compliance levels before connecting the Model 2651A to a device that can deliver energy. Failure to consider the output-off state and source and compliance levels may result in damage to the instrument or to the device under test.

# PULSE SPECIFICATIONS

MINIMUM PROGRAMMABLE PULSE WIDTH <sup>3</sup>: 100µs. Note: Minimum pulse width for settled source at a given I/V output and load can be longer than 100µs.

PULSE WIDTH PROGRAMMING RESOLUTION:  $1\mu s$ .

PULSE WIDTH PROGRAMMING ACCURACY 3: ±5µs.

PULSE WIDTH JITTER: 2µs (typical).

PULSE RISE TIME (TYPICAL):

| Current Range | <b>R</b> <sub>load</sub> | Rise Time (typical) |
|---------------|--------------------------|---------------------|
| 50 A          | 0.05 Ω                   | 26 µs               |
| 50 A          | 0.2 Ω                    | 57 µs               |
| 50 A          | $0.4 \Omega$             | 85 µs               |
| 20 A          | 0.5 Ω                    | 95 µs               |
| 50 A          | 0.8 Ω                    | 130 µs              |
| 20 A          | 1 Ω                      | $180 \mu s$         |
| 10 A          | 2 Ω                      | 330 µs              |
| 5 A           | 8.2 Ω                    | $400 \mu s$         |

1.888.KEITHLEY (U.S. only) www.keithley.com



| Region | Region<br>Maximums | Maximum<br>Pulse Width <sup>3</sup> | Maximum<br>Duty Cycle ⁴ |
|--------|--------------------|-------------------------------------|-------------------------|
| 1      | 5 A at 40 V        | DC, no limit                        | 100%                    |
| 1      | 10 A at 20 V       | DC, no limit                        | 100%                    |
| 1      | 20 A at 10 V       | DC, no limit                        | 100%                    |
| 2      | 30 A at 10 V       | 1 ms                                | 50%                     |
| 3      | 20 A at 20 V       | 1.5 ms                              | 40%                     |
| 4      | 10 A at 40 V       | 1.5 ms                              | 40%                     |
| 5      | 50 A at 10 V       | 1 ms                                | 35%                     |
| 6      | 50 A at 20 V       | 330 µs                              | 10%                     |
| 7      | 50 A at 40 V       | 300 µs                              | 1%                      |

NOTES

1. Full power source operation regardless of load to 30°C ambient. Above 30°C or power sink operation, refer to

"Operating Boundaries" in the Model 2651A Reference manual for additional power derating information.

Quadrants 2 and 4 power envelope is trimmed at 36V and 4.5A.
 Times measured from the start of pulse to the start off-time; see figure below.

Pulse Level



Thermally limited in sink mode (quadrants 2 and 4) and ambient temperatures above 30°C. See power equations in the Model 2651A Reference Manual for more information.



The Model 2651A supports GPIB, LXI, Digital I/O, and Keithley's TSP-Link for multi-channel synchronization.



A GREATER MEASURE OF CONFIDENCE

# 50A, High Power System SourceMeter<sup>®</sup> Instrument

# ADDITIONAL SOURCE SPECIFICATIONS

NOISE (10Hz to 20MHz): <100mV peak-peak (typical), <30mV RMS (typical), 10V range with a 20A limit.

#### **OVERSHOOT**:

Voltage:  $<\pm(0.1\% + 10\text{mV})$  (typical). Step size = 10% to 90% of range, resistive load, maximum current limit/compliance.

Current:  $<\pm(0.1\% + 10mV)$  (typical). Step Size = 10% to 90% of range, resistive load. See Current Source Output Settling Time specifications for additional test conditions

#### RANGE CHANGE OVERSHOOT: Vo

| oltage: | <300mV | + 0.1% | of larger | range (for | <20V | ranges) | (typical |
|---------|--------|--------|-----------|------------|------|---------|----------|
|---------|--------|--------|-----------|------------|------|---------|----------|

<400mV + 0.1% of larger range (for ≥20V ranges) (typical).

Overshoot into a  $100k\Omega$  load, 20MHz bandwidth.

Current: <5% of larger range + 360 mV/R<sub>load</sub> (for >10 $\mu$ A ranges) (typical). I<sub>out</sub> × R<sub>load</sub> = 1V. VOLTAGE SOURCE OUTPUT SETTLING TIME: Time required to reach within 0.1% of final value

after source level command is processed on a fixed range.

### Range Settling Time (typical)

| -    | -    |      |  |
|------|------|------|--|
| 1 V  | < 70 | ) μs |  |
| 10 V | <160 | ) µs |  |
| 20 V | <190 | ) μs |  |
| 40 V | <175 | iμs  |  |
|      |      |      |  |

CURRENT SOURCE OUTPUT SETTLING TIME: Time required to reach within 0.1% of final value after source level command is processed on a fixed range. Values below for Iout × Rload

| Current Range | <b>R</b> <sub>load</sub> | Settling time (typical) |
|---------------|--------------------------|-------------------------|
| 20 A          | 0.5 Ω                    | <195 µs                 |
| 10 A          | 1.5 Ω                    | <540 µs                 |
| 5 A           | 5Ω                       | <560 µs                 |
| 1 A           | 1 Ω                      | $< 80 \ \mu s$          |
| 100 mA        | 10 Ω                     | $< 80 \ \mu s$          |
| 10 mA         | 100 Ω                    | <210 µs                 |
| 1 mA          | 1 kΩ                     | <300 µs                 |
| $100 \ \mu A$ | 10 kΩ                    | <500 µs                 |
| 10 µA         | 100 kΩ                   | < 15 ms                 |
| $1 \mu A$     | $1 \mathrm{M}\Omega$     | < 35 ms                 |
| 100 nA        | 10 MO                    | <110 ms                 |

#### TRANSIENT RESPONSE TIME:

10V and 20V Ranges: <70µs for the output to recover to within 0.1% for a 10% to 90% step change in load.

40V Range: <110µs for the output to recover to within 0.1% for a 10% to 90% step change in load. GUARD OFFSET VOLTAGE: <4mV, current <10mA.

#### **REMOTE SENSE OPERATING RANGE 2:**

Maximum Voltage between HI and SENSE HI: 3V.

Maximum Voltage between LO and SENSE LO: 3V.

# MAXIMUM IMPEDANCE PER SOURCE LEAD:

Maximum impedance limited by 3V drop by remote sense operating range.

Maximum resistance = 3V/source current value (amperes) (maximum of  $1\Omega$  per source lead). 3V = L di/dt.

#### VOLTAGE OUTPUT HEADROOM:

5A Range: Maximum output voltage = 48.5V – (Total voltage drop across source leads). 10A Range: Maximum output voltage = 24.5V - (Total voltage drop across source leads). 20A Range: Maximum output voltage = 15.9V – (Total voltage drop across source leads). OVERTEMPERATURE PROTECTION: Internally sensed temperature overload puts unit in

standby mode

LIMIT/COMPLIANCE: Bipolar limit (compliance) set with single value

Voltage<sup>3</sup>: Minimum value is 10mV: accuracy is the same as voltage source.

Current 4: Minimum value is 10nA; accuracy is the same as current source.

# NOTES

With measure and compliance set to the maximum current for the specified voltage range

- Add 50 µV to source accuracy specifications per volt of HI lead drop.
- For sink mode operation (quadrants II and IV), add 0.6% of limit range to the corresponding voltage source accuracy specifications. For 100mV range add an additional 60mV of uncertainty. Specifications apply with sink mode enabled.
- For sink mode operation (quadrants II and IV), add 0.6% of limit range to the corresponding current limit accuracy specifications. Specifications apply with sink mode enabled

### ADDITIONAL MEASUREMENT SPECIFICATIONS

#### CONTACT CHECK

| Speed  | Maximum Measurement<br>Time to Memory<br>for 60Hz (50Hz) | Accuracy (1 Year)<br>23°±5°C<br>±(% reading + ohms) |
|--------|--|---|
| Fast   | 1.1 ms (1.2 ms)  | 5% + 15 Ω   |
| Medium | 4.1 ms (5 ms)  | $5\% + 5 \Omega$                                    |
| Slow   | 36 ms (42 ms)  | $5\% + 3\Omega$                                     |

### NOTES

1. Includes measurement of SENSE HI to HI and SENSE LO to LO contact resistances

### ADDITIONAL METER SPECIFICATIONS

MAXIMUM LOAD IMPEDANCE:

Normal Mode: 10nF (typical), 3µH (typical). High-Capacitance Mode: 50µF (typical), 3µH (typical). COMMON MODE VOLTAGE: 250V DC.

COMMON MODE ISOLATION: >1GQ, <4500pF.

MEASURE INPUT IMPEDANCE: >10GΩ.

SENSE HIGH INPUT IMPEDANCE:  $>10G\Omega$ .

MAXIMUM SENSE LEAD RESISTANCE:  $1k\Omega$  for rated accuracy.

OVERRANGE: 101% of source range, 102% of measure range.

### **HIGH-CAPACITANCE MODE 1,2**

ACCURACY SPECIFICATIONS 3: Accuracy specifications are applicable in both normal and highcapacitance modes

VOLTAGE SOURCE OUTPUT SETTLING TIME: Time required to reach within 0.1 % of final value after source level command is processed on a fixed range.

| Voltage Source | Settling Time with                  |
|----------------|-------------------------------------|
| Range          | C <sub>load</sub> = 4.7µF (typical) |
| 1 V            | 75 µs                               |
| 10 V           | $170 \ \mu s$                       |
| 20 V           | 200 µs                              |
| 40 V           | 180 µs                              |

MODE CHANGE DELAY:

- 100 µA Current Range and Above: Delay into High-Capacitance Mode: 11ms. Delay out of High-Capacitance Mode: 11ms.
- 1 µA and 10 µA Current Ranges:
- Delay into High-Capacitance Mode: 250ms. Delay out of High-Capacitance Mode: 11ms.
- **MEASURE INPUT IMPEDANCE:** >10G $\Omega$  in parallel with 25nF.

VOLTAGE SOURCE RANGE CHANGE OVERSHOOT: <400mV + 0.1% of larger range (typical). Overshoot into a  $100k\Omega$  load, 20MHz bandwidth

#### NOTES

1. High-capacitance mode specifications are for DC measurements only and use locked ranges. Autorange is disabled

100nA range is not available in high-capacitance mode. 2

Add an additional 2nA to the source current accuracy and measure current accuracy offset for the 1µA range

With measure and compliance set to the maximum current for the specified voltage range



# 50A, High Power System SourceMeter<sup>®</sup> Instrument

# **MEASUREMENT SPEED SPECIFICATIONS 1, 2**

# MAXIMUM SWEEP OPERATION RATES (operations per second) FOR 60Hz (50Hz):

| A/D Converter<br>Speed | Trigger Origin | Measure<br>To Memory Using<br>User Scripts | Measure<br>To GPIB Using<br>User Scripts | Source Measure<br>To Memory Using<br>User Scripts | Source Measure<br>To GPIB Using<br>User Scripts | Source Measure<br>To Memory Using<br>Sweep API | Source Measure<br>To GPIB Using<br>Sweep API |
|------------------------|----------------|--|--|---|---|--|--|
| 0.001 NPLC             | Internal       | 20000 (20000)                              | 9800 (9800)                              | 7000 (7000)                                       | 6200 (6200)                                     | 12000 (12000)                                  | 5900 (5900)                                  |
| 0.001 NPLC             | Digital I/O    | 8100 (8100)                                | 7100 (7100)                              | 5500 (5500)                                       | 5100 (5100)                                     | 11200 (11200)                                  | 5700 (5700)                                  |
| 0.01 NPLC              | Internal       | 4900 (4000)                                | 3900 (3400)                              | 3400 (3000)                                       | 3200 (2900)                                     | 4200 (3700)                                    | 4000 (3500)                                  |
| 0.01 NPLC              | Digital I/O    | 3500 (3100)                                | 3400 (3000)                              | 3000 (2700)                                       | 2900 (2600)                                     | 4150 (3650)                                    | 3800 (3400)                                  |
| 0.1 NPLC               | Internal       | 580 (480)                                  | 560 (470)                                | 550 (465)   | 550 (460)                                       | 560 (470)                                      | 545 (460)                                    |
| 0.1 NPLC               | Digital I/O    | 550 (460)                                  | 550 (460)                                | 540 (450)   | 540 (450)                                       | 560 (470)                                      | 545 (460)                                    |
| 1.0 NPLC               | Internal       | 59 (49)                                    | 59 (49)                                  | 59 (49)   | 59 (49)   | 59 (49)  | 59 (49)                                      |
| 1.0 NPLC               | Digital I/O    | 58 (48)                                    | 58 (49)                                  | 59 (49)   | 59 (49)   | 59 (49)  | 59 (49)                                      |
| HS ADC                 | Internal       | 38500 (38500)                              | 18000 (18000)                            | 10000 (10000)                                     | 9500 (9500)                                     | 14300 (14300)                                  | 6300 (6300)                                  |
| HS ADC                 | Digital I/O    | 12500 (12500)                              | 11500 (11500)                            | 7500 (7500)                                       | 7000 (7000)                                     | 13200 (13200)                                  | 6000 (6000)                                  |

### **HIGH SPEED ADC BURST MEASUREMENT RATES 3**

| Burst Length<br>(readings) | Readings per<br>Second | Bursts per Second |
|----------------------------|------------------------|-------------------|
| 100                        | 1,000,000              | 400               |
| 500                        | 1,000,000              | 80                |
| 1000                       | 1,000,000              | 40                |
| 2500                       | 1,000,000              | 16                |
| 5000                       | 1,000,000              | 8                 |

# MAXIMUM SINGLE MEASUREMENT RATES (operations per second) FOR 60Hz (50Hz)

| A/D Converter<br>Speed | Trigger<br>Origin | Measure<br>To GPIB | Source<br>Measure<br>To GPIB | Source<br>Measure<br>Pass/Fail<br>To GPIB |
|------------------------|-------------------|--------------------|------------------------------|---|
| 0.001 NPLC             | Internal          | 1900 (1800)        | 1400 (1400)                  | 1400 (1400)                               |
| 0.01 NPLC              | Internal          | 1450 (1400)        | 1200 (1100)                  | 1100 (1100)                               |
| 0.1 NPLC               | Internal          | 450 (390)          | 425 (370)                    | 425 (375)                                 |
| 1.0 NPLC               | Internal          | 58 (48)            | 57 (48)                      | 57 (48)                                   |

MAXIMUM MEASUREMENT RANGE CHANGE RATE: >4000 per second for >10 $\mu$ A (typical).

MAXIMUM SOURCE RANGE CHANGE RATE: >325 per second for >10 $\mu$ A, typical. When changing to or from a range >1A, maximum rate is >250 per second, typical.

COMMAND PROCESSING TIME: Maximum time required for the output to begin to change following the receipt of the smua.source.levelv or smua.source.leveli command. <1ms typical.

### NOTES

 Tests performed with a Model 2651A on channel A using the following equipment: Computer hardware (Intel<sup>®</sup> Pentium<sup>®</sup> 4 2.4GHz, 2GB RAM, National Instruments<sup>™</sup> PCI-GPIB). Driver (NI-488.2 Version 2.2 PCI-GPIB). Software (Microsoft<sup>®</sup> Windows<sup>®</sup> XP, Microsoft Visual Studio<sup>®</sup> 2010, VISA<sup>™</sup> version 4.1).

2. Exclude current measurement ranges less than 1mA.

3. smua.measure.adc has to be enabled and the smua.measure.count set to the burst length.

# TRIGGERING AND SYNCHRONIZATION SPECIFICATIONS

#### TRIGGERING:

**Trigger In to Trigger Out:** 0.5µs (typical). **Trigger In to Source Change**<sup>1</sup>: 10µs (typical).

**Trigger Timer Accuracy:**  $\pm 2\mu s$  (typical).

Source Change <sup>1</sup> After LXI Trigger: 280µs (typical).

SYNCHRONIZATION:

Single-Node Synchronized Source Change <sup>1</sup>: <0.5µs (typical). Multi-Node Synchronized Source Change <sup>1</sup>: <0.5µs (typical).

### NOTES

1. Fixed source range with no polarity change.





# 50A, High Power System SourceMeter<sup>®</sup> Instrument

# SUPPLEMENTAL INFORMATION

FRONT PANEL INTERFACE: Two-line vacuum fluorescent display (VFD) with keypad and navigation wheel.

#### DISPLAY-

- Show error messages and user defined messages Display source and limit settings • View measurements stored in dedicated
- Show current and voltage measurements (61/2-digit to 41/2-digit)

### **KEYPAD OPERATIONS:**

- Change host interface settings
- · Save and restore instrument setups

• Load and run factory and user defined test scripts that prompt for input and send results to the display

reading buffers

Store measurements into dedicated reading buffers

PROGRAMMING: Embedded Test Script Processor (TSP®) scripting engine is accessible from any host interface.

- · Responds to individual instrument control commands.
- Responds to high speed test scripts comprised of instrument control commands and Test
- Script Language (TSL) statements (for example, branching, looping, and math).

# Able to execute high speed test scripts stored in memory without host intervention.

MINIMUM USER MEMORY AVAILABLE: 16MB (approximately 250,000 lines of TSP code).

#### TEST SCRIPT BUILDER: Integrated development environment for building, running, and managing TSP scripts. Includes an instrument console for communicating with any TSP enabled

- instrument in an interactive manner. Requires:
- VISA (NI-VISA included on CD)
- Microsoft® .NET Framework (included on CD)
- . Keithley I/O Layer (included on CD)
- Intel® Pentium III 800MHz or faster personal computer
- Microsoft Windows® 2000, XP, Vista®, or 7

#### TSP EXPRESS (embedded): Tool that allows users to quickly and easily perform common I-V tests without programming or installing software. To run TSP Express, you need:

- Java<sup>™</sup> Platform, Standard Edition 6
- Microsoft Internet Explorer®, Mozilla® Firefox®, or another Java-compatible web browser
- SOFTWARE INTERFACE: TSP Express (embedded), direct GPIB/VISA, read/write with Microsoft Visual Basic<sup>®</sup>, Visual C/C++<sup>®</sup>, Visual C#<sup>®</sup>, LabVIEW<sup>™</sup>, CEC TestPoint<sup>™</sup> Data Acquisition Software Package, NI LabWindows™/CVI, etc.
- READING BUFFERS: Nonvolatile memory uses dedicated storage areas reserved for measurement data. Reading buffers are arrays of measurement elements. Each element can hold the following items
  - Measurement
    - · Source setting (at the time the measurement was taken) Range information
  - · Measurement status Timestamp
- Two reading buffers are reserved for each Model 2651A channel. Reading buffers can be filled using the front panel STORE key and retrieved using the RECALL key or host interface.

### Buffer Size, with timestamp and source setting: >60,000 samples.

Buffer Size, without timestamp and source setting: >140.000 samples

SYSTEM EXPANSION: The TSP-Link expansion interface allows TSP-enabled instruments to trigger and communicate with each other. See figure below.



Each Model 2651A has two TSP-Link connectors to make it easier to connect instruments together in sequence.

- Once source-measure instruments are interconnected through the TSP-Link expansion interface, a computer can access all of the resources of each source-measure instrument through the host interface of any Model 2651A
- A maximum of 32 TSP-Link nodes can be interconnected. Each source-measure instrument consumes one TSP-Link node.
- TIMER: Free-running 47-bit counter with 1MHz clock input. Resets each time instrument power is turned on. If the instrument is not turned off, the timer is reset to zero every 4 years. Timestamp: TIMER value is automatically saved when each measurement is triggered.

Resolution: 1µs. Timestamp Accuracy: ±100ppm.

# 1.888.KEITHLEY (U.S. only) www.keithley.com



STORAGE: -25° to 65°C



Model 2651A specifications

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Keithley Instruments, Inc.: 2651A