



This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



SPECIFICATIONS

TUSONIX PART NO.	538-006 F 15.0 - 60
Capacitance Range:	15 - 60 pF
Capacitance Tolerance:	MIN: +10% , MAX: -10%+100%
Temperature Characteristic:	DIELECTRIC CODE F
Working Voltage:	200 VDC AT +85°C 100 VDC AT +125°C
Operating Temperature Range:	-55°C TO + 125°C
To Tusonix Spec Unless Stated Otherwise	

NOTES:

1. TUSONIX STANDARD
PART NUMBER: 0538 006 F 15.0-60.
TUSONIX RoHS COMPLIANT
PART NUMBER: 0538 006 F 15.0-60 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. ALL METAL PARTS SILVER PLATED.
3. PART MARKING: TUSONIX TRADEMARK, CAPACITANCE RANGE, AND DIELECTRIC CODE; STANDARD PART, BLACK INK; RoHS PART, GREEN INK.

X-2015 Rev-0

REVISION RECORD											
Original Release C.O. 20020919-3-01		0									
DIM'S IN METRIC, & NOTES 1-3 ADDED L.E. 04-11-06											
20060406-2-05		1									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tusonix:

[0538-006-F-15.0-60LF](#)