




MARKETING SALES DRAWING


Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTE:
ALL METAL PARTS SILVER PLATED.

FOR DIMENSIONS ≤ .125"/3.18mm,
TOLERANCE IS ±.015"/0.38mm.
FOR DIMENSIONS ≥ .126"/3.20mm,
TOLERANCE IS ±.030"/0.76mm.



SPECIFICATIONS

TUSONIX PART NO.	538-011 A 5.5 - 18
Value	5.5 - 18pF
Value Tol.	MIN. + 10%, MAX. -10% +100%
Dielectric Type Code	A
Rating	350 VDC @ +85°C, 200 VDC @ 125°C
Operating Temperature Range:	-55°C TO + 125°C
To Tusonix Spec Unless Stated Otherwise	

X-2015 Rev-0

REVISION RECORD

0	Original Release
1	METRIC DIM'S 0.81 & 0.76 ADDED L.E. 06-03-03
20030530-1-04	

TOLERANCES
unless otherwise specified

2 PLC.
DECIMAL ±

3 PLC.
DECIMAL ±

ANGLES ± 10°

TUSONIX
TUCSON, ARIZONA

Title

**CERAMIC
TRIMMER**

Drawn S.M. 05-08-03

Scale X

Approved T.C. 05-08-03

A

538-011 A 5.5-18

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tusonix:

[0538-011-A-5.5-18LF](#)