

SERIES 2000 ANTENNAS

Check for Samples: [RI-ANT-G01E](#), [RI-ANT-G02E](#), [RI-ANT-S01C](#), [RI-ANT-S02C](#)

FEATURES

- **Best in Class Performance Through Patented HDX Technology**
- **Protection Class IP 65 and Higher**
- **Four Form Factors Available**
- **Proven in Harsh Industrial Environments**
- **Easy to Install and Use**

APPLICATIONS

- **Access Control**
- **Vehicle Identification**
- **Container Tracking**
- **Asset Management**
- **Waste Management**

DESCRIPTION

These antenna products connect to radio frequency modules (RFM) and reader/writers to form the interface to the low-frequency (LF) 134.2-kHz Texas Instruments transponders. In combination with a reader/writer, they transmit energy and signals to the transponder and receive the response from the tag. There are two standard gate antennas and two standard stick antennas with 1-meter or 3-meter cable length. Each antenna generates a specific size and shape of read zone to meet the requirements of the target application. In general, the gate antennas generate a large read zone with greater distance, while the stick antennas provide a more focused read zone and an ability to discriminate between transponders.

The antennas are well suited for use in a broad range of applications including access control, vehicle identification, container tracking, asset management, and waste management applications.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

Gate Antennas – Specifications

Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)

	RI-ANT-G01E	RI-ANT-G02E	UNIT
Operating Temperature	–30 to +60	–30 to +60	°C
Storage Temperature	–40 to +70	–40 to +70	°C

Operating Characteristics

over operating free-air temperature range (unless otherwise noted)

PARAMETER	RI-ANT-G01E	RI-ANT-G02E	UNIT
Inductance (typical), at 134.2 kHz	27	27	μH
Protection Class	IP 65	IP 65	
Vibration	Mil-Std-810E, Test 514.4 (Category 1, Procedure 1; Basic transportation)		
Case Material	UVSHIPS (UV-Stabilized High Impact Polystyrol)		
Dimensions	715 ± 5 × 270 ± 3 × 25 ± 1	200 ± 3 × 200 ± 3 × 25 ± 1	mm
Weight (typical)	745	425	g
Cable Length	1	1	m
Connection Terminals	Spade and tongue, stud hole 3.5 mm, width 7.5 mm		
Mounting	Use nonmetallic clamps, standard screws, and washers through 6.5-mm predrilled holes, so that the screw hole is flush with the mounting. Mounting material is not supplied with the antenna.		

Stick Antennas – Specifications

Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)

	RI-ANT-S01C	RI-ANT-S02C	UNIT
Operating Temperature	–30 to +70	–30 to +70	°C
Storage Temperature	–40 to +85	–40 to +85	°C

Operating Characteristics

over operating free-air temperature range (unless otherwise noted)

PARAMETER	RI-ANT-S01C	RI-ANT-S02C	UNIT
Inductance (typical), at 134.2 kHz	27	27	μH
Protection Class	IP 66	IP 66	
Vibration	Mil-Std-810E, Test 514.4 (Category 1, Procedure 1; Basic transportation)		
Case Material	Glass reinforced epoxy (gray)		
Dimensions	140 ± 2 × 21 ± 2 (dia.)	140 ± 2 × 21 ± 2 (dia.)	mm
Weight (typical)	134	185	g
Cable Length	1	3	m
Connection Terminals	Ring lugs: 3.5-mm inside diameter 7.5-mm outside diameter	Ring lugs: 3.5-mm inside diameter 7.5-mm outside diameter	
Mounting	Use nonmetal clamps. Mounting material is not supplied with the antenna.		

Readout Pattern of Ferrite Rod (Stick) and Gate Antennas




Figure 1. Readout Pattern of Antennas

REVISION HISTORY

REVISION	CHANGES
SCBS845	First release
SCBS845A	Removed all information about RI-ANT-G04E and RI-ANT-P02A (obsolete)

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead/Ball Finish (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
RI-ANT-G01E-30	NRND			0	1	TBD	Call TI	Call TI	-30 to 60		
RI-ANT-S01C-30	OBSOLETE			0		TBD	Call TI	Call TI	-30 to 70		
TRPGR30ATGA	ACTIVE	RFIDT	TGA	0	2000	Pb-Free (RoHS)	Call TI	N / A for Pkg Type	-25 to 70		Samples
TRPGR30ATGB	ACTIVE	RFIDT	TGB	0	2000	Pb-Free (RoHS)	Call TI	N / A for Pkg Type	-25 to 70		Samples
TRPGR30ENATGA	ACTIVE	RFIDT	TGA	0	2000	Pb-Free (RoHS)	Call TI	N / A for Pkg Type	-25 to 70		Samples
TRPGR30ENATGB	ACTIVE	RFIDT	TGB	0	2000	Pb-Free (RoHS)	Call TI	N / A for Pkg Type	-25 to 70		Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

IMPORTANT NOTICE

Texas Instruments Incorporated (TI) reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

TI's published terms of sale for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>) apply to the sale of packaged integrated circuit products that TI has qualified and released to market. Additional terms may apply to the use or sale of other types of TI products and services.

Reproduction of significant portions of TI information in TI data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such reproduced documentation. Information of third parties may be subject to additional restrictions. Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyers and others who are developing systems that incorporate TI products (collectively, "Designers") understand and agree that Designers remain responsible for using their independent analysis, evaluation and judgment in designing their applications and that Designers have full and exclusive responsibility to assure the safety of Designers' applications and compliance of their applications (and of all TI products used in or for Designers' applications) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to their applications, Designer has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any applications that include TI products, Designer will thoroughly test such applications and the functionality of such TI products as used in such applications.

TI's provision of technical, application or other design advice, quality characterization, reliability data or other services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using TI Resources in any way, Designer (individually or, if Designer is acting on behalf of a company, Designer's company) agrees to use any particular TI Resource solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

Designer is authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNER AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

Unless TI has explicitly designated an individual product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949 and ISO 26262), TI is not responsible for any failure to meet such industry standard requirements.

Where TI specifically promotes products as facilitating functional safety or as compliant with industry functional safety standards, such products are intended to help enable customers to design and create their own applications that meet applicable functional safety standards and requirements. Using products in an application does not by itself establish any safety features in the application. Designers must ensure compliance with safety-related requirements and standards applicable to their applications. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

TI may expressly designate certain products as completing a particular qualification (e.g., Q100, Military Grade, or Enhanced Product). Designers agree that it has the necessary expertise to select the product with the appropriate qualification designation for their applications and that proper product selection is at Designers' own risk. Designers are solely responsible for compliance with all legal and regulatory requirements in connection with such selection.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Texas Instruments:](#)

[RI-ANT-G01E-30](#)