





Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTE:
ALL METAL PARTS SILVER PLATED.



FOR DIMENSIONS $\leq .125"/3.18\text{mm}$,
TOLERANCE IS $\pm .015"/0.38\text{mm}$.
FOR DIMENSIONS $\geq .126"/3.20\text{mm}$,
TOLERANCE IS $\pm .030"/0.76\text{mm}$.



ORDERING INFORMATION

Part No.	538-011 F 15.0-60
Value	15.0 - 60pF
Value Tol.	MIN. +10%, MAX. -10% +100%
Dielectric Type Code	F
Rating	200 WVDC @ 85°, 100 WVDC @ 125°C
Operating Temperature Range:	-55°C TO + 125°C
To Tusonix Spec Unless Stated Otherwise	

X-2015 Rev-0

REVISION RECORD	Original Release	0	METRIC DIM'S & ORIENTATION SYMBOL CIRCUIT & NOTES ADDED L.E. 06-03-03	1	20030530-1-03	TOLERANCES unless otherwise specified		Title CERAMIC TRIMMER					
	C.O. 19990913-2-01					2 PLC. DECIMAL ± 							
						3 PLC. DECIMAL ± 							
						ANGLES ± 10°	Drawn	S.M. 09-14-99	Scale	2 X			
						TUSONIX TUCSON, ARIZONA		Approved E.F. 09-14-99					
								A	538-011 F 15.0-60				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tusonix:

[0538-011-F-15.0-60LF](#)