


This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING

DIMENSIONS IN METRIC - []

ALL METAL PARTS SILVER PLATED




ORIENTATION



CIRCUIT

**Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.**



SPECIFICATIONS

TUSONIX STYLE	538-054
Capacitance Range:	8.0 - 25 pF
Capacitance Tolerance:	MIN: +0% , MAX: -0, +50%
Temperature Characteristic:	DIELECTRIC CODE C
Working Voltage:	350 VDC AT + 85°C
Operating Temperature Range:	-55°C TO + 125°C
To MIL - C - 81/4E CV31C250	

← .320 →
[8.13]

TYPICAL MOUNTING
HOLE LAYOUT

X-2015 Rev-0

REVISION RECORD

A
Original Release
C.O. ECO-669

TOLERANCES
unless otherwise specified

2 PLC.
DECIMAL ± //

3 PLC.
DECIMAL ± .010 [0.25]

ANGLES ± //

TUSONIX
TUCSON, ARIZONA

Title

**CERAMIC
TRIMMER**

Drawn L.E. 04-16-09

Scale 2 X

Approved R.L. 04-16-09

A

538-054 C 8.0 - 25

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tusonix:

[0538-054-C-8.0-25](#)