




MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.




MOUNTING HARDWARE



NOTES:

1. OPERATING TEMPERATURE RANGE: -55°C TO +125°C.
2. SILVER PLATED CASE AND MOUNTING HARDWARE, SILVER PLATED LEAD
3. MAX. RECOMMENDED MOUNTING TORQUE: 3.5 Lb.-IN.
4. MAX. RECOMMENDED SOLDERING TEMPERATURE: 260°C. SEE INSTALLATION RECOMMENDATIONS.
5. NUT AND LOCKWASHER INCLUDED.
6. TUSONIX TRADEMARK & PART VARIATION NUMBER STAMPED ON HEX FLATS.

4404		050		22,000		100		10A		7		17		27		34		43		50		60	
STYLE		VAR.		MIN. CAP.(pf)		125 °C		DC CURRENT (AMPS)		1 MHz		3 MHz		10 MHz		30 MHz		100 MHz		300 MHz		1GHz	
						DC WORKING VOLTAGE				MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220													
REVISION RECORD Original Release C.O. 950201-2 HARDWARE, NOTES & CAP CHART ADDED. S.M. 02-24-95 RE-ISSUE 950201-2 1 CHANGED LEAD DIM'S. S.M. 07-18-96 960718-2 REV'D T-050 WAS T-000 L.E. 09-15-97 970829-4 --TOLERANCES-- Unless Otherwise Specified DECIMAL ±  ANGLES ±  TUSONIX TUCSON, ARIZONA Title BUSHING STYLE EMI FILTER Drawn S.M. 02-14-95 Approved O.S. 02-14-95 A 4404-050																							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4404-050LF](#)