


SMD TCXO

2.5 x 2.0 x 0.8 mm

7L Series




Features

- Temperature Stability: $\pm 0.5 \text{ ppm} \sim \pm 2.0 \text{ ppm}$
- Operating Temperature Range: $-30^\circ\text{C} \sim 85^\circ\text{C}$
- Supply Voltage: $1.8 \text{ V} \sim 3.3 \text{ V}$
- Voltage Control Function Available
- Frequencies: 16.367667 MHz, 16.368 MHz, 16.369 MHz, 19.2 MHz, 26 MHz, 33.6 MHz, 38.4 MHz, 40 MHz
- Applications: GPS, WiMAX, Cellular and Wireless Communications
- RoHS Compliant / Pb Free

Electrical Specifications


Item / Type		7L
Output Type		Clipped Sinewave
Output Load		10K Ω // 10 pF
Oscillation Mode		Fundamental
Supply Voltage		1.8 ~ 3.3 V
Frequency Range		13 ~ 52 MHz
Clipped Sinewave Output Voltage		0.8 Vp-p typical
Frequency Stability	Vs. Temperature ($-30 \sim +85^\circ\text{C}$)	$\pm 0.5 / \pm 2.0 \text{ ppm}$
	Vs. Load (Load varies $\pm 10\%$)	$\pm 0.2 \text{ ppm Max.}$
	Vs. Supply Voltage ($V_{cc} = \text{Typical} \pm 0.1 \text{ V}$)	$\pm 0.2 \text{ ppm Max.}$
Frequency Tolerance	at 25°C after 2 Reflows with Typical Applied to Auto Frequency Control Pin	$\pm 2.5 \text{ ppm Max.}$
Slope of Frequency Drift		$\pm 0.1 \text{ ppm} / ^\circ\text{C}$ Typical ; $\pm 0.5 \text{ ppm} / ^\circ\text{C}$ Max.
Storage Temperature Range		$-40 \sim +85^\circ\text{C}$
Auto Frequency Control (AFC) Range (Center @ 1.4 V)		$\pm 7 \sim \pm 16 \text{ ppm} / \text{V}$
Supply Current		2.0 mA Max.
Start-up Time		5 ms Max.
Harmonics		- 5 dBc Max.
Phase Noise at 1 KHz offset		- 130 dBc / Hz
Aging (at 25°C)		$\pm 1 \text{ ppm} / \text{year Max.}$

Dimensions



Pin Connection

Name	Function
Pin 1	AFC
Pin 2	GND
Pin 3	OUTPUT
Pin 4	VCC



Units: mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[7L-16.368MCG-T](#) [7L-16.369MCG-T](#) [7L-19.200MCG-T](#) [7L-26.000MCG-T](#) [7L-38.400MCG-T](#) [7L-16.368MBG-T](#) [7L-16.368MDG-T](#) [7L-16.369MBG-T](#) [7L-16.369MDG-T](#) [7L-19.200MBG-T](#) [7L-19.200MBV-T](#) [7L-19.200MCV-T](#) [7L-19.200MDG-T](#) [7L-19.200MDV-T](#) [7L-26.000MBG-T](#) [7L-26.000MDG-T](#) [7L-38.400MBG-T](#) [7L-38.400MDG-T](#) [7L-40.000MDG-T](#) [7L-27.000MBG-T](#)