

Features

- Frequency range : 20MHz to 66MHz
- Ultra compact and thin
- AuSn sealing, ceramic SMD package
- External dimensions (mm)
L : 1.6 x W : 1.2 x H : 0.35
- RoHS compliant & Pb free

Applications

- BT, BLE, W-LAN, NFC
- SiP modules
- Mobile phone, Wearables
- Internet of Things (IoT)
- Portable consumer products


Electrical Characteristics

Item		8Q	Conditions
Frequency Range	F_0	20MHz ~ 66MHz	
Frequency Tolerance	F_{tol}	$\pm 30\text{ppm}$, $\pm 20\text{ppm}$, $\pm 10\text{ppm}$	at 25°C
Frequency Stability over Operating Temperature Range (refer to 25°C)	F_{stab}	$\pm 30\text{ ppm}$	-20°C ~ +70°C
		$\pm 20\text{ ppm}$	
		$\pm 10\text{ ppm}$	
		$\pm 10\text{ ppm}$	-30°C ~ +85°C
		$\pm 30\text{ ppm}$	-40°C ~ +85°C
		$\pm 20\text{ ppm}$	
		$\pm 60\text{ ppm}$	-40°C ~ +125°C
Operating Temperature Range	T_{OTR}	-20°C ~ +70°C	
		-40°C ~ +85°C	
		-40°C ~ +125°C	
Shunt Capacitance	C_0	3pF Max.	
Drive Level	D_L	1 ~ 200 μ W (50 μ W Typ.)	
Load Capacitance	C_L	6pF, 7pF, 8pF, 9pF, 10pF, 12pF, 16pF, 18pF	
Aging	F_{aging}	$\pm 3\text{ ppm Max.}$	at 25°C $\pm$ 3°C, first year
Storage Temperature Range	T_{STR}	-55°C ~ +125°C	


Motional Resistance (ESR)

Fundamental	
20 ~ 30 MHz	100 Ω Max.
30 ~ 66 MHz	80 Ω Max.


Dimensions



Ordering Information




Packing



Reflow Profile

Solder melting point : 220°C ± 10°C, 60 sec. Min.

Peak temperature : 260°C ± 10°C, 10 sec. Min.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[8Q-26.000MDDV-T](#) [8Q-24.000MAAV-T](#) [8Q-37.400MAAV-T](#) [8Q-26.000MAAV-T](#) [8Q-32.000MDDV-T](#) [8Q-24.000MDDV-T](#) [8Q-27.120MDDV-T](#) [8Q-32.000MAAV-T](#) [8Q-40.000MDDV-T](#) [8Q-27.120MAAV-T](#) [8Q-52.000MAAV-T](#) [8Q-40.000MAAV-T](#) [8Q-37.400MDDV-T](#) [8Q-40.000MAAQ-T](#) [8Q-37.400MDDE-T](#) [8Q-27.120MAAJ-T](#) [8Q-25.000MAHB-T](#) [8Q-38.400MAHY-T](#) [8Q-32.000MDDQ-T](#) [8Q-25.000MAAV-T](#) [8Q-25.000MAHI-T](#) [8Q-48.000MAAY-T](#) [8Q-27.1200MAHV-T](#) [8Q-48.000MAHV-T](#) [8Q-32.000MDDE-T](#) [8Q-25.000MDDV-T](#) [8Q-25.000MAAI-T](#) [8Q-38.400MDDY-T](#) [8Q-26.000MDDY-T](#) [8Q-38.400MAAC-T](#) [8Q-40.000MAAE-T](#) [8Q-38.400MAAQ-T](#) [8Q-32.000MAAQ-T](#) [8Q-48.000MAAQ-T](#) [8Q-26.000MAAC-T](#) [8Q-26.000MAAY-T](#) [8Q-37.400MAAI-T](#) [8Q-37.400MAAC-T](#) [8Q-24.000MAAE-T](#) [8Q-32.000MAHE-T](#) [8Q-48.000MDDQ-T](#) [8Q-38.400MAAY-T](#) [8Q-24.000MAHV-T](#) [8Q-32.000MAAE-T](#) [8Q-32.000MAHV-T](#) [8Q-37.400MAHI-T](#) [8Q-27.000MAAJ-T](#) [8Q-26.000MAAB-T](#) [8Q-26.000MAAI-T](#) [8Q-24.000MAAI-T](#) [8Q-40.000MAHQ-T](#) [8Q-26.000MAAE-T](#) [8Q-32.000MAHQ-T](#) [8Q-26.000MAHB-T](#) [8Q-27.120MAHQ-T](#) [8Q-27.120MDDQ-T](#) [8Q-37.400MAAE-T](#) [8Q-48.000MDDY-T](#) [8Q-26.000MDDE-T](#) [8Q-40.000MDDQ-T](#) [8Q-27.120MAAQ-T](#) [8Q-26.000MDDB-T](#) [8Q-24.000MDDQ-T](#) [8Q-38.400MDDQ-T](#) [8Q-24.000MAAQ-T](#) [8Q-25.000MAAB-T](#) [8Q-25.000MAAJ-T](#) [8Q-40.000MDDY-T](#) [8Q-50.000MAAV-T](#)