

Features

- Frequency range : 32.768 kHz
- SMD : Ceramic package
- External dimensions (mm)
L : 1.6 x W : 1.0 x H : 0.5
- RoHS compliant & Pb free


Applications

- Smart phone
- Compact portable consumer devices
- Communication devices
- Consumer products


Electrical Characteristics

Item	Symbol	9HT12	Conditions
Nominal Frequency	f_0	32.768 kHz	
Frequency Tolerance	$\Delta f/f_0$	$\pm 20\text{ppm}$, $\pm 30\text{ppm}$, $\pm 50\text{ppm}$	at 25°C
Load Capacitance	C_L	6pF, 7pF, 9pF, 12.5pF	
Operating Temperature Range	T_{OTR}	-40°C ~ +85°C	
Storage Temperature Range	T_{STR}	-55°C ~ +125°C	
Turnover Temperature	T_M	25°C $\pm$ 5°C	
Temperature Coefficient	β	-0.04 ppm/°C ² Max.	
Motional Capacitance	C_1	6.4 fF Typ.	
Motional Resistance (ESR)	R_1	90 kΩ Max.	at 25°C
Drive Level	D_L	0.1μW Typ. / 0.5μW Max.	
Aging	$\Delta f/f_0$	± 3 ppm Max.	at 25°C $\pm$ 3°C, first year
Shunt Capacitance	C_0	1.3 pF Typ.	

Dimensions



Top View Crystal Connection



Ordering Information

9HT12 - 32.768K D Z F - T

Frequency Tolerance (at 25°C)

B ± 50 ppm
A ± 30 ppm
D ± 20 ppm

Frequency Stability (over Temp.)

Z **Standard for kHz**


Packaging Method

T **Tape & Reel**


Load Capacitance

B	6 pF
Y	7 pF
C	9 pF
F	12.5 pF

Packing



Reflow Profile



Total time : Max. 200 sec.
Solder melting point : 220°C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[9HT12-32.768KBZF-T](#) [9HT12-32.768KAZF-T](#) [9HT12-32.768KDZF-T](#) [9HT12-32.768KBZC-T](#) [9HT12-32.768KDZC-T](#)
[9HT12-32.768KAZY-T](#) [9HT12-32.768KBZY-T](#) [9HT12-32.768KDZY-T](#) [9HT12-32.768KAZC-T](#) [9HT12-32.768KAZB-T](#)
[9HT12-32.768KDZB-T](#) [9HT12-32.768KBZB-T](#)