

Features

- Frequency range : 32.768 kHz
- SMD : Plastic package
- External dimensions (mm)
L : 6.9 x W : 1.4 x H : 1.4
- RoHS compliant
Contains Pb, exempted by RoHS directive


Applications

- Small mobile devices
Consumer products

Electrical Characteristics

Item	Symbol	9HT7	Conditions
Nominal Frequency	f_0	32.768 kHz	
Frequency Tolerance	$\Delta f/f_0$	$\pm 20\text{ppm}$, $\pm 30\text{ppm}$, $\pm 50\text{ppm}$	at 25°C
Load Capacitance	C_L	7pF, 9pF, 12.5pF	
Operating Temperature Range	T_{OTR}	-40°C ~ +85°C	
Storage Temperature Range	T_{STR}	-55°C ~ +125°C	
Turnover Temperature	T_M	25°C $\pm$ 5°C	
Temperature Coefficient	β	-0.04ppm/°C ² Max.	
Motional Capacitance	C_1	1.9 fF Typ.	
Motional Resistance (ESR)	R_1	65 kΩ Max.	at 25°C
Drive Level	D_L	1 μ W Max.	
Aging	$\Delta f/f_0$	± 3 ppm Max.	at 25°C $\pm$ 3°C, first year
Shunt Capacitance	C_0	0.8 pF Typ.	

Dimensions



Internal Connection



Do not connect pin2 & pin3 to external device.

(Unit: mm)

Ordering Information

9HT7 - 32.768K - D Z F - T

Frequency Tolerance (at 25°C)

B	± 50 ppm
A	± 30 ppm
D	± 20 ppm

Frequency Stability (over Temp.)

Z	Standard for kHz
---	------------------


Packaging Method

T	Tape & Reel
---	-------------

Load Capacitance


Y	7 pF
C	9 pF
F	12.5 pF

Packing



Reflow Profile

Total time : Max. 200 sec.
Solder melting point : 220°C



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[9HT7-32.768KBZF-T](#) [9HT7-32.768KAZF-T](#) [9HT7-32.768KDZF-T](#) [9HT7-32.768KBZY-T](#) [9HT7-32.768KAZY-T](#) [9HT7-32.768KDZY-T](#) [9H03200413](#)