

Features

- Frequency range : 3.2MHz to 90MHz
- Resistance welded, metal can SMD type
- External dimensions (mm)
L : 12.7 x W : 4.8 x H : 3.8
- RoHS compliant & Pb free

Applications

- TV, STB, Cable modem
- Microprocessor
- Computer peripherals
- Home electronics
- Consumer products

Electrical Characteristics


Item		QT49S	Conditions
Frequency Range	F_0	3.2MHz ~ 90MHz	
Frequency Tolerance	F_{tol}	$\pm 50\text{ppm}$, $\pm 30\text{ppm}$, $\pm 20\text{ppm}$, $\pm 10\text{ppm}$	at 25°C
Frequency Stability over Operating Temperature Range (refer to 25°C)	F_{stab}	$\pm 50\text{ ppm}$	-20°C ~ +70°C
		$\pm 30\text{ ppm}$	
		$\pm 20\text{ ppm}$	
		$\pm 10\text{ ppm}$	
		$\pm 30\text{ ppm}$	-40°C ~ +85°C
		$\pm 20\text{ ppm}$	
Operating Temperature Range	T_{OTR}	-20°C ~ +70°C	
		-40°C ~ +85°C	
Shunt Capacitance	C_0	7pF Max.	
Drive Level	D_L	1 ~ 500μW (100μW Typ.)	
Load Capacitance	C_L	12pF, 16pF, 18pF, 20pF	
Aging	F_{aging}	$\pm 5\text{ ppm Max.}$	at 25°C $\pm 3^\circ\text{C}$, first year
Storage Temperature Range	T_{STR}	-55°C ~ +125°C	

Motional Resistance (ESR)


Fundamental	
3.2 ~ 3.686 MHz	200Ω Max.
3.686 ~ 5 MHz	150Ω Max.
5 ~ 10 MHz	80Ω Max.
10 ~ 14 MHz	40Ω Max.
14 ~ 30 MHz	30Ω Max.

3rd Overtone	
27 ~ 30 MHz	100Ω Max.
30 ~ 50 MHz	80Ω Max.
50 ~ 90 MHz	60Ω Max.


Dimensions



Ordering Information




Packing



Reflow Profile

Solder melting point : $220^{\circ}\text{C} \pm 10^{\circ}\text{C}$, 60 sec. Min.

Peak temperature : $260^{\circ}\text{C} \pm 5^{\circ}\text{C}$, 10 sec. Min.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[QT49S-11.000MAHJ-T](#) [QT49S-11.2896MAHJ-T](#) [QT49S-12.288MAHJ-T](#) [QT49S-12.500MAHJ-T](#) [QT49S-13.225625MAHE-T](#) [QT49S-15.360MAHJ-T](#) [QT49S-16.000MAHE-T](#) [QT49S-16.384MAHJ-T](#) [QT49S-18.432MAHE-T](#) [QT49S-19.6608MAHJ-T](#) [QT49S-19.660MAHJ-T](#) [QT49S-20.000MAHE-T](#) [QT49S-22.000MAHJ-T](#) [QT49S-22.1184MAHE-T](#) [QT49S-22.5792MAHJ-T](#) [QT49S-24.000MAHE-T](#) [QT49S-25.000MAHE-T](#) [QT49S-26.000MAHJ-T](#) [QT49S-27.000MAHE-T](#) [QT49S-27.120MAHJ-T](#) [QT49S-28.224MAHJ-T](#) [QT49S-28.63636MAHE-T](#) [QT49S-28.800MAHJ-T](#) [QT49S-30.000MAHE-T](#) [QT49S-30.000MAHJ-T](#) [QT49S-32.000MAHE-T](#) [QT49S-32.000MAHJ-T](#) [QT49S-33.3330MAHJ-T](#) [QT49S-4.000MAHE-T](#) [QT49S-4.194304MAHJ-T](#) [QT49S-48.000MAHJ-T](#) [QT49S-5.000MAHJ-T](#) [QT49S-50.000MAHJ-T](#) [QT49S-54.000MAHJ-T](#) [QT49S-6.000MAHJ-T](#) [QT49S-6.144MAHJ-T](#) [QT49S-6.500MAHJ-T](#) [QT49S-60.000MAHJ-T](#) [QT49S-64.000MAHJ-T](#) [QT49S-7.3728MAHE-T](#) [QT49S-7.680MAHJ-T](#) [QT49S-8.000MAHE-T](#) [QT49S-10.000MAHJ-T](#) [QT49S-11.0592MAHJ-T](#) [QT49S-12.000MAHJ-T](#) [QT49S-13.560MAHJ-T](#) [QT49S-14.31818MAHJ-T](#) [QT49S-14.7456MAHJ-T](#) [QT49S-16.000MAHJ-T](#) [QT49S-18.432MAHJ-T](#) [QT49S-19.200MAHJ-T](#) [QT49S-20.000MAHJ-T](#) [QT49S-22.1184MAHJ-T](#) [QT49S-24.000MAHJ-T](#) [QT49S-24.576MAHJ-T](#) [QT49S-25.000MAHJ-T](#) [QT49S-27.000MAHJ-T](#) [QT49S-28.63636MAHJ-T](#) [QT49S-3.579545MAHJ-T](#) [QT49S-3.6864MAHJ-T](#) [QT49S-4.000MAHJ-T](#) [QT49S-4.096MAHJ-T](#) [QT49S-4.9152MAHJ-T](#) [QT49S-7.3728MAHJ-T](#) [QT49S-8.000MAHJ-T](#) [QT49S-10.000MAAJ-T](#) [QT49S-10.000MAGJ-T](#) [QT49S-10.000MBBK-T](#) [QT49S-10.000MEEJ-T](#) [QT49S-11.000MAAJ-T](#) [QT49S-11.0592MAAJ-T](#) [QT49S-11.0592MAGJ-T](#) [QT49S-11.0592MBBK-T](#) [QT49S-11.0592MEEJ-T](#) [QT49S-11.2896MAAJ-T](#) [QT49S-11.2896MBBK-T](#) [QT49S-11.2896MEEJ-T](#) [QT49S-12.000MAAJ-T](#) [QT49S-12.000MAGE-T](#) [QT49S-12.000MAGJ-T](#) [QT49S-12.000MAHK-T](#) [QT49S-12.000MBBK-T](#) [QT49S-12.000MEEJ-T](#) [QT49S-12.288MAAE-T](#) [QT49S-12.288MAAJ-T](#) [QT49S-12.288MBBK-T](#) [QT49S-12.288MEEJ-T](#) [QT49S-12.500MAAJ-T](#) [QT49S-13.0625MBBK-T](#) [QT49S-13.225625MAAE-T](#) [QT49S-13.225625MAAK-T](#) [QT49S-13.225625MBBK-T](#) [QT49S-13.225625MDAE-T](#) [QT49S-13.560MAAE-T](#) [QT49S-13.560MAAJ-T](#) [QT49S-13.560MBBK-T](#) [QT49S-13.560MEEJ-T](#) [QT49S-13.824MAAJ-T](#) [QT49S-13.824MEEK-T](#) [QT49S-14.31818MAAJ-T](#)