

Features

- Frequency range : 1MHz to 133MHz
- SMD seam sealing ceramic package
- Supply voltage : 1.8V ~ 3.3V
- CMOS output
- Tri-state function available
- External dimensions (mm)
L : 3.2 x W : 2.5 x H : 1.0
- RoHS compliant & Pb free

Applications

- Networking, Server, Storage
- Wireless communications
- Fibre channel, Ethernet, SATA, SAS, PCI-E, USB, WLAN, xDSL, xPON
- PC mainboard, Notebook, HDD, SSD, Graphics card, Computer peripherals
- Audio, Video, Gaming, Printer, DSC, IP CAM, Consumer products


Electrical Characteristics

Item	QTM325	Conditions
Frequency Range (F_0)	1MHz ~ 133MHz	
Frequency Stability (F_{stab})	± 50 , ± 25 ppm	-10°C ~ +70°C; Note [1]
	± 50 , ± 25 , ± 20 ppm	-40°C ~ +85°C; Note [1]
Operating Temperature Range (T_{OTR})	-10°C ~ +70°C	
	-40°C ~ +85°C	
Supply Voltage (V_{DD})	1.8V, 2.5V, 3.3V	$V_{DD} \pm 10\%$
Current Consumption (I_{DD})	10 mA Max.	1MHz ~ 75MHz
	15 mA Max.	75MHz ~ 133MHz
Output Type	CMOS	
Output Load (C_L)	15 pF	
Output Voltage High (V_{OH})	90% V_{DD} Min.	
Output Voltage Low (V_{OL})	10% V_{DD} Max.	
Rise & Fall Time (T_r / T_f)	8 ns Max.	10% ~ 90% of V_{DD}
Duty Cycle	45% ~ 55%	
Start-up Time	5 ms Max.	
Enable Voltage High, Logic "1"	70% V_{DD} Min.	Input to Pin1 Note [2]
Enable Voltage Low, Logic "0"	30% V_{DD} Max.	
Phase Jitter, RMS	1 ps Max.	Note [3]
Aging (F_{aging})	± 3 ppm Max.	at 25°C $\pm$ 3°C, first year
Storage Temperature Range (T_{STR})	-55°C ~ +125°C	

Notes:

- [1] Inclusive of frequency tolerance at 25°C, 1st year aging at 25°C, and variations over operating temperature, supply voltage, and load.
- [2] Output will be enabled if Pin1 is Logic "1" or open; Output will be disabled if Pin1 is Logic "0".
- [3] Freq. 10MHz~40MHz, integrated 12kHz~5MHz; Freq. >40MHz, integrated 12kHz~20MHz.

Dimensions



(Unit: mm)

Ordering Information

QTM325 - 30.000M B E - T

Frequency in Hz

Please contact us for available frequencies

Packaging Method

T Tape & Reel





Supply Voltage

B	3.3 V
C	2.5 V
D	1.8 V

Frequency Stability

B	± 50 ppm (-10°C ~ +70°C)
A	± 25 ppm (-10°C ~ +70°C)
E	± 50 ppm (-40°C ~ +85°C)
D	± 25 ppm (-40°C ~ +85°C)
I	± 20 ppm (-40°C ~ +85°C)


Packing



Reflow Profile

Solder melting point : $220^\circ\text{C} \pm 10^\circ\text{C}$, 60 sec. Min.

Peak temperature : $260^\circ\text{C} \pm 10^\circ\text{C}$, 10 sec. Min.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[QTM325-16.384MBE-T](#) [QTM325-24.000MBE-T](#) [QTM325-25.000MBE-T](#) [QTM325-25.000MDE-T](#) [QTM325-27.000MBE-T](#) [QTM325-27.000MDE-T](#) [QTM325-40.000MDE-T](#) [QTM325-50.000MDE-T](#) [QTM325-14.31818MBA-T](#) [QTM325-14.31818MBB-T](#) [QTM325-14.31818MBE-T](#) [QTM325-24.576MBA-T](#) [QTM325-25.000MBB-T](#) [QTM325-30.000MBA-T](#) [QTM325-48.000MBB-T](#) [QTM325-54.000MBE-T](#) [QTM325-75.000MBD-T](#) [QTM325-75.000MBE-T](#) [QTM325-75.000MDE-T](#) [QTM325-50.000MBD-T](#) [QTM325-1.000MCE-T](#) [QTM325-24.000MDI-T](#) [QTM325-48.000MDE-T](#) [QTM325-16.384MDE-T](#) [QTM325-20.000MBE-T](#) [QTM325-33.000MBE-T](#) [QTM325-24.576MDE-T](#) [QTM325-33.000MDE-T](#) [QTM325-62.500MBE-T](#) [QTM325-2.048MBE-T](#) [QTM325-25.000MBD-T](#) [QTM325-25.000MCE-T](#) [QTM325-33.000MCE-T](#) [QTM325-62.500MCE-T](#) [QTM325-16.000MBD-T](#) [QTM325-16.384MCE-T](#) [QTM325-32.768MBE-T](#) [QTM325-32.768MDE-T](#) [QTM325-66.000MBE-T](#) [QTM325-20.000MCE-T](#) [QTM325-10.000MCE-T](#) [QTM325-32.000MBE-T](#) [QTM325-40.000MCE-T](#) [QTM325-20.480MDE-T](#) [QTM325-30.000MDE-T](#) [QTM325-48.000MBE-T](#) [QTM325-48.000MCE-T](#) [QTM325-2.048MCE-T](#) [QTM325-60.000MCE-T](#) [QTM325-12.288MBE-T](#) [QTM325-12.288MCE-T](#) [QTM325-24.000MDD-T](#) [QTM325-30.000MCE-T](#) [QTM325-7.3728MBD-T](#) [QTM325-33.333MCE-T](#) [QTM325-66.000MCE-T](#) [QTM325-2.048MDE-T](#) [QTM325-33.333MBD-T](#) [QTM325-60.000MDE-T](#) [QTM325-27.000MCE-T](#) [QTM325-32.000MDE-T](#) [QTM325-40.000MBE-T](#) [QTM325-50.000MCE-T](#) [QTM325-62.500MDE-T](#) [QTM325-24.000MCE-T](#) [QTM325-30.000MBE-T](#) [QTM325-72.000MBA-T](#) [QTM325-10.000MBE-T](#) [QTM325-24.576MCE-T](#) [QTM325-1.000MBE-T](#) [QTM325-1.000MDE-T](#) [QTM325-66.000MDE-T](#) [QTM325-10.000MDE-T](#) [QTM325-32.000MCE-T](#) [QTM325-8.192MBA-T](#) [QTM325-12.288MDE-T](#) [QTM325-20.480MBE-T](#) [QTM325-32.768MCE-T](#) [QTM325-60.000MBE-T](#) [QTM325-33.333MBE-T](#) [QTM325-50.000MBE-T](#) [QTM325-20.480MCE-T](#) [QTM325-24.576MBE-T](#) [QTM325-33.333MDE-T](#) [QTM325-20.000MDE-T](#) [QTM325-24.000MDE-T](#)