

SMD LVDS Crystal Oscillators - Differential Output

5.0 x 3.2 x 1.2 mm CF Series



Features


- 3rd overtone solution.
- 3.3V and 2.5V operation available.
- LVDS output, output frequencies 25 MHz to 200 MHz.
- Excellent low phase noise and jitter.
- Tri-State function available.
- Applications : Fibre Channel, Gigabit Ethernet, Serial ATA, Serial Attached SCSI, PCI-Express, SDH/SONET.
- RoHS Compliant / Pb Free.

Electrical Specifications

Item / Type	CF
Output Type	LVDS
Output Load	100 Ω
Oscillation Mode	3rd Overtone
Supply Voltage	2.5 V, 3.3 V
Frequency Range	25 ~ 200 MHz
Overall Frequency Stability *	± 50 ppm, or specify
Operating Temperature Range	0 ~ +70 $^{\circ}\text{C}$, -40 ~ +85 $^{\circ}\text{C}$, or specify
Storage Temperature Range	-55 ~ +125 $^{\circ}\text{C}$
Voltage Vol (Min.) / Voh (Max.)	0.9 V / 1.6 V
Rise (Tr) / Fall (Tf) Time (20 % ~ 80 %)	1 nS Max.
Supply Current	80 mA Max.
Symmetry	45 ~ 55 %
Start-up Time	10 mS Max.
Phase Jitter (12 KHz ~ 20 MHz)	1 pS Max.

* Inclusive of frequency tolerance at 25 $^{\circ}\text{C}$, variation over temperature, supply voltage variation, aging and vibration.


Dimensions



PAD FUNCTION:

- 1: ENABLE CONTROL or NC
- 2: ENABLE CONTROL or NC
- 3: GND
- 4: OUT
- 5: OUTN
- 6: VDD

* :External high frequency power supply decoupling required.



Units: mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TXC Corporation:](#)

[CF-100.000MBE-T](#) [CF-156.250MBB-T](#) [CF-133.3330MBB-T](#) [CF-150.000MBB-T](#) [CF-155.520MBB-T](#) [CF-125.000MBE-T](#)