


AS SUPPLIED



REVISIONS		
LTR	DESCRIPTION	DATE
Z1	REVISED PER ECO-11-005139	29MAR11

NOTES:

1. ALL DIMENSIONS ARE IN  $\frac{\text{INCHES}}{[\text{MILLIMETERS}]}$
2. DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:
  - a - AS SUPPLIED
  - b - AFTER UNRESTRICTED RECOVERY

3. COATING (ADHESIVE): IS OPTIONAL  
AS SUPPLIED DIMENSIONS APPEARING  
IN TABLE ARE FOR UNCOATED PARTS.  
WHEN COATING IS ADDED, ENTRY  
DIAMETER WILL BE REDUCED BY .06 MAX.

4. "S" AND "T" DIMENSIONS APPLY TO A MINIMUM OF 240° OF THE CIRCUMFERENCE.

5. MATERIAL -780 IS AVAILABLE FOR PART NO. 202C611 ONLY

6. ORDERING INFORMATION:

202C6XX -XX -XX /XXX -0

BASE PART NUMBER \_\_\_\_\_

MATERIAL DASH NUMBER \_\_\_\_\_

-50 FLEXIBLE VPB (RT-1313)

—51 FLEXIBLE EPB (RT-1321)

-71 FLEXIBLE POLYOLEFIN (RT-1316)

—770 NBCCS (RT-770 TYPE II)




–780 NBCCS (RT-780 TYPE II)

MODIFICATION NUMBER

ADHESIVE SLASH NUMBER .  
SEE COMPATIBILITY CHART

COLOR DESIGNATOR

## CUSTOMER DRAWING

COMPATIBILITY CHART			UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCHES. METRIC DIMENSIONS ARE IN BRACKETS.  DECIMAL TOLERANCES .XXX ± 0.005 [0.13 mm] .XX ± 0.01 [0.25 mm] .X ± 0.1 [0.50 mm]  ANGLE TOLERANCE .X ± 1 DEG.  TE CONNECTIVITY RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANY TIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.  © 2006,2011 Tyco Electronics Corporation.a TE connectivity Ltd.company. All rights reserved.	DRAWN YUNGUYEN	 TE Connectivity Raychem Molded Parts 305 Constitution Dr Menlo Park, CA 94025		
MATERIAL DASH NO.	ADHESIVE (COATING) SLASH NO.	ADHESIVE (COATING) S NO.		APPROVED STRAN			TITLE  UNI-BOOT
-50	/86	S-1048			SIZE B	CODE IDENT. NO. 06090	DWG. NO. 202C611thru663
-51	/164; /86	S-1124; S-1048					
-71	/42; /86; /180	S-1017; S-1048; S-1030					
-770	N/A	N/A					
-780 	N/A	N/A	DO NOT SCALE THIS DRAWING		SHEET 1 OF 1		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202C632-50/86-0](#)