


AS SUPPLIED



AFTER UNRESTRICTED RECOVERY

| | | |
|-----------|---------------------------|---------|
| REVISIONS | | |
| LTR | DESCRIPTION | DATE |
| Z1 | REVISED PER ECO-11-005139 | 29MAR11 |

NOTES:

1. ALL DIMENSIONS ARE IN $\frac{\text{INCHES}}{[\text{MILLIMETERS}]}$
2. DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:
 - a - AS SUPPLIED
 - b - AFTER UNRESTRICTED RECOVERY

3. COATING (ADHESIVE): IS OPTIONAL
AS SUPPLIED DIMENSIONS APPEARING
IN TABLE ARE FOR UNCOATED PARTS.
WHEN COATING IS ADDED, ENTRY
DIAMETER WILL BE REDUCED BY .06 MAX.

4. "S" AND "T" DIMENSIONS APPLY TO A MINIMUM OF 240° OF THE CIRCUMFERENCE.

- △ 5. MATERIAL -780 IS AVAILABLE FOR PART NO. 202C611 ONLY

6. ORDERING INFORMATION: 00000000 0000 0000 0000 0000 0000

202C6XX -XX -XX /XXX -0

BASE PART NUMBER _____

MATERIAL DASH NUMBER _____

-50 FLEXIBLE VPB (RT-1313)

-51 FLEXIBLE EPB (RT-1321)

-71 FLEXIBLE POLYOLEFIN (RT-1316)

–770 NBCCS (RT-770 TYPE II)

–780 NBCCS (RT–780 TYPE II)




MODIFICATION NUMBER

ADHESIVE SLASH NUMBER

SEE COMPATIBILITY CHART

COLOR DESIGNATOR

CUSTOMER DRAWING

| | | | | | | | | |
|--|------------------------------|--------------------------|--|--|--|---|--------------------------|----------------------------|
| COMPATIBILITY CHART | | | <div>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCHES. METRIC DIMENSIONS ARE IN BRACKETS.</div> <div>DECIMAL TOLERANCES</div> <div>.XXX ± 0.005 [0.13 mm] .XX ± 0.01 [0.25 mm] .X ± 0.1 [0.50 mm]</div> <div>ANGLE TOLERANCE</div> <div>.X ± 1 DEG.</div> <div>TE CONNECTIVITY RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANY TIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.</div> <div>© 2006,2011 Tyco Electronics Corporation.a TE connectivity Ltd.company. All rights reserved.</div> | DRAWN YUNGUYEN | | <div> TE Connectivity</div> <div>Raychem Molded Parts 305 Constitution Dr Menlo Park, CA 94025</div> | | |
| MATERIAL DASH NO. | ADHESIVE (COATING) SLASH NO. | ADHESIVE (COATING) S NO. | | APPROVED STRAN | | TITLE UNI-BOOT | | |
| -50 | /86 | S-1048 | | <div>THIRD ANGLE PROJECTION</div> <div></div> | | SIZE B | CODE IDENT. NO. 06090 | DWG. NO. 202C611thru663 |
| -51 | /164; /86 | S-1124; S-1048 | | | | | | |
| -71 | /42; /86; /180 | S-1017; S-1048; S-1030 | | | | | | |
| -770 | N/A | N/A | | | | | | |
| -780  | N/A | N/A | | | | | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202C653-71/42-0](#)