




**NOTES**

- ALL DIMENSIONS ARE IN  $\frac{\text{INCHES}}{\text{MILLIMETERS}}$
- DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:
  - a - AS SUPPLIED
  - b - AFTER UNRESTRICTED RECOVERY

3. COATING (ADHESIVE): IS OPTIONAL AS SUPPLIED DIMENSIONS APPEARING IN TABLE ARE FOR UNCOATED PARTS. WHEN COATING IS ADDED, ENTRY DIAMETER WILL BE REDUCED BY .06 [1.5] MAX.

4. ORDERING INFORMATION



| REVISIONS |                           |            |
|-----------|---------------------------|------------|
| LTR       | DESCRIPTION               | DATE       |
| F         | REVISED PER ECO-11-007558 | 04/11/2011 |

TABLE OF DIMENSIONS

| PART DESCRIPTION | H           |     | J           |     | K           |             | L           |             | P            | R          | S         | LW        | CABLE O.D. RANGE |             | HOLE DIAMETER      |                    |                    |
|------------------|-------------|-----|-------------|-----|-------------|-------------|-------------|-------------|--------------|------------|-----------|-----------|------------------|-------------|--------------------|--------------------|--------------------|
|                  | MAX         | b   | MAX         | b   | MIN         | ±8% b       | MIN         | MAX         | ±10% b       | ±10% b     | ±10% b    | ±20% b    | MIN              | MAX         | .063±.02 [1,6±0,5] | .125±.02 [3,2±0,5] | .250±.02 [6,4±0,5] |
|                  |             |     |             |     |             |             |             |             |              |            |           |           |                  |             | PANEL THICKNESS    | PANEL THICKNESS    | PANEL THICKNESS    |
| 205A112          | 1.16 [29,5] | .06 | 1.01 [25,7] | .06 | .44 [11,2]  | .50 [12,7]  | .44 [11,2]  | .17 [4,3]   | 1.75 [44,5]  | .65 [16,5] | .26 [6,6] | .06 [1,5] | .17 [4,3]        | .40 [10,2]  | .98 [24,9]         | .99 [25,2]         | 1.00 [25,4]        |
| 205A123          | 1.50 [38,1] | .06 | 1.34 [34,0] | .06 | .71 [18,0]  | .78 [19,8]  | .71 [18,0]  | .38 [9,7]   | 2.20 [55,9]  | .65 [16,5] | .26 [6,6] | .07 [1,8] | .38 [9,7]        | .70 [17,8]  | 1.27 [32,3]        | 1.28 [32,5]        | 1.31 [33,3]        |
| 205A134          | 2.00 [50,8] | .06 | 1.83 [46,5] | .06 | 1.09 [27,7] | 1.20 [30,5] | 1.09 [27,7] | .65 [16,5]  | 2.25 [57,2]  | .70 [17,8] | .26 [6,6] | .10 [2,5] | .65 [16,5]       | 1.05 [26,7] | 1.74 [44,2]        | 1.75 [44,5]        | 1.78 [45,2]        |
| 205A145          | 2.30 [58,4] | .06 | 2.15 [54,6] | .06 | 1.39 [35,3] | 1.50 [38,1] | 1.39 [35,3] | .99 [25,2]  | 3.00 [76,2]  | .69 [17,5] | .26 [6,6] | .09 [2,3] | 1.00 [25,4]      | 1.35 [34,3] | 2.04 [51,8]        | 2.06 [52,3]        | 2.09 [53,1]        |
| 205A155          | 3.06 [77,7] | .06 | 2.97 [75,4] | .06 | 1.82 [46,2] | 1.98 [50,3] | 1.82 [46,2] | 1.28 [32,5] | 3.60 [91,4]  | .78 [19,8] | .27 [6,9] | .10 [2,5] | 1.28 [32,5]      | 1.80 [45,7] | 2.95 [74,9]        | 2.97 [75,4]        | 3.00 [76,2]        |
| 205A165          | 3.92 [99,6] | .06 | 3.82 [97,0] | .06 | 2.51 [63,8] | 2.76 [70,1] | 2.51 [63,8] | 1.77 [45,0] | 4.50 [114,3] | .83 [21,1] | .27 [6,9] | .12 [3,1] | 1.77 [45,0]      | 2.50 [63,5] | 3.78 [96,0]        | 3.80 [96,5]        | 3.83 [97,3]        |

If this document is printed it becomes uncontrolled. Check for the latest revision

Raychem Molded Parts  
**CUSTOMER DRAWING**

COMPATIBILITY CHART

| MATERIAL DASH NO. | ADHESIVE (COATING) SLASH NUMBER | ADHESIVE (COATING) S NUMBER |
|-------------------|---------------------------------|-----------------------------|
| -3                | /42; /86;                       | S-1017; S-1048;             |
| -4                | /42; /86;                       | S-1017; S-1048;             |
| -25               | /42; /86; /225                  | S-1017; S-1048; S-1206      |
| -100              | /86;                            | S-1048;                     |

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCHES. METRIC DIMENSIONS ARE IN BRACKETS.  
DECIMAL TOLERANCES  
.XXX ± 0.005 [0.13 mm]  
.XX ± 0.01 [0.25 mm]  
.X ± 0.1 [0.50 mm]  
ANGLE TOLERANCE  
.X ± 1 DEG.  
TYCO ELECTRONICS CORPORATION RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANY TIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.  
© 2001- 2011 Tyco Electronics Corporation. All rights reserved.

REVISED  
UNGUYEN  
APPROVED  
DHURRELL  
THIRD ANGLE PROJECTION

TE Connectivity  
**STE**  
TITLE  
FEEDTHROUGH, SEAL  
SIZE B  
CODE IDENT. NO. 06090  
DWG. NO. 205A112thru165  
SCALE: NTS DO NOT SCALE THIS DRAWING SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[205A112-3/42-0](#)