








LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A2	REVISED PER ECO-15-014342	07OCT2015	NK	RH




- | | |
|---|---|
| 1 | HARDWARE SUPPLIED WITH THREADED-BUSHING
PARTS ONLY: TE P/N 2213733-3 (NUT) X2
P/N 2213733-2 (LOCKING WASHER) X1 |
|---|---|

	POS.1	POS.2	POS.3
MODEL NO.			
TMS	ON	NONE	ON
TERM. COMM.	2-3,5-6		2-1,5-4
SCHEMATIC		N/A	


SWITCH FUNCTION



WITHOUT LOCKING RING



WITH STANDARD LOCKING RING



P.C MOUNTING

LAYOUT FOR PN 2267077-2

SPECIFICATIONS

MECHANICAL LIFE: 30,000 MAKE-AND-BREAK CYCLES.

CONTACT RESISTANCE: 20 mΩ MAX. INITIAL @ 2-4VDC
100mA FOR BOTH SILVER AND GOLD PLATED CONTACTS.



CONTACT RATING: GOLD PLATED: 0.4VA MAX @ 20 V MAX (AC OR DC)

INSULATION RESISTANCE: 1,000 MΩ MIN.

DIELECTRIC STRENGTH: 1,000 Vrms MIN.@SEA LEVEL.

OPERATING TEMPERATURE: -30°C TO 85°C .




SILVER	ON-ON	SOLDER LUG	VERTICAL	2	2	TMD1T4B5M1QE	2267077-3
GOLD	ON-ON	PC THROUGH HOLE	VERTICAL	2	2	TMD1T4B5M2RE	2267077-2
GOLD	ON-ON	PC THROUGH HOLE	VERTICAL	1	2	TMS1T4B5M2RE	2267077-1
CONTACT MATERIAL	FUNCTION	TERMINATION	MOUNT ANGLE	POLES	THROWS	DESCRIPTIVE PN	TE PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 10JUL2014		 TE Connectivity	
		CHK HILL, RYAN 10JUL2014			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SUBMINIATURE TOGGLE SWITCH	
		APVD HILL, RYAN 10JUL2014			
0 PLC ± — 1 PLC ± 0.38[.015] 2 PLC ± 0.25[.010] 3 PLC ± — 4 PLC ± — ANGLES ± 5°		PRODUCT SPEC —			
		APPLICATION SPEC —			
MATERIAL —		FINISH —		SIZE A2	
		WEIGHT —		CAGE CODE 00779	
				DRAWING NO C-2267077	
				RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 3:1	
				SHEET 1 OF 3	
				REV A2	

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
—	—	—	—	SEE SHEET 1	—	—

MODEL NO.	POS.1	POS.2	POS.3
TMD	ON	NONE	ON
TERM. COMM.	2-3	N/A	2-1
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING

P.C MOUNTING

LAYOUT FOR PN 2267077-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

NAGALAKSHMI K

10JUL2014

CHK

HILL, RYAN

10JUL2014

APVD

HILL, RYAN

10JUL2014

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

TE

TE Connectivity

NAME

SUBMINIATURE TOGGLE SWITCH

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=2267077

RESTRICTED TO

—

SCALE

3:1

SHEET

2 OF 3




REV

A2


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
-	-	-	-	SEE SHEET 1	-	-

MODEL NO.	POS.1	POS.2	POS.3
TMD	ON	NONE	ON
TERM. COMM.	2-3,5-6	N/A	2-1,5-4
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING



SOLDER LUG

LAYOUT FOR PN 2267077-3

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	0.38[.015]
2 PLC	±	0.25[.010]
3 PLC	±	-
4 PLC	±	-
ANGLES	±	5°

FINISH
-

DWN
NAGALAKSHMI K
10JUL2014

CHK
HILL, RYAN
10JUL2014

APVD
HILL, RYAN
10JUL2014

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
SUBMINIATURE TOGGLE SWITCH

SIZE A2	CAGE CODE 00779	DRAWING NO. C=2267077	RESTRICTED TO -
------------	--------------------	--------------------------	--------------------

SCALE 3:1	SHEET 3 OF 3	REV A2
--------------	-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TMD1T4B5M1QE](#)