



LOC —	DIST —	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
			A1	REVISED PER ECO-15-014342	07OCT2015	NK	RH	

1 HARDWARE SUPPLIED WITH THREADED-BUSHING
PARTS ONLY: TE P/N 2213733-1 (NUT) X2
P/N 2213733-2 (LOCKING WASHER) X1




MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	OFF	ON
TERM. COMM.	2-3	OPEN	2-1
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING



SOLDER LUG

LAYOUT FOR PN 2267079-6

SPECIFICATIONS

MECHANICAL LIFE: 30,000 MAKE-AND-BREAK CYCLES.

CONTACT RESISTANCE: 20 mΩ MAX. INITIAL @ 2-4VDC
100mA FOR BOTH SILVER AND GOLD PLATED CONTACTS.

CONTACT RATING: SILVER PLATED: 3A @ 120 VAC OR 28 VDC, 1A @ 250 VAC
GOLD PLATED: 0.4VA MAX @ 20 V MAX (AC OR DC)



INSULATION RESISTANCE: 1,000 MΩ MIN.

DIELECTRIC STRENGTH: 1,000 Vrms MIN.@SEA LEVEL.

OPERATING TEMPERATURE: -30°C TO 85°C.


GOLD	ON-OFF-ON	PC THROUGH-HOLE	VERTICAL	1	2	TMS3T3B1M2RE	2267079-6
SILVER	ON-ON	SOLDER LUG	VERTICAL	2	2	TMD1T3B1M1QE	2267079-5
SILVER	ON-OFF-ON	SOLDER LUG	VERTICAL	1	2	TMS3T3B1M1QE	2267079-4
SILVER	ON-ON	SOLDER LUG	VERTICAL	1	2	TMS1T3B1M1QE	2267079-3
SILVER	OFF-ON	SOLDER LUG	VERTICAL	1	2	TMS6T3B1M1QE	2267079-2
GOLD	ON-ON	WIRE WRAP	VERTICAL	1	2	TMS1T3B1M5RE	2267079-1
CONTACT MATERIAL	FUNCTION	TERMINATION	MOUNT ANGLE	POLES	THROWS	DESCRIPTIVE PN	TE PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11JUL2014 NAGALAKSHMI K	TE Connectivity				
DIMENSIONS: mm [INCHES]		CHK 11JUL2014 HILL, RYAN					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 11JUL2014 HILL, RYAN	NAME				
0 PLC ± - 1 PLC ± 0.38[.015] 2 PLC ± 0.25[.010] 3 PLC ± - 4 PLC ± - ANGLES ± 5°		PRODUCT SPEC					
MATERIAL		FINISH	SUBMINIATURE TOGGLE SWITCH				
-		-					
WEIGHT		-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
CUSTOMER DRAWING		-	A2	00779	C=2267079		
SCALE		3:1	SHEET		1 of 6	REV	
						A1	




MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	NONE	ON
TERM. COMM.	2-3,5-6		2-1,5-4
SCHEMATIC		N/A	

SWITCH FUNCTION



PANEL MOUNTING



SOLDER LUG

LAYOUT FOR PN 2267079-5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

11JUL2014

NAGALAKSHMI_K

CHK

11JUL2014

HILL, RYAN

APVD

11JUL2014

HILL, RYAN

DIMENSIONS:

mm [INCHES]

0 PLC

±

—

1 PLC

±

0.38[.015]

2 PLC

±

0.25[.010]

3 PLC

±

—

4 PLC

±

—

ANGLES

±

5°

MATERIAL

—

FINISH

—

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

TE Connectivity

NAME

SUBMINIATURE TOGGLE SWITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=2267079

—

SCALE

3:1

SHEET

2 OF 6



REV

A1


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
-	-	-	-	SEE SHEET 1	-	-

MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	NONE	ON
TERM. COMM.	2-3	N/A	2-1
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING




SOLDER LUG

LAYOUT FOR PN 2267079-3


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 11JUL2014		 TE Connectivity					
		CHK HILL, RYAN 11JUL2014							
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SUBMINIATURE TOGGLE SWITCH					
		APVD HILL, RYAN 11JUL2014							
		PRODUCT SPEC —							
		APPLICATION SPEC —							
MATERIAL —		FINISH —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		WEIGHT —		A2	00779	C=2267079	—		
CUSTOMER DRAWING				SCALE	3:1	SHEET	3 of 6	REV	A1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		—	SEE SHEET 1	—	—	—




MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	OFF	ON
TERM. COMM.	2-3	OPEN	2-1
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING




SOLDER LUG

LAYOUT FOR PN 2267079-4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 11JUL2014	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK HILL, RYAN 11JUL2014				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± - 1 PLC ± 0.38[.015] 2 PLC ± 0.25[.010] 3 PLC ± - 4 PLC ± - ANGLES ± 5°		SUBMINIATURE TOGGLE SWITCH			
	FINISH		RESTRICTED TO			
MATERIAL		APVD HILL, RYAN 11JUL2014	PRODUCT SPEC		SIZE	
		APPLICATION SPEC			CAGE CODE	
		WEIGHT	-		DRAWING NO	
		CUSTOMER DRAWING	SCALE 3:1		SHEET 4 OF 6	
			REV A1			

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		—	SEE SHEET 1	—	—	—



MODEL NO.	POS.1	POS.2	POS.3
TMD	OFF	NONE	ON
TERM. COMM.	OPEN	N/A	3-1
SCHEMATIC			

SWITCH FUNCTION

WITHOUT LOCKING RING

WITH STANDARD LOCKING RING






PANEL MOUNTING

LAYOUT FOR PN 2267079-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 11JUL2014	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK HILL, RYAN 11JUL2014				
		APVD HILL, RYAN 11JUL2014	NAME			
		PRODUCT SPEC	SUBMINIATURE TOGGLE SWITCH			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± -		—	A2	00779	C=2267079	—
1 PLC ± 0.38[.015]		WEIGHT	SCALE 3:1			
2 PLC ± 0.25[.010]		—	SHEET 5 OF 6			
3 PLC ± -		CUSTOMER DRAWING	REV A1			
4 PLC ± -		—				
ANGLES ± 5°		—				
FINISH		—				

MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	NONE	ON
TERM. COMM.	2-3	N/A	2-1
SCHEMATIC			


SWITCH FUNCTION



SOLDER LUG

PANEL MOUNTING

LAYOUT FOR PN 2267079-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 11JUL2014		 TE Connectivity							
DIMENSIONS: mm [INCHES]		CHK HILL, RYAN 11JUL2014									
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD HILL, RYAN 11JUL2014		NAME						
	0 PLC ± - 1 PLC ± 0.38[.015] 2 PLC ± 0.25[.010] 3 PLC ± - 4 PLC ± - ANGLES ± 5°		PRODUCT SPEC								
	FINISH		APPLICATION SPEC								
MATERIAL			WEIGHT -		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO		
-			A2		00779	C=2267079		-			
CUSTOMER DRAWING					SCALE	3:1		SHEET	6 of 6	REV	A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TMS3T3B1M2RE](#)