



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECO-15-014342	07OCT2015	NK	RH

1 HARDWARE SUPPLIED WITH THREADED-BUSHING
PARTS ONLY: TE P/N 2213733-1 (NUT) X2
P/N 2213733-2 (LOCKING WASHER) X1




MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	OFF	ON
TERM. COMM.	2-3	OPEN	2-1
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING



SOLDER LUG

LAYOUT FOR PN 2267079-6

GOLD	ON-OFF-ON	PC THROUGH-HOLE	VERTICAL	1	2	TMS3T3B1M2RE	2267079-6
SILVER	ON-ON	SOLDER LUG	VERTICAL	2	2	TMD1T3B1M1QE	2267079-5
SILVER	ON-OFF-ON	SOLDER LUG	VERTICAL	1	2	TMS3T3B1M1QE	2267079-4
SILVER	ON-ON	SOLDER LUG	VERTICAL	1	2	TMS1T3B1M1QE	2267079-3
SILVER	OFF-ON	SOLDER LUG	VERTICAL	1	2	TMS6T3B1M1QE	2267079-2
GOLD	ON-ON	WIRE WRAP	VERTICAL	1	2	TMS1T3B1M5RE	2267079-1
CONTACT MATERIAL	FUNCTION	TERMINATION	MOUNT ANGLE	POLES	THROWS	DESCRIPTIVE PN	TE PN

SPECIFICATIONS

MECHANICAL LIFE: 30,000 MAKE-AND-BREAK CYCLES.

CONTACT RESISTANCE: 20 mΩ MAX. INITIAL @ 2-4VDC
100mA FOR BOTH SILVER AND GOLD PLATED CONTACTS.



CONTACT RATING: SILVER PLATED: 3A @ 120 VAC OR 28 VDC, 1A @ 250 VAC
GOLD PLATED: 0.4VA MAX @ 20 V MAX (AC OR DC)

INSULATION RESISTANCE: 1,000 MΩ MIN.

DIELECTRIC STRENGTH: 1,000 Vrms MIN.@SEA LEVEL.


OPERATING TEMPERATURE: -30°C TO 85°C.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN NAGALAKSHMI K 11JUL2014	TE Connectivity			
DIMENSIONS: mm [INCHES]			CHK HILL, RYAN 11JUL2014				
			APVD HILL, RYAN 11JUL2014	NAME			
			PRODUCT SPEC	SUBMINIATURE TOGGLE SWITCH			
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APPLICATION SPEC				
MATERIAL			WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-			-	A2	00779	C=2267079	-
FINISH			CUSTOMER DRAWING	SCALE	SHEET	REV	
-				3:1	1 of 6	A1	




MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	NONE	ON
TERM. COMM.	2-3,5-6		2-1,5-4
SCHEMATIC		N/A	

SWITCH FUNCTION



PANEL MOUNTING



SOLDER LUG

LAYOUT FOR PN 2267079-5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

11JUL2014

NAGALAKSHMI_K

CHK

11JUL2014

HILL, RYAN

APVD

11JUL2014

HILL, RYAN

DIMENSIONS:

mm [INCHES]

0 PLC

±

—

1 PLC

±

0.38[.015]

2 PLC

±

0.25[.010]

3 PLC

±

—

4 PLC

±

—

ANGLES

±

5°

MATERIAL

—

FINISH

—

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

—

TE Connectivity

NAME

SUBMINIATURE TOGGLE SWITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=2267079

—

SCALE

SHEET

REV

3:1



2 OF 6

A1


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
-	-	-	-	SEE SHEET 1	-	-

MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	NONE	ON
TERM. COMM.	2-3	N/A	2-1
SCHEMATIC			

SWITCH FUNCTION





PANEL MOUNTING




SOLDER LUG

LAYOUT FOR PN 2267079-3


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 11JUL2014		 TE Connectivity			
		CHK HILL, RYAN 11JUL2014					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC ± -				PRODUCT SPEC	
		1 PLC ± 0.38[.015]					
		2 PLC ± 0.25[.010]		APPLICATION SPEC			
		3 PLC ± -					
MATERIAL -		4 PLC ± -		SIZE A2			
		ANGLES ± 5°				CAGE CODE 00779	
		FINISH -					
		WEIGHT -		RESTRICTED TO -			
		CUSTOMER DRAWING					
				SCALE 3:1			
				SHEET 3 of 6			
				REV A1			

		1					
LOC	DIST	REVISIONS					
—	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—




MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	OFF	ON
TERM. COMM.	2-3	OPEN	2-1
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING




SOLDER LUG

LAYOUT FOR PN 2267079-4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 11JUL2014	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK HILL, RYAN 11JUL2014				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± - 1 PLC ± 0.38[.015] 2 PLC ± 0.25[.010] 3 PLC ± - 4 PLC ± - ANGLES ± 5°		SUBMINIATURE TOGGLE SWITCH			
	FINISH		RESTRICTED TO			
MATERIAL	-	APVD HILL, RYAN 11JUL2014	PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO
		WEIGHT	-	A2	00779	C=2267079
		CUSTOMER DRAWING		SCALE	3:1	SHEET 4 OF 6
				REV A1		

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		—	SEE SHEET 1	—	—	—



MODEL NO.	POS.1	POS.2	POS.3
TMD	OFF	NONE	ON
TERM. COMM.	OPEN	N/A	3-1
SCHEMATIC			

SWITCH FUNCTION

WITHOUT LOCKING RING

WITH STANDARD LOCKING RING



PANEL MOUNTING

LAYOUT FOR PN 2267079-2


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 11JUL2014	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK HILL, RYAN 11JUL2014				
		APVD HILL, RYAN 11JUL2014	NAME			
		PRODUCT SPEC	SUBMINIATURE TOGGLE SWITCH			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE			
0 PLC ± -		—	CAGE CODE			
1 PLC ± 0.38[.015]		—	DRAWING NO			
2 PLC ± 0.25[.010]		—	RESTRICTED TO			
3 PLC ± -		—	SCALE			
4 PLC ± -		—	SHEET			
ANGLES ± 5°		—	REV			
FINISH		—	A1			
MATERIAL		—	CUSTOMER DRAWING			
—		—	3:1			
—		—	5 OF 6			
—		—	A1			

MODEL NO.	POS.1	POS.2	POS.3
TMS	ON	NONE	ON
TERM. COMM.	2-3	N/A	2-1
SCHEMATIC			

SWITCH FUNCTION



PANEL MOUNTING



SOLDER LUG

LAYOUT FOR PN 2267079-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

11JUL2014

NAGALAKSHMI K

CHK

11JUL2014

HILL, RYAN

APVD

11JUL2014

HILL, RYAN

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.38[.015]

2 PLC ± 0.25[.010]

3 PLC ± -

4 PLC ± -

ANGLES ± 5°

FINISH -

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

SCALE 3:1

SHEET 6 OF 6

REV A1

TE Connectivity

SUBMINIATURE TOGGLE SWITCH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[TMS1T3B1M1QE](#)